

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060841

Luminaire Tested: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1060841  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-78)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S  
Description: DEFINE 4 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 333.4 lumens  
Efficiency: N/A  
Efficacy: 28.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 1.11 / 0.97  
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1060841

CATALOG NUMBER: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1060841

CATALOG NUMBER: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	87	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2287	2287	2287
5°	2202	2239	2284
10°	2030	2132	2261
15°	1822	1979	2212
20°	1593	1799	2138
25°	1347	1598	2043
30°	1088	1385	1928
35°	810	1157	1817
40°	514	917	1709
45°	206	672	1611
50°	90	429	1471
55°	69	222	1284
60°	48	152	1018
65°	37	151	695
70°	35	133	320
75°	47	140	130
80°	69	159	139
85°	138	277	207

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 1611 cd/sqm



TEST NUMBER: P1060841

CATALOG NUMBER: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.3	7.3
10°-20°	62.7	18.8
20°-30°	79.2	23.8
30°-40°	72.8	21.8
40°-50°	49.6	14.9
50°-60°	26.9	8.1
60°-70°	11.4	3.4
70°-80°	4.0	1.2
80°-90°	2.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	166.3	49.9
0°-40°	239.0	71.7
0°-60°	315.5	94.6
0°-90°	333.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	266	266	266	266	266	
5°	255	259	259	261	264	24
15°	204	211	222	238	248	57
25°	142	151	168	194	215	65
35°	77	87	110	145	173	48
45°	17	27	55	98	132	16
55°	5	5	15	54	86	4
65°	2	2	7	17	34	2
75°	1	4	4	4	4	1
85°	1	3	3	3	2	1
90°	0	0	0	0	0	



TEST NUMBER: P1060841

CATALOG NUMBER: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	265.6	265.6	265.6	265.6	265.6
2.5°	261.8	264.9	263.2	263.9	264.6
5°	254.7	258.6	259.0	261.1	264.2
7.5°	244.9	249.5	252.3	257.6	262.5
10°	232.2	237.9	243.8	252.3	258.6
12.5°	218.9	224.8	233.6	245.6	254.0
15°	204.4	211.1	222.0	237.9	248.1
17.5°	189.3	196.7	209.7	228.4	241.4
20°	173.8	181.9	196.3	217.4	233.3
22.5°	158.0	166.4	182.3	206.2	224.8
25°	141.8	150.9	168.2	194.2	215.0
27.5°	126.3	134.8	153.8	182.3	205.1
30°	109.4	118.9	139.3	169.9	193.9
32.5°	93.9	103.1	124.6	157.3	183.3
35°	77.1	87.3	110.1	144.6	172.8
37.5°	61.2	71.1	96.1	132.6	162.6
40°	45.7	55.9	81.6	120.7	152.0
42.5°	30.6	41.5	67.9	108.4	142.1
45°	16.9	27.1	55.2	97.8	132.3
47.5°	8.8	14.8	43.3	87.3	121.7
50°	6.7	8.1	32.0	75.6	109.8
52.5°	5.6	6.0	21.8	64.0	97.8
55°	4.6	4.9	14.8	53.8	85.5
57.5°	3.5	3.9	10.6	44.0	71.8
60°	2.8	3.2	8.8	33.8	59.1
62.5°	2.1	2.5	8.4	25.0	46.4
65°	1.8	2.1	7.4	16.9	34.1
67.5°	1.4	2.1	6.3	10.9	22.9
70°	1.4	2.8	5.3	7.0	12.7
72.5°	1.4	3.2	4.6	4.6	4.6
75°	1.4	3.9	4.2	3.9	3.9
77.5°	1.4	3.5	3.5	3.5	3.5
80°	1.4	3.2	3.2	3.2	2.8
82.5°	1.4	2.8	3.2	3.2	2.5
85°	1.4	2.8	2.8	2.8	2.1
87.5°	1.1	2.8	2.8	2.8	1.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060841  
 CATALOG NUMBER: S124RDRP-H350D935-X4F0-XX-UDD-BVL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	11.32	12.60	11.69	12.91	13.22
	3H	0.00	0.00	0.00	0.00	0.00	11.68	12.80	12.06	13.13	13.50
	4H	0.00	0.00	0.00	0.00	0.00	11.64	12.69	12.05	13.04	13.43
	6H	0.00	0.00	0.00	0.00	0.00	11.62	12.58	12.03	12.95	13.34
	8H	0.00	0.00	0.00	0.00	0.00	11.61	12.52	12.04	12.91	13.31
	12H	0.00	0.00	0.00	0.31	0.74	11.60	12.48	12.04	12.86	13.29
4H	2H	0.00	0.00	0.00	0.00	0.00	11.12	12.17	11.53	12.52	12.91
	3H	0.00	0.00	0.00	0.00	0.11	11.52	12.37	11.93	12.78	13.18
	4H	0.00	0.67	0.34	1.09	1.54	11.50	12.26	11.93	12.68	13.13
	6H	1.15	1.81	1.61	2.25	2.72	11.52	12.18	11.98	12.62	13.09
	8H	1.71	2.33	2.18	2.77	3.24	11.53	12.14	12.00	12.59	13.06
	12H	2.38	2.92	2.86	3.40	3.88	11.56	12.11	12.05	12.59	13.07
8H	4H	0.97	1.59	1.44	2.04	2.51	11.40	12.01	11.87	12.46	12.93
	6H	2.59	3.09	3.09	3.59	4.07	11.45	11.95	11.95	12.45	12.93
	8H	3.41	3.87	3.94	4.38	4.88	11.51	11.96	12.03	12.48	12.97
	12H	4.37	4.77	4.89	5.26	5.84	11.62	12.02	12.14	12.52	13.09
12H	4H	1.16	1.71	1.65	2.19	2.67	11.36	11.90	11.85	12.39	12.86
	6H	2.94	3.39	3.46	3.91	4.40	11.42	11.87	11.94	12.39	12.88
	8H	3.95	4.35	4.47	4.85	5.42	11.52	11.92	12.04	12.42	12.99