

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996553

Luminaire Tested: S124DRP-B575DB50-4F0-XX-W2A-A

Issue Date: 5/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P996553  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124DRP-B575DB50-4F0-XX-W2A-A  
Description: Define 4 Direct Perimeter with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2482.0 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 24  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

### Luminous Intensity Polar Plot



TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 109 | 105 | 101 | 97  | 107 | 103 | 99  | 96  | 98  | 95  | 93  |  | 95  | 92  | 90  |  | 91  | 89  | 87  | 85  |
| 2   | 100 | 92  | 86  | 80  | 98  | 90  | 84  | 79  | 87  | 82  | 78  |  | 84  | 79  | 76  |  | 81  | 77  | 74  | 72  |
| 3   | 92  | 82  | 74  | 68  | 89  | 80  | 73  | 67  | 77  | 71  | 66  |  | 74  | 69  | 65  |  | 72  | 67  | 64  | 62  |
| 4   | 84  | 73  | 64  | 58  | 82  | 72  | 64  | 58  | 69  | 62  | 57  |  | 67  | 61  | 56  |  | 65  | 60  | 55  | 53  |
| 5   | 78  | 65  | 57  | 50  | 76  | 64  | 56  | 50  | 62  | 55  | 50  |  | 60  | 54  | 49  |  | 58  | 53  | 49  | 46  |
| 6   | 72  | 59  | 51  | 44  | 70  | 58  | 50  | 44  | 56  | 49  | 44  |  | 55  | 48  | 43  |  | 53  | 47  | 43  | 41  |
| 7   | 67  | 54  | 45  | 39  | 65  | 53  | 45  | 39  | 52  | 44  | 39  |  | 50  | 44  | 39  |  | 49  | 43  | 38  | 36  |
| 8   | 62  | 49  | 41  | 35  | 61  | 49  | 41  | 35  | 47  | 40  | 35  |  | 46  | 40  | 35  |  | 45  | 39  | 35  | 33  |
| 9   | 58  | 45  | 37  | 32  | 57  | 45  | 37  | 32  | 44  | 37  | 32  |  | 43  | 36  | 32  |  | 42  | 36  | 31  | 30  |
| 10  | 55  | 42  | 34  | 29  | 54  | 41  | 34  | 29  | 40  | 34  | 29  |  | 39  | 33  | 29  |  | 39  | 33  | 29  | 27  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 90°   | 180° | 270° |
|-----|------|-------|------|------|
| 0°  | 7335 | 7335  | 7335 | 7335 |
| 5°  | 7332 | 8637  | 7375 | 6490 |
| 10° | 7293 | 10342 | 7349 | 5843 |
| 15° | 7222 | 12236 | 7273 | 5367 |
| 20° | 7146 | 13625 | 7197 | 4940 |
| 25° | 7027 | 13845 | 7094 | 4646 |
| 30° | 6911 | 11781 | 6996 | 4554 |
| 35° | 6743 | 9058  | 6817 | 4555 |
| 40° | 6544 | 7060  | 6608 | 4640 |
| 45° | 6231 | 5887  | 6308 | 4718 |
| 50° | 5852 | 5181  | 5937 | 4878 |
| 55° | 5404 | 4747  | 5488 | 5075 |
| 60° | 4971 | 4447  | 5116 | 5312 |
| 65° | 4573 | 4141  | 4615 | 5507 |
| 70° | 4103 | 3784  | 4194 | 5632 |
| 75° | 3664 | 3381  | 3639 | 5564 |
| 80° | 3010 | 2836  | 2973 | 5391 |
| 85° | 2227 | 2096  | 2096 | 5155 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 11327 cd/sqm

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 87.5   | 3.5       |
| 10°-20°   | 270.2  | 10.9      |
| 20°-30°   | 429.2  | 17.3      |
| 30°-40°   | 477.0  | 19.2      |
| 40°-50°   | 433.7  | 17.5      |
| 50°-60°   | 354.5  | 14.3      |
| 60°-70°   | 253.0  | 10.2      |
| 70°-80°   | 139.2  | 5.6       |
| 80°-90°   | 37.6   | 1.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 787.0  | 31.7      |
| 0°-40°    | 1263.9 | 50.9      |
| 0°-60°    | 2052.1 | 82.7      |
| 0°-90°    | 2482.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2482.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 90°  | 180° | 270° | 360° | Flux |
|-----|-----|------|------|------|------|------|
| 0°  | 900 | 900  | 900  | 900  | 900  |      |
| 5°  | 896 | 1055 | 901  | 793  | 896  | 85   |
| 15° | 856 | 1449 | 862  | 636  | 856  | 241  |
| 25° | 781 | 1539 | 788  | 516  | 781  | 360  |
| 35° | 677 | 910  | 685  | 458  | 677  | 423  |
| 45° | 540 | 510  | 547  | 409  | 540  | 417  |
| 55° | 380 | 334  | 386  | 357  | 380  | 342  |
| 65° | 237 | 215  | 239  | 285  | 237  | 234  |
| 75° | 116 | 107  | 116  | 177  | 116  | 122  |
| 85° | 24  | 22   | 22   | 55   | 24   | 29   |
| 90° | 0   | 0    | 0    | 0    | 0    |      |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°    | 10°   | 15°   | 20°    | 22.5°  | 25°    | 30°    | 35°    | 40°    | 45°    |
|-------|-------|-------|-------|-------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 899.5 | 899.5 | 899.5 | 899.5 | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  |
| 2.5°  | 899.5 | 908.4 | 912.1 | 915.1 | 924.8  | 927.8  | 928.5  | 933.0  | 936.7  | 937.5  | 937.5  |
| 5°    | 895.7 | 909.9 | 921.1 | 931.5 | 947.2  | 953.9  | 962.1  | 971.0  | 982.9  | 990.4  | 994.1  |
| 7.5°  | 889.8 | 910.6 | 927.8 | 945.7 | 967.3  | 980.7  | 988.1  | 1012.0 | 1028.4 | 1041.8 | 1058.2 |
| 10°   | 880.8 | 907.7 | 932.3 | 958.3 | 988.9  | 1005.3 | 1021.7 | 1050.7 | 1073.8 | 1099.9 | 1120.8 |
| 12.5° | 867.4 | 902.4 | 932.3 | 968.8 | 1006.8 | 1026.1 | 1045.5 | 1096.2 | 1123.0 | 1146.1 | 1183.4 |
| 15°   | 855.5 | 890.5 | 933.0 | 970.3 | 1017.2 | 1046.3 | 1074.6 | 1107.4 | 1149.9 | 1199.8 | 1235.5 |
| 17.5° | 842.1 | 886.0 | 925.5 | 977.7 | 1029.9 | 1057.4 | 1080.5 | 1131.2 | 1190.8 | 1240.0 | 1272.8 |
| 20°   | 823.5 | 868.2 | 920.3 | 975.5 | 1037.3 | 1058.9 | 1089.5 | 1157.3 | 1211.0 | 1259.4 | 1313.1 |
| 22.5° | 801.8 | 854.0 | 909.1 | 962.1 | 1026.1 | 1071.6 | 1105.1 | 1164.8 | 1229.6 | 1285.5 | 1345.8 |
| 25°   | 781.0 | 837.6 | 886.0 | 958.3 | 1026.1 | 1056.7 | 1094.7 | 1165.5 | 1236.3 | 1304.1 | 1366.0 |
| 27.5° | 758.6 | 811.5 | 877.1 | 934.5 | 1011.2 | 1044.8 | 1085.8 | 1163.3 | 1238.5 | 1306.3 | 1372.7 |
| 30°   | 734.0 | 790.7 | 845.1 | 912.9 | 987.4  | 1030.6 | 1068.6 | 1152.8 | 1229.6 | 1300.4 | 1362.2 |
| 32.5° | 706.5 | 760.1 | 818.2 | 882.3 | 960.6  | 1004.5 | 1052.2 | 1138.7 | 1220.6 | 1281.8 | 1329.4 |
| 35°   | 677.4 | 731.8 | 782.5 | 848.0 | 928.5  | 972.5  | 1018.7 | 1114.1 | 1195.3 | 1245.2 | 1272.8 |
| 37.5° | 645.3 | 696.8 | 746.7 | 811.5 | 892.0  | 939.0  | 985.9  | 1078.3 | 1155.1 | 1196.8 | 1189.3 |
| 40°   | 614.8 | 661.0 | 707.2 | 768.3 | 852.5  | 902.4  | 943.4  | 1036.6 | 1103.6 | 1121.5 | 1096.9 |
| 42.5° | 579.8 | 619.3 | 664.0 | 726.6 | 808.5  | 855.5  | 906.9  | 991.9  | 1041.8 | 1034.3 | 992.6  |
| 45°   | 540.3 | 575.3 | 620.0 | 678.9 | 762.3  | 810.8  | 854.0  | 934.5  | 971.0  | 952.4  | 876.4  |
| 47.5° | 502.3 | 536.5 | 573.1 | 631.9 | 713.2  | 754.1  | 798.1  | 870.4  | 891.3  | 851.8  | 775.8  |
| 50°   | 461.3 | 489.6 | 527.6 | 583.5 | 659.5  | 702.7  | 739.2  | 797.4  | 804.8  | 756.4  | 677.4  |
| 52.5° | 421.8 | 445.6 | 482.1 | 537.3 | 608.1  | 642.4  | 678.1  | 729.6  | 723.6  | 673.7  | 597.7  |
| 55°   | 380.1 | 402.4 | 435.9 | 486.6 | 549.2  | 582.0  | 612.6  | 658.0  | 645.3  | 593.9  | 527.6  |
| 57.5° | 345.0 | 360.7 | 393.5 | 440.4 | 491.8  | 527.6  | 553.7  | 589.5  | 570.1  | 518.7  | 456.8  |
| 60°   | 304.8 | 324.2 | 351.7 | 389.7 | 440.4  | 464.3  | 487.4  | 511.2  | 497.8  | 448.6  | 393.5  |
| 62.5° | 268.3 | 283.2 | 307.0 | 343.5 | 383.0  | 404.6  | 429.2  | 444.1  | 430.7  | 385.3  | 339.1  |
| 65°   | 237.0 | 248.9 | 267.5 | 297.3 | 335.3  | 353.2  | 367.4  | 381.5  | 370.4  | 327.9  | 294.4  |
| 67.5° | 202.7 | 213.1 | 228.8 | 252.6 | 284.7  | 297.3  | 310.8  | 320.4  | 307.8  | 279.5  | 246.7  |
| 70°   | 172.1 | 179.6 | 194.5 | 212.4 | 234.7  | 246.7  | 257.8  | 267.5  | 256.4  | 232.5  | 207.9  |
| 72.5° | 140.8 | 146.8 | 160.2 | 172.9 | 193.0  | 201.2  | 209.4  | 216.9  | 213.1  | 190.8  | 170.7  |
| 75°   | 116.3 | 118.5 | 127.4 | 137.9 | 150.5  | 159.5  | 165.4  | 169.9  | 166.9  | 149.0  | 136.4  |
| 77.5° | 87.9  | 90.9  | 97.6  | 105.8 | 117.0  | 122.2  | 125.9  | 130.4  | 126.7  | 112.5  | 103.6  |
| 80°   | 64.1  | 64.8  | 68.6  | 76.0  | 83.5   | 84.2   | 87.9   | 93.9   | 91.7   | 82.0   | 75.3   |
| 82.5° | 41.0  | 43.2  | 44.7  | 49.2  | 54.4   | 55.9   | 58.1   | 59.6   | 58.9   | 52.9   | 50.7   |
| 85°   | 23.8  | 23.8  | 25.3  | 28.3  | 29.8   | 32.0   | 32.8   | 33.5   | 35.0   | 31.3   | 29.1   |
| 87.5° | 10.4  | 11.2  | 11.2  | 11.9  | 13.4   | 13.4   | 14.2   | 14.9   | 15.6   | 14.9   | 12.7   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 50°    | 55°    | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  |
| 2.5°  | 939.7  | 953.1  | 959.1  | 960.6  | 968.8  | 963.5  | 965.8  | 965.0  | 971.0  | 971.7  | 971.7  |
| 5°    | 1008.3 | 1023.9 | 1029.1 | 1036.6 | 1047.8 | 1050.7 | 1048.5 | 1053.0 | 1061.2 | 1055.2 | 1064.2 |
| 7.5°  | 1080.5 | 1097.7 | 1109.6 | 1126.0 | 1129.7 | 1139.4 | 1145.4 | 1150.6 | 1152.1 | 1152.8 | 1154.3 |
| 10°   | 1147.6 | 1169.2 | 1185.6 | 1213.2 | 1219.2 | 1224.4 | 1250.5 | 1240.0 | 1253.4 | 1249.0 | 1250.5 |
| 12.5° | 1202.0 | 1244.5 | 1257.9 | 1304.1 | 1308.6 | 1326.5 | 1325.0 | 1341.4 | 1344.3 | 1350.3 | 1344.3 |
| 15°   | 1273.6 | 1322.7 | 1344.3 | 1370.4 | 1385.3 | 1406.2 | 1409.9 | 1432.3 | 1441.2 | 1449.4 | 1441.2 |
| 17.5° | 1339.1 | 1365.2 | 1420.4 | 1441.2 | 1450.9 | 1462.1 | 1490.4 | 1498.6 | 1512.0 | 1506.8 | 1521.7 |
| 20°   | 1371.9 | 1409.2 | 1467.3 | 1503.1 | 1518.0 | 1528.4 | 1552.3 | 1564.9 | 1570.1 | 1570.1 | 1571.6 |
| 22.5° | 1401.0 | 1454.6 | 1497.9 | 1538.8 | 1552.3 | 1559.7 | 1573.9 | 1583.6 | 1585.8 | 1587.3 | 1588.8 |
| 25°   | 1427.1 | 1475.5 | 1510.5 | 1533.6 | 1538.8 | 1538.8 | 1547.0 | 1541.1 | 1531.4 | 1538.8 | 1543.3 |
| 27.5° | 1427.1 | 1461.3 | 1477.0 | 1485.2 | 1485.2 | 1465.1 | 1453.1 | 1428.6 | 1407.7 | 1401.7 | 1415.1 |
| 30°   | 1403.2 | 1418.9 | 1397.3 | 1377.1 | 1361.5 | 1348.1 | 1301.1 | 1263.9 | 1256.4 | 1251.2 | 1271.3 |
| 32.5° | 1348.1 | 1328.0 | 1285.5 | 1227.4 | 1204.3 | 1173.7 | 1137.2 | 1108.9 | 1091.7 | 1085.8 | 1081.3 |
| 35°   | 1250.5 | 1198.3 | 1143.1 | 1064.9 | 1048.5 | 1009.8 | 959.8  | 939.0  | 910.6  | 909.9  | 919.6  |
| 37.5° | 1143.9 | 1063.4 | 1003.8 | 929.3  | 906.2  | 865.2  | 818.2  | 796.6  | 777.2  | 762.3  | 780.2  |
| 40°   | 1019.4 | 949.4  | 858.5  | 797.4  | 764.6  | 743.0  | 703.5  | 679.6  | 670.7  | 663.2  | 674.4  |
| 42.5° | 903.2  | 826.4  | 755.6  | 693.0  | 666.2  | 641.6  | 615.5  | 592.4  | 585.7  | 585.0  | 593.2  |
| 45°   | 787.7  | 712.4  | 646.8  | 593.2  | 576.0  | 561.1  | 535.8  | 529.1  | 517.9  | 510.5  | 514.2  |
| 47.5° | 695.3  | 617.8  | 563.4  | 522.4  | 507.5  | 494.8  | 478.4  | 467.2  | 457.6  | 454.6  | 459.0  |
| 50°   | 604.4  | 552.2  | 496.3  | 462.0  | 450.8  | 438.9  | 426.3  | 415.8  | 411.4  | 408.4  | 411.4  |
| 52.5° | 531.3  | 475.4  | 437.4  | 409.9  | 398.7  | 389.7  | 380.8  | 376.3  | 370.4  | 371.9  | 374.8  |
| 55°   | 465.8  | 416.6  | 384.5  | 364.4  | 357.7  | 354.0  | 342.8  | 337.6  | 335.3  | 333.9  | 335.3  |
| 57.5° | 403.9  | 368.1  | 344.3  | 327.1  | 318.2  | 316.0  | 307.0  | 307.0  | 304.8  | 302.6  | 303.3  |
| 60°   | 354.7  | 324.2  | 301.1  | 287.6  | 286.2  | 282.4  | 276.5  | 275.7  | 270.5  | 272.7  | 273.5  |
| 62.5° | 304.8  | 280.2  | 264.5  | 256.4  | 251.1  | 249.6  | 245.9  | 245.2  | 242.9  | 243.7  | 242.2  |
| 65°   | 265.3  | 245.2  | 229.5  | 222.8  | 220.6  | 219.8  | 216.9  | 214.6  | 213.1  | 214.6  | 213.1  |
| 67.5° | 225.8  | 212.4  | 200.5  | 193.8  | 190.8  | 190.0  | 187.8  | 186.3  | 187.0  | 184.8  | 186.3  |
| 70°   | 188.5  | 175.1  | 167.7  | 163.9  | 162.5  | 160.2  | 160.2  | 160.2  | 160.2  | 158.7  | 158.0  |
| 72.5° | 158.7  | 145.3  | 140.1  | 137.9  | 136.4  | 135.6  | 133.4  | 134.1  | 133.4  | 132.6  | 135.6  |
| 75°   | 125.9  | 117.7  | 112.5  | 110.3  | 111.8  | 109.5  | 107.3  | 108.8  | 106.6  | 107.3  | 110.3  |
| 77.5° | 95.4   | 91.7   | 88.7   | 87.2   | 85.7   | 84.2   | 84.2   | 82.7   | 82.7   | 82.7   | 82.7   |
| 80°   | 69.3   | 68.6   | 63.3   | 62.6   | 62.6   | 61.1   | 61.1   | 61.1   | 61.1   | 60.4   | 61.1   |
| 82.5° | 46.2   | 45.5   | 44.0   | 43.2   | 41.7   | 42.5   | 42.5   | 41.0   | 41.0   | 40.2   | 41.0   |
| 85°   | 26.8   | 26.8   | 25.3   | 24.6   | 23.8   | 24.6   | 23.1   | 22.4   | 23.1   | 22.4   | 23.1   |
| 87.5° | 12.7   | 11.2   | 11.9   | 11.2   | 9.7    | 10.4   | 8.9    | 9.7    | 8.9    | 8.2    | 9.7    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  | 899.5  |
| 2.5°  | 970.3  | 968.0  | 965.0  | 965.0  | 961.3  | 961.3  | 955.4  | 944.9  | 936.0  | 933.0  | 934.5  |
| 5°    | 1053.0 | 1053.7 | 1049.2 | 1045.5 | 1038.8 | 1033.6 | 1023.9 | 1005.3 | 999.3  | 987.4  | 979.2  |
| 7.5°  | 1147.6 | 1144.6 | 1136.4 | 1130.5 | 1129.0 | 1117.1 | 1096.2 | 1073.8 | 1056.0 | 1044.0 | 1026.9 |
| 10°   | 1254.2 | 1242.3 | 1230.3 | 1226.6 | 1217.7 | 1197.5 | 1173.7 | 1149.1 | 1124.5 | 1098.4 | 1069.4 |
| 12.5° | 1343.6 | 1320.5 | 1319.8 | 1310.8 | 1293.7 | 1282.5 | 1254.2 | 1219.2 | 1176.7 | 1147.6 | 1114.8 |
| 15°   | 1439.7 | 1418.1 | 1400.2 | 1383.8 | 1375.6 | 1342.9 | 1319.0 | 1275.0 | 1224.4 | 1193.1 | 1170.7 |
| 17.5° | 1508.3 | 1498.6 | 1468.1 | 1460.6 | 1449.4 | 1411.4 | 1373.4 | 1330.2 | 1286.2 | 1242.3 | 1181.9 |
| 20°   | 1563.4 | 1557.5 | 1537.4 | 1526.9 | 1509.0 | 1479.2 | 1433.0 | 1383.1 | 1332.4 | 1269.8 | 1213.2 |
| 22.5° | 1587.3 | 1579.8 | 1563.4 | 1554.5 | 1543.3 | 1518.0 | 1478.5 | 1421.9 | 1355.5 | 1299.6 | 1239.3 |
| 25°   | 1540.3 | 1553.8 | 1549.3 | 1545.6 | 1541.1 | 1526.2 | 1496.4 | 1446.4 | 1381.6 | 1318.3 | 1243.0 |
| 27.5° | 1434.5 | 1457.6 | 1480.0 | 1483.0 | 1490.4 | 1496.4 | 1484.4 | 1448.7 | 1394.3 | 1327.2 | 1244.5 |
| 30°   | 1292.2 | 1302.6 | 1348.1 | 1361.5 | 1371.9 | 1409.9 | 1432.3 | 1423.3 | 1381.6 | 1321.2 | 1245.2 |
| 32.5° | 1109.6 | 1137.2 | 1183.4 | 1215.4 | 1243.7 | 1286.2 | 1344.3 | 1367.5 | 1352.5 | 1303.4 | 1228.1 |
| 35°   | 936.7  | 969.5  | 1023.2 | 1064.2 | 1092.5 | 1152.8 | 1221.4 | 1271.3 | 1289.9 | 1265.4 | 1198.3 |
| 37.5° | 795.1  | 834.6  | 882.3  | 898.0  | 930.8  | 1005.3 | 1099.9 | 1169.2 | 1214.7 | 1216.9 | 1164.8 |
| 40°   | 688.6  | 708.7  | 746.7  | 770.5  | 802.6  | 865.2  | 957.6  | 1049.2 | 1117.8 | 1140.9 | 1113.3 |
| 42.5° | 598.4  | 614.0  | 642.4  | 671.4  | 700.5  | 748.2  | 833.1  | 918.8  | 1011.2 | 1057.4 | 1056.7 |
| 45°   | 526.9  | 543.3  | 562.6  | 586.5  | 606.6  | 658.0  | 725.1  | 813.0  | 892.8  | 964.3  | 982.2  |
| 47.5° | 464.3  | 478.4  | 502.3  | 512.7  | 526.1  | 574.6  | 632.7  | 714.7  | 797.4  | 879.3  | 900.2  |
| 50°   | 418.1  | 430.0  | 446.4  | 453.1  | 468.0  | 503.8  | 551.5  | 617.8  | 709.4  | 784.7  | 823.5  |
| 52.5° | 376.3  | 385.3  | 397.9  | 403.2  | 413.6  | 440.4  | 483.6  | 535.8  | 611.8  | 689.3  | 743.7  |
| 55°   | 340.6  | 346.5  | 355.5  | 361.4  | 368.9  | 392.7  | 424.8  | 471.7  | 537.3  | 604.4  | 657.3  |
| 57.5° | 307.0  | 311.5  | 320.4  | 323.4  | 329.4  | 348.0  | 370.4  | 409.9  | 470.2  | 529.8  | 581.3  |
| 60°   | 275.7  | 278.7  | 283.9  | 290.6  | 295.1  | 307.8  | 328.6  | 361.4  | 409.9  | 464.3  | 506.0  |
| 62.5° | 245.9  | 250.4  | 251.9  | 254.9  | 258.6  | 270.5  | 286.9  | 310.8  | 353.2  | 397.9  | 441.9  |
| 65°   | 215.4  | 219.1  | 222.1  | 222.8  | 226.5  | 235.5  | 250.4  | 271.3  | 298.8  | 337.6  | 378.6  |
| 67.5° | 187.0  | 189.3  | 190.8  | 193.8  | 197.5  | 202.0  | 213.9  | 229.5  | 254.9  | 286.2  | 318.9  |
| 70°   | 161.0  | 161.0  | 163.2  | 163.9  | 168.4  | 173.6  | 178.8  | 193.8  | 216.1  | 241.4  | 263.8  |
| 72.5° | 132.6  | 136.4  | 135.6  | 139.4  | 138.6  | 142.3  | 149.0  | 158.7  | 175.1  | 195.2  | 216.9  |
| 75°   | 108.1  | 110.3  | 110.3  | 110.3  | 111.8  | 114.8  | 118.5  | 127.4  | 140.1  | 156.5  | 169.2  |
| 77.5° | 84.2   | 85.7   | 85.7   | 85.7   | 86.4   | 89.4   | 93.2   | 99.1   | 108.1  | 117.7  | 125.2  |
| 80°   | 60.4   | 61.9   | 61.9   | 63.3   | 63.3   | 64.1   | 67.8   | 70.8   | 75.3   | 82.7   | 90.2   |
| 82.5° | 41.0   | 41.7   | 43.2   | 43.2   | 42.5   | 44.0   | 44.7   | 47.7   | 52.2   | 53.7   | 58.9   |
| 85°   | 22.4   | 23.1   | 23.8   | 23.8   | 24.6   | 26.1   | 25.3   | 28.3   | 28.3   | 31.3   | 32.8   |
| 87.5° | 8.9    | 10.4   | 10.4   | 9.7    | 10.4   | 10.4   | 10.4   | 11.9   | 12.7   | 13.4   | 12.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 150°   | 155°   | 157.5° | 160°   | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|-------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 899.5  | 899.5  | 899.5  | 899.5  | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 |
| 2.5°  | 927.8  | 924.8  | 922.6  | 922.6  | 915.9 | 909.1 | 905.4 | 903.9 | 902.4 | 896.5 | 888.3 |
| 5°    | 965.8  | 956.1  | 949.4  | 942.7  | 931.5 | 919.6 | 907.7 | 901.0 | 891.3 | 877.9 | 868.2 |
| 7.5°  | 1008.3 | 985.2  | 977.7  | 969.5  | 947.2 | 927.0 | 910.6 | 896.5 | 880.8 | 863.7 | 846.6 |
| 10°   | 1044.0 | 1019.4 | 1003.0 | 988.9  | 959.8 | 933.0 | 908.4 | 887.5 | 867.4 | 845.1 | 824.2 |
| 12.5° | 1078.3 | 1043.3 | 1026.1 | 1005.3 | 974.7 | 936.0 | 903.9 | 877.9 | 848.0 | 824.9 | 799.6 |
| 15°   | 1126.0 | 1067.1 | 1038.8 | 1025.4 | 984.4 | 939.0 | 900.2 | 861.5 | 836.9 | 801.8 | 779.5 |
| 17.5° | 1133.5 | 1085.8 | 1067.1 | 1032.9 | 983.7 | 932.3 | 887.5 | 848.8 | 811.5 | 780.2 | 751.2 |
| 20°   | 1159.5 | 1096.9 | 1067.1 | 1045.5 | 980.7 | 928.5 | 879.3 | 829.4 | 793.6 | 760.1 | 727.3 |
| 22.5° | 1175.9 | 1105.1 | 1073.8 | 1039.6 | 977.7 | 915.1 | 857.0 | 813.8 | 769.8 | 735.5 | 709.4 |
| 25°   | 1171.5 | 1100.7 | 1065.6 | 1033.6 | 958.3 | 895.7 | 843.6 | 788.4 | 747.4 | 710.2 | 675.9 |
| 27.5° | 1169.2 | 1089.5 | 1052.2 | 1016.5 | 945.7 | 880.1 | 814.5 | 769.8 | 724.3 | 681.1 | 655.8 |
| 30°   | 1163.3 | 1075.3 | 1032.1 | 993.4  | 919.6 | 851.0 | 795.1 | 743.0 | 697.5 | 658.0 | 624.5 |
| 32.5° | 1143.1 | 1051.5 | 1009.8 | 968.0  | 891.3 | 822.7 | 766.1 | 717.6 | 672.2 | 631.2 | 599.1 |
| 35°   | 1116.3 | 1023.2 | 977.7  | 933.7  | 857.0 | 787.7 | 735.5 | 684.8 | 642.4 | 602.9 | 572.3 |
| 37.5° | 1089.5 | 990.4  | 947.9  | 897.2  | 826.4 | 754.1 | 700.5 | 655.0 | 615.5 | 574.6 | 541.0 |
| 40°   | 1050.7 | 951.6  | 904.7  | 861.5  | 778.7 | 710.9 | 661.7 | 620.8 | 582.0 | 543.3 | 514.9 |
| 42.5° | 997.8  | 909.1  | 860.7  | 813.0  | 735.5 | 668.4 | 620.8 | 584.2 | 547.7 | 515.7 | 484.4 |
| 45°   | 944.2  | 857.7  | 814.5  | 772.0  | 687.8 | 624.5 | 580.5 | 547.0 | 516.4 | 481.4 | 456.1 |
| 47.5° | 879.3  | 806.3  | 763.1  | 721.4  | 641.6 | 578.3 | 538.0 | 506.7 | 478.4 | 449.4 | 425.5 |
| 50°   | 813.0  | 749.7  | 710.2  | 667.0  | 590.9 | 533.6 | 494.1 | 468.0 | 444.9 | 417.3 | 397.9 |
| 52.5° | 741.5  | 686.3  | 652.8  | 611.1  | 544.0 | 491.1 | 450.8 | 424.8 | 405.4 | 385.3 | 368.1 |
| 55°   | 665.5  | 625.2  | 589.5  | 555.9  | 492.6 | 444.9 | 409.1 | 386.0 | 372.6 | 354.0 | 339.1 |
| 57.5° | 596.9  | 558.2  | 536.5  | 498.5  | 443.4 | 396.4 | 368.1 | 348.8 | 333.1 | 321.9 | 310.0 |
| 60°   | 525.4  | 494.1  | 470.2  | 442.7  | 394.2 | 354.7 | 324.9 | 313.7 | 297.3 | 289.1 | 283.9 |
| 62.5° | 456.8  | 434.5  | 412.1  | 391.2  | 348.0 | 310.8 | 288.4 | 274.2 | 264.5 | 256.4 | 251.9 |
| 65°   | 392.0  | 371.1  | 355.5  | 336.8  | 301.1 | 271.3 | 250.4 | 239.2 | 229.5 | 227.3 | 222.1 |
| 67.5° | 328.6  | 319.7  | 302.6  | 287.6  | 257.1 | 234.0 | 218.3 | 204.2 | 199.0 | 196.7 | 192.3 |
| 70°   | 275.0  | 264.5  | 251.1  | 238.5  | 215.4 | 195.2 | 181.1 | 175.9 | 168.4 | 167.7 | 162.5 |
| 72.5° | 226.5  | 213.9  | 204.2  | 194.5  | 177.4 | 159.5 | 152.0 | 144.6 | 140.8 | 137.9 | 135.6 |
| 75°   | 179.6  | 170.7  | 163.9  | 155.7  | 140.8 | 128.9 | 118.5 | 115.5 | 113.3 | 112.5 | 111.0 |
| 77.5° | 134.1  | 128.2  | 125.2  | 117.0  | 106.6 | 96.1  | 91.7  | 87.2  | 87.2  | 85.7  | 86.4  |
| 80°   | 95.4   | 91.7   | 87.9   | 83.5   | 74.5  | 70.0  | 66.3  | 63.3  | 61.9  | 61.1  | 61.9  |
| 82.5° | 60.4   | 58.1   | 57.4   | 54.4   | 48.4  | 46.2  | 43.2  | 41.0  | 41.0  | 41.0  | 41.0  |
| 85°   | 33.5   | 33.5   | 33.5   | 29.1   | 26.8  | 24.6  | 23.1  | 22.4  | 22.4  | 22.4  | 23.1  |
| 87.5° | 14.2   | 14.2   | 11.9   | 11.9   | 11.2  | 9.7   | 8.9   | 8.9   | 9.7   | 9.7   | 10.4  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°  | 245°  |
|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 899.5 | 899.5  | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 |
| 2.5°  | 886.0 | 883.1  | 884.6 | 877.1 | 870.4 | 860.7 | 852.5 | 851.0 | 849.5 | 854.0 | 851.0 |
| 5°    | 860.7 | 857.0  | 853.3 | 844.3 | 830.9 | 822.7 | 810.8 | 810.0 | 805.6 | 798.9 | 800.3 |
| 7.5°  | 833.1 | 830.9  | 825.7 | 811.5 | 799.6 | 785.4 | 775.8 | 767.6 | 763.8 | 757.9 | 755.6 |
| 10°   | 810.8 | 802.6  | 798.1 | 782.5 | 768.3 | 753.4 | 740.7 | 734.8 | 728.1 | 722.8 | 719.1 |
| 12.5° | 780.2 | 778.0  | 765.3 | 752.7 | 740.7 | 723.6 | 713.9 | 696.8 | 687.8 | 692.3 | 690.8 |
| 15°   | 760.1 | 749.7  | 746.7 | 728.8 | 708.7 | 697.5 | 679.6 | 668.4 | 664.7 | 658.0 | 649.8 |
| 17.5° | 733.3 | 726.6  | 716.1 | 699.7 | 676.6 | 661.0 | 648.3 | 637.9 | 633.4 | 624.5 | 617.8 |
| 20°   | 707.9 | 696.8  | 688.6 | 673.7 | 651.3 | 631.2 | 615.5 | 608.8 | 597.7 | 590.2 | 586.5 |
| 22.5° | 684.8 | 676.6  | 664.7 | 642.4 | 623.0 | 603.6 | 585.0 | 575.3 | 564.9 | 560.4 | 554.4 |
| 25°   | 656.5 | 643.1  | 634.9 | 610.3 | 589.5 | 573.8 | 556.7 | 544.0 | 538.0 | 530.6 | 529.1 |
| 27.5° | 629.0 | 616.3  | 606.6 | 585.0 | 559.6 | 539.5 | 529.1 | 520.2 | 509.7 | 509.7 | 506.0 |
| 30°   | 601.4 | 592.4  | 577.5 | 556.7 | 532.8 | 513.4 | 501.5 | 493.3 | 489.6 | 486.6 | 485.9 |
| 32.5° | 573.8 | 561.9  | 552.9 | 524.6 | 506.7 | 488.9 | 479.9 | 473.2 | 468.7 | 468.0 | 468.7 |
| 35°   | 545.5 | 532.1  | 523.1 | 497.8 | 479.9 | 463.5 | 459.8 | 453.8 | 451.6 | 450.8 | 454.6 |
| 37.5° | 515.7 | 505.2  | 494.1 | 473.2 | 453.1 | 443.4 | 435.9 | 433.7 | 433.0 | 437.4 | 438.9 |
| 40°   | 488.1 | 479.2  | 468.7 | 446.4 | 431.5 | 421.0 | 417.3 | 415.1 | 418.1 | 422.5 | 424.8 |
| 42.5° | 462.0 | 449.4  | 441.2 | 421.0 | 407.6 | 401.7 | 397.2 | 397.2 | 400.2 | 405.4 | 409.1 |
| 45°   | 434.5 | 424.8  | 416.6 | 398.7 | 386.8 | 380.1 | 379.3 | 380.1 | 383.8 | 387.5 | 392.0 |
| 47.5° | 407.6 | 397.9  | 389.0 | 374.1 | 363.7 | 359.9 | 359.2 | 359.9 | 365.9 | 371.1 | 376.3 |
| 50°   | 383.0 | 372.6  | 364.4 | 350.2 | 342.0 | 337.6 | 338.3 | 342.0 | 346.5 | 354.0 | 360.7 |
| 52.5° | 354.0 | 346.5  | 339.1 | 326.4 | 318.9 | 316.0 | 318.2 | 321.2 | 329.4 | 334.6 | 342.8 |
| 55°   | 325.7 | 318.9  | 313.0 | 303.3 | 297.3 | 295.1 | 296.6 | 301.1 | 307.8 | 316.7 | 326.4 |
| 57.5° | 299.6 | 292.1  | 286.2 | 279.5 | 272.7 | 273.5 | 274.2 | 280.2 | 288.4 | 296.6 | 307.8 |
| 60°   | 270.5 | 266.0  | 260.8 | 252.6 | 249.6 | 249.6 | 251.9 | 258.6 | 266.0 | 279.5 | 289.1 |
| 62.5° | 244.4 | 238.5  | 234.7 | 229.5 | 225.1 | 225.8 | 231.0 | 237.0 | 245.9 | 257.1 | 269.8 |
| 65°   | 217.6 | 210.9  | 207.9 | 203.4 | 202.0 | 202.7 | 206.4 | 215.4 | 225.1 | 234.7 | 246.7 |
| 67.5° | 187.8 | 185.6  | 182.6 | 178.1 | 179.6 | 180.3 | 184.1 | 191.5 | 202.0 | 211.6 | 225.1 |
| 70°   | 162.5 | 158.0  | 157.2 | 153.5 | 153.5 | 155.7 | 163.2 | 168.4 | 178.1 | 188.5 | 202.7 |
| 72.5° | 135.6 | 131.9  | 131.9 | 128.9 | 131.2 | 133.4 | 137.1 | 144.6 | 153.5 | 163.9 | 175.9 |
| 75°   | 108.1 | 106.6  | 108.1 | 106.6 | 106.6 | 110.3 | 114.8 | 120.7 | 130.4 | 141.6 | 151.3 |
| 77.5° | 83.5  | 83.5   | 82.7  | 85.0  | 85.0  | 87.2  | 93.2  | 99.1  | 106.6 | 115.5 | 125.9 |
| 80°   | 61.1  | 61.1   | 61.1  | 63.3  | 65.6  | 65.6  | 69.3  | 76.8  | 83.5  | 89.4  | 99.1  |
| 82.5° | 41.7  | 41.7   | 41.7  | 43.2  | 46.2  | 46.2  | 50.7  | 55.1  | 62.6  | 67.8  | 72.3  |
| 85°   | 25.3  | 25.3   | 24.6  | 26.1  | 26.8  | 29.1  | 32.8  | 35.8  | 39.5  | 44.0  | 48.4  |
| 87.5° | 11.2  | 11.2   | 11.9  | 12.7  | 13.4  | 14.9  | 16.4  | 17.9  | 21.6  | 23.1  | 25.3  |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 250°  | 255°  | 260°  | 265°  | 270°  | 275°  | 280°  | 285°  | 290°  | 292.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0°    | 899.5  | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5  |
| 2.5°  | 848.8  | 848.0 | 844.3 | 845.8 | 841.3 | 842.8 | 845.1 | 845.8 | 848.8 | 846.6 | 845.8  |
| 5°    | 796.6  | 795.1 | 792.9 | 790.7 | 789.9 | 792.9 | 787.7 | 789.2 | 790.7 | 792.9 | 795.9  |
| 7.5°  | 754.1  | 753.4 | 751.2 | 747.4 | 745.9 | 744.5 | 745.2 | 750.4 | 749.7 | 748.9 | 754.1  |
| 10°   | 715.4  | 716.1 | 711.7 | 710.9 | 706.5 | 705.7 | 706.5 | 707.9 | 710.2 | 713.2 | 713.9  |
| 12.5° | 675.2  | 684.8 | 676.6 | 673.7 | 667.0 | 670.7 | 672.2 | 665.5 | 669.2 | 671.4 | 682.6  |
| 15°   | 649.8  | 645.3 | 640.1 | 640.1 | 637.1 | 635.7 | 631.9 | 637.1 | 640.1 | 644.6 | 643.1  |
| 17.5° | 614.8  | 607.3 | 604.4 | 601.4 | 602.1 | 605.1 | 596.9 | 608.8 | 608.8 | 611.1 | 607.3  |
| 20°   | 584.2  | 578.3 | 574.6 | 573.1 | 570.8 | 569.3 | 568.6 | 571.6 | 576.0 | 577.5 | 581.3  |
| 22.5° | 552.2  | 552.2 | 546.2 | 544.0 | 542.5 | 540.3 | 544.0 | 541.8 | 544.7 | 547.7 | 553.7  |
| 25°   | 525.4  | 525.4 | 523.1 | 520.2 | 517.9 | 516.4 | 518.7 | 517.9 | 520.2 | 523.9 | 525.4  |
| 27.5° | 503.8  | 501.5 | 500.8 | 500.0 | 499.3 | 500.0 | 499.3 | 501.5 | 503.8 | 504.5 | 503.0  |
| 30°   | 485.1  | 482.9 | 483.6 | 483.6 | 484.4 | 483.6 | 482.9 | 485.1 | 485.9 | 484.4 | 485.1  |
| 32.5° | 468.0  | 468.0 | 469.5 | 470.2 | 470.2 | 471.0 | 471.7 | 470.2 | 471.0 | 468.7 | 469.5  |
| 35°   | 453.8  | 455.3 | 456.8 | 457.6 | 458.3 | 457.6 | 459.0 | 458.3 | 456.8 | 455.3 | 454.6  |
| 37.5° | 439.7  | 441.2 | 444.1 | 444.9 | 447.1 | 447.9 | 446.4 | 446.4 | 445.6 | 442.7 | 441.2  |
| 40°   | 424.8  | 426.3 | 430.0 | 432.2 | 433.7 | 435.9 | 434.5 | 434.5 | 431.5 | 428.5 | 426.3  |
| 42.5° | 410.6  | 413.6 | 417.3 | 419.6 | 422.5 | 422.5 | 422.5 | 421.0 | 417.3 | 414.3 | 412.1  |
| 45°   | 396.4  | 397.2 | 402.4 | 406.1 | 409.1 | 409.1 | 409.1 | 406.9 | 404.6 | 398.7 | 395.7  |
| 47.5° | 380.8  | 383.0 | 389.0 | 392.7 | 395.7 | 396.4 | 396.4 | 394.2 | 389.7 | 384.5 | 380.8  |
| 50°   | 363.7  | 367.4 | 374.1 | 379.3 | 383.0 | 384.5 | 382.3 | 380.8 | 375.6 | 369.6 | 365.2  |
| 52.5° | 347.3  | 351.7 | 359.9 | 364.4 | 369.6 | 370.4 | 369.6 | 367.4 | 361.4 | 353.2 | 349.5  |
| 55°   | 330.9  | 334.6 | 343.5 | 351.0 | 355.5 | 357.0 | 355.5 | 351.7 | 344.3 | 336.1 | 332.4  |
| 57.5° | 313.0  | 318.2 | 327.9 | 335.3 | 340.6 | 341.3 | 339.8 | 336.1 | 330.1 | 319.7 | 314.5  |
| 60°   | 294.4  | 301.1 | 310.8 | 318.2 | 324.9 | 325.7 | 324.2 | 318.9 | 311.5 | 301.1 | 296.6  |
| 62.5° | 275.7  | 280.9 | 292.1 | 300.3 | 305.5 | 309.3 | 306.3 | 301.1 | 293.6 | 283.2 | 276.5  |
| 65°   | 254.1  | 261.6 | 271.3 | 278.7 | 284.7 | 285.4 | 283.9 | 279.5 | 271.3 | 260.1 | 254.9  |
| 67.5° | 233.2  | 238.5 | 248.2 | 257.8 | 260.1 | 262.3 | 260.1 | 255.6 | 248.9 | 239.2 | 231.8  |
| 70°   | 207.9  | 212.4 | 224.3 | 231.0 | 234.0 | 236.2 | 234.7 | 230.3 | 224.3 | 215.4 | 209.4  |
| 72.5° | 182.6  | 186.3 | 197.5 | 202.7 | 208.7 | 207.9 | 207.2 | 204.2 | 196.0 | 190.0 | 186.3  |
| 75°   | 155.7  | 160.2 | 167.7 | 174.4 | 176.6 | 176.6 | 176.6 | 174.4 | 169.2 | 159.5 | 155.7  |
| 77.5° | 131.2  | 133.4 | 139.4 | 143.1 | 145.3 | 146.1 | 145.3 | 141.6 | 138.6 | 131.9 | 129.7  |
| 80°   | 100.6  | 106.6 | 111.0 | 111.8 | 114.8 | 114.8 | 114.8 | 113.3 | 110.3 | 103.6 | 102.8  |
| 82.5° | 76.0   | 77.5  | 82.0  | 84.2  | 85.7  | 85.0  | 85.0  | 82.0  | 81.2  | 77.5  | 76.0   |
| 85°   | 51.4   | 53.7  | 52.9  | 55.9  | 56.6  | 55.1  | 55.1  | 56.6  | 52.9  | 53.7  | 51.4   |
| 87.5° | 28.3   | 28.3  | 29.8  | 29.1  | 32.0  | 32.0  | 30.6  | 31.3  | 29.8  | 29.1  | 28.3   |
| 90°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 295°  | 300°  | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0°    | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5 | 899.5  | 899.5 |
| 2.5°  | 845.8 | 850.3 | 845.8 | 848.8 | 850.3 | 854.0 | 855.5 | 862.2 | 864.4 | 869.7  | 869.7 |
| 5°    | 795.1 | 797.4 | 798.1 | 801.1 | 804.1 | 811.5 | 816.7 | 826.4 | 837.6 | 839.1  | 845.8 |
| 7.5°  | 754.1 | 757.9 | 763.8 | 761.6 | 766.8 | 778.0 | 784.7 | 796.6 | 807.8 | 813.8  | 822.0 |
| 10°   | 717.6 | 722.1 | 724.3 | 726.6 | 736.3 | 745.9 | 756.4 | 764.6 | 779.5 | 788.4  | 795.1 |
| 12.5° | 687.8 | 684.1 | 688.6 | 696.8 | 707.9 | 713.9 | 728.1 | 740.7 | 751.9 | 761.6  | 767.6 |
| 15°   | 649.1 | 652.1 | 656.5 | 670.7 | 673.7 | 688.6 | 693.8 | 707.9 | 728.8 | 737.8  | 745.2 |
| 17.5° | 611.8 | 621.5 | 630.4 | 635.7 | 644.6 | 656.5 | 671.4 | 687.1 | 700.5 | 710.9  | 719.9 |
| 20°   | 582.0 | 591.7 | 596.9 | 600.6 | 609.6 | 626.0 | 640.1 | 659.5 | 676.6 | 684.8  | 696.8 |
| 22.5° | 558.2 | 558.2 | 565.6 | 576.8 | 582.0 | 597.7 | 609.6 | 630.4 | 649.1 | 659.5  | 670.7 |
| 25°   | 528.3 | 532.8 | 538.8 | 548.5 | 555.9 | 568.6 | 585.7 | 603.6 | 623.7 | 632.7  | 646.8 |
| 27.5° | 503.8 | 509.0 | 517.2 | 519.4 | 526.9 | 538.0 | 555.9 | 575.3 | 596.2 | 605.9  | 617.8 |
| 30°   | 485.1 | 488.1 | 491.1 | 495.6 | 502.3 | 512.0 | 526.9 | 544.0 | 569.3 | 576.8  | 591.7 |
| 32.5° | 468.7 | 470.2 | 471.7 | 475.4 | 479.2 | 488.9 | 500.8 | 519.4 | 540.3 | 551.5  | 564.9 |
| 35°   | 453.8 | 452.3 | 453.1 | 455.3 | 459.0 | 462.8 | 475.4 | 491.1 | 510.5 | 523.9  | 534.3 |
| 37.5° | 439.7 | 436.7 | 435.9 | 435.9 | 437.4 | 441.9 | 451.6 | 465.0 | 485.9 | 497.1  | 507.5 |
| 40°   | 424.0 | 421.0 | 419.6 | 418.8 | 418.1 | 421.0 | 428.5 | 441.9 | 458.3 | 468.7  | 480.7 |
| 42.5° | 409.1 | 406.1 | 402.4 | 401.7 | 400.2 | 401.7 | 406.9 | 419.6 | 433.7 | 444.1  | 453.8 |
| 45°   | 394.2 | 389.0 | 384.5 | 381.5 | 382.3 | 380.1 | 383.8 | 393.5 | 409.9 | 416.6  | 426.3 |
| 47.5° | 377.8 | 371.9 | 365.9 | 362.9 | 359.9 | 361.4 | 362.9 | 371.1 | 385.3 | 392.0  | 401.7 |
| 50°   | 362.2 | 354.0 | 347.3 | 343.5 | 341.3 | 339.8 | 341.3 | 349.5 | 359.9 | 365.9  | 374.1 |
| 52.5° | 344.3 | 336.1 | 329.4 | 323.4 | 320.4 | 318.2 | 318.9 | 326.4 | 336.1 | 342.0  | 350.2 |
| 55°   | 327.9 | 317.5 | 308.5 | 301.1 | 298.8 | 298.1 | 297.3 | 302.6 | 310.8 | 316.7  | 323.4 |
| 57.5° | 309.3 | 298.8 | 289.1 | 280.2 | 275.7 | 275.0 | 275.0 | 276.5 | 286.9 | 291.4  | 295.1 |
| 60°   | 290.6 | 279.5 | 269.0 | 260.8 | 254.1 | 251.9 | 251.1 | 254.1 | 259.3 | 263.8  | 269.0 |
| 62.5° | 269.8 | 258.6 | 245.9 | 238.5 | 231.8 | 225.8 | 228.0 | 228.8 | 236.2 | 238.5  | 242.9 |
| 65°   | 249.6 | 237.0 | 226.5 | 214.6 | 207.2 | 203.4 | 202.0 | 203.4 | 209.4 | 210.1  | 213.1 |
| 67.5° | 226.5 | 214.6 | 202.0 | 193.8 | 187.0 | 180.3 | 178.8 | 178.8 | 181.8 | 184.1  | 187.8 |
| 70°   | 204.2 | 192.3 | 178.1 | 169.2 | 162.5 | 156.5 | 154.3 | 153.5 | 155.7 | 157.2  | 161.0 |
| 72.5° | 178.1 | 166.2 | 155.7 | 146.1 | 137.9 | 133.4 | 131.2 | 129.7 | 131.9 | 133.4  | 134.1 |
| 75°   | 150.5 | 140.8 | 130.4 | 120.7 | 115.5 | 111.0 | 108.1 | 105.8 | 107.3 | 107.3  | 107.3 |
| 77.5° | 124.4 | 114.8 | 106.6 | 99.9  | 93.2  | 87.9  | 85.7  | 83.5  | 84.2  | 84.2   | 85.7  |
| 80°   | 96.9  | 90.2  | 83.5  | 77.5  | 71.5  | 67.1  | 65.6  | 63.3  | 61.9  | 61.1   | 61.1  |
| 82.5° | 71.5  | 66.3  | 60.4  | 55.1  | 52.2  | 47.7  | 46.2  | 43.2  | 43.2  | 42.5   | 42.5  |
| 85°   | 47.7  | 44.7  | 38.8  | 35.0  | 32.8  | 30.6  | 29.1  | 27.6  | 25.3  | 25.3   | 24.6  |
| 87.5° | 25.3  | 23.8  | 22.4  | 17.9  | 17.9  | 15.6  | 14.9  | 14.2  | 11.9  | 12.7   | 12.7  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |

TEST NUMBER: P996553

CATALOG NUMBER: S124DRP-B575DB50-4F0-XX-W2A-A

**CANDELA DISTRIBUTION (continued):**

|       | 345°  | 350°  | 355°  | 360°  |
|-------|-------|-------|-------|-------|
| 0°    | 899.5 | 899.5 | 899.5 | 899.5 |
| 2.5°  | 874.9 | 882.3 | 889.0 | 899.5 |
| 5°    | 855.5 | 865.9 | 880.1 | 895.7 |
| 7.5°  | 833.1 | 849.5 | 868.2 | 889.8 |
| 10°   | 812.3 | 830.9 | 854.7 | 880.8 |
| 12.5° | 790.7 | 813.0 | 839.1 | 867.4 |
| 15°   | 766.1 | 788.4 | 817.5 | 855.5 |
| 17.5° | 743.7 | 770.5 | 801.8 | 842.1 |
| 20°   | 717.6 | 743.0 | 777.2 | 823.5 |
| 22.5° | 694.5 | 723.6 | 761.6 | 801.8 |
| 25°   | 669.2 | 694.5 | 732.5 | 781.0 |
| 27.5° | 643.9 | 675.2 | 711.7 | 758.6 |
| 30°   | 619.3 | 645.3 | 684.8 | 734.0 |
| 32.5° | 592.4 | 623.7 | 660.3 | 706.5 |
| 35°   | 563.4 | 593.2 | 627.5 | 677.4 |
| 37.5° | 537.3 | 566.4 | 601.4 | 645.3 |
| 40°   | 508.2 | 538.8 | 570.8 | 614.8 |
| 42.5° | 479.9 | 507.5 | 539.5 | 579.8 |
| 45°   | 452.3 | 476.2 | 505.2 | 540.3 |
| 47.5° | 424.0 | 444.1 | 471.0 | 502.3 |
| 50°   | 393.5 | 415.1 | 435.2 | 461.3 |
| 52.5° | 365.2 | 383.8 | 400.2 | 421.8 |
| 55°   | 337.6 | 350.2 | 363.7 | 380.1 |
| 57.5° | 308.5 | 318.2 | 327.9 | 345.0 |
| 60°   | 279.5 | 288.4 | 293.6 | 304.8 |
| 62.5° | 251.1 | 254.9 | 261.6 | 268.3 |
| 65°   | 219.8 | 225.1 | 228.8 | 237.0 |
| 67.5° | 191.5 | 193.8 | 197.5 | 202.7 |
| 70°   | 161.7 | 166.9 | 168.4 | 172.1 |
| 72.5° | 136.4 | 138.6 | 140.1 | 140.8 |
| 75°   | 108.1 | 110.3 | 111.8 | 116.3 |
| 77.5° | 85.0  | 84.2  | 87.2  | 87.9  |
| 80°   | 62.6  | 60.4  | 61.1  | 64.1  |
| 82.5° | 41.0  | 41.7  | 41.0  | 41.0  |
| 85°   | 25.3  | 24.6  | 23.1  | 23.8  |
| 87.5° | 11.2  | 11.2  | 10.4  | 10.4  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |

(END OF REPORT)