

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060643

Luminaire Tested: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-78)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S
Description: DEFINE 4 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.8 lumens
Efficiency: N/A
Efficacy: 36.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.11 / 0.97
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060643

CATALOG NUMBER: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1060643

CATALOG NUMBER: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	87	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	50
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7717	7717	7717
5°	7429	7551	7705
10°	6850	7193	7628
15°	6148	6677	7460
20°	5374	6069	7212
25°	4545	5391	6891
30°	3671	4673	6503
35°	2733	3905	6127
40°	1734	3096	5764
45°	694	2270	5435
50°	303	1447	4961
55°	231	749	4330
60°	164	512	3434
65°	120	507	2345
70°	118	448	1075
75°	156	472	436
80°	233	531	471
85°	464	939	701

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5435 cd/sqm



TEST NUMBER: P1060643

CATALOG NUMBER: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.0	7.3
10°-20°	211.6	18.8
20°-30°	267.2	23.8
30°-40°	245.5	21.8
40°-50°	167.4	14.9
50°-60°	90.8	8.1
60°-70°	38.5	3.4
70°-80°	13.3	1.2
80°-90°	8.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.9	49.9
0°-40°	806.3	71.7
0°-60°	1064.5	94.6
0°-90°	1124.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	896	896	896	896	896	
5°	859	872	874	881	891	80
15°	690	712	749	802	837	192
25°	478	509	567	655	725	219
35°	260	294	372	488	583	161
45°	57	91	186	330	446	52
55°	15	17	50	182	288	14
65°	6	7	25	57	115	6
75°	5	13	14	13	13	5
85°	5	10	10	10	7	4
90°	0	0	0	0	0	



TEST NUMBER: P1060643

CATALOG NUMBER: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	896.2	896.2	896.2	896.2	896.2
2.5°	883.1	893.8	887.9	890.2	892.6
5°	859.4	872.4	873.6	880.7	891.4
7.5°	826.1	841.6	851.1	868.9	885.5
10°	783.4	802.4	822.6	851.1	872.4
12.5°	738.3	758.5	788.2	828.5	857.0
15°	689.6	712.2	749.0	802.4	836.8
17.5°	638.6	663.5	707.4	770.4	814.3
20°	586.4	613.7	662.3	733.6	787.0
22.5°	533.0	561.4	614.9	695.6	758.5
25°	478.4	509.2	567.4	655.2	725.3
27.5°	426.1	454.6	518.7	614.9	692.0
30°	369.2	401.2	470.0	573.3	654.0
32.5°	316.9	347.8	420.2	530.6	618.4
35°	260.0	294.4	371.5	487.9	582.8
37.5°	206.5	239.8	324.0	447.5	548.4
40°	154.3	188.7	275.4	407.1	512.8
42.5°	103.3	140.1	229.1	365.6	479.5
45°	57.0	91.4	186.4	330.0	446.3
47.5°	29.7	49.9	146.0	294.4	410.7
50°	22.6	27.3	108.0	255.2	370.3
52.5°	19.0	20.2	73.6	216.0	330.0
55°	15.4	16.6	49.9	181.6	288.4
57.5°	11.9	13.1	35.6	148.4	242.1
60°	9.5	10.7	29.7	114.0	199.4
62.5°	7.1	8.3	28.5	84.3	156.7
65°	5.9	7.1	24.9	57.0	115.1
67.5°	4.7	7.1	21.4	36.8	77.2
70°	4.7	9.5	17.8	23.7	42.7
72.5°	4.7	10.7	15.4	15.4	15.4
75°	4.7	13.1	14.2	13.1	13.1
77.5°	4.7	11.9	11.9	11.9	11.9
80°	4.7	10.7	10.7	10.7	9.5
82.5°	4.7	9.5	10.7	10.7	8.3
85°	4.7	9.5	9.5	9.5	7.1
87.5°	3.6	9.5	9.5	9.5	4.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060643
 CATALOG NUMBER: S124RDRP-H1020D840-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	15.54	16.82	15.91	17.13	17.45
	3H	0.00	0.19	0.00	0.52	0.88	15.90	17.03	16.28	17.36	17.72
	4H	0.44	1.49	0.84	1.84	2.22	15.86	16.91	16.27	17.26	17.65
	6H	1.79	2.76	2.21	3.13	3.52	15.84	16.80	16.25	17.17	17.57
	8H	2.47	3.38	2.90	3.77	4.18	15.83	16.74	16.26	17.13	17.54
	12H	3.26	4.13	3.70	4.52	4.95	15.83	16.70	16.26	17.08	17.51
4H	2H	1.24	2.29	1.65	2.64	3.03	15.35	16.39	15.75	16.75	17.13
	3H	2.66	3.52	3.07	3.92	4.32	15.74	16.59	16.15	17.00	17.40
	4H	4.11	4.88	4.55	5.30	5.74	15.72	16.48	16.16	16.90	17.35
	6H	5.36	6.01	5.82	6.46	6.93	15.74	16.40	16.20	16.84	17.31
	8H	5.92	6.54	6.39	6.98	7.45	15.75	16.36	16.22	16.81	17.28
	12H	6.59	7.13	7.08	7.62	8.09	15.79	16.33	16.27	16.81	17.29
8H	4H	5.19	5.80	5.66	6.25	6.72	15.62	16.24	16.09	16.68	17.15
	6H	6.80	7.30	7.30	7.80	8.28	15.67	16.17	16.17	16.67	17.15
	8H	7.63	8.08	8.15	8.60	9.09	15.73	16.18	16.25	16.70	17.19
	12H	8.59	8.99	9.11	9.49	10.06	15.84	16.24	16.36	16.74	17.31
12H	4H	5.38	5.92	5.86	6.40	6.88	15.58	16.12	16.07	16.61	17.08
	6H	7.15	7.60	7.67	8.11	8.61	15.64	16.09	16.16	16.61	17.10
	8H	8.16	8.56	8.68	9.06	9.63	15.74	16.14	16.26	16.64	17.21