

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060968

Luminaire Tested: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-75)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 988.5 lumens
Efficiency: N/A
Efficacy: 42.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.11 / 0.97
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060968

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot



TEST NUMBER: P1060968

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90					90			
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81					81			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72					72			
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65					65			
5	86	75	68	63	84	74	68	63	72	67	62	71	66	62	69	65	61	59					59			
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54					54			
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49					49			
8	71	60	53	48	70	59	52	48	58	52	48	57	51	47	56	51	47	45					45			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42					42			
10	63	52	45	41	62	52	45	41	51	45	41	50	44	41	49	44	40	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6755	6755	6755
5°	6525	6620	6748
10°	6013	6295	6673
15°	5401	5852	6525
20°	4707	5323	6302
25°	3972	4723	6027
30°	3204	4083	5712
35°	2371	3416	5391
40°	1469	2721	5071
45°	583	1984	4776
50°	259	1246	4342
55°	207	650	3801
60°	143	491	3028
65°	94	487	2082
70°	93	441	974
75°	123	429	429
80°	183	501	501
85°	366	998	731

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4776 cd/sqm



TEST NUMBER: P1060968

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	7.3
10°-20°	185.7	18.8
20°-30°	234.4	23.7
30°-40°	215.0	21.8
40°-50°	146.5	14.8
50°-60°	79.8	8.1
60°-70°	34.5	3.5
70°-80°	12.6	1.3
80°-90°	8.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.0	49.8
0°-40°	707.1	71.5
0°-60°	933.3	94.4
0°-90°	988.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	988.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	755	765	766	774	781	70
15°	606	627	656	703	732	168
25°	418	447	497	576	634	191
35°	226	259	325	428	513	139
45°	48	80	163	289	392	44
55°	14	15	43	159	253	12
65°	5	6	24	50	102	5
75°	4	12	13	13	13	4
85°	4	8	10	10	7	3
90°	0	0	0	0	0	



TEST NUMBER: P1060968

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	784.4	784.4	784.4	784.4	784.4
2.5°	775.1	784.4	777.9	779.7	779.7
5°	754.9	765.0	765.9	774.2	780.7
7.5°	724.5	739.2	746.6	763.2	774.2
10°	687.7	705.2	719.9	748.4	763.2
12.5°	648.1	668.4	690.4	728.2	749.4
15°	605.8	626.9	656.4	703.3	731.9
17.5°	558.8	584.6	620.5	676.6	711.6
20°	513.7	539.5	580.9	644.4	687.7
22.5°	466.7	493.4	539.5	610.4	661.9
25°	418.0	447.4	497.1	576.3	634.3
27.5°	370.1	401.4	453.9	540.4	604.8
30°	322.2	353.5	410.6	503.6	574.5
32.5°	273.4	305.6	367.3	464.9	543.2
35°	225.5	258.7	325.0	428.1	512.8
37.5°	176.8	211.7	282.6	392.2	482.4
40°	130.7	165.7	242.1	356.3	451.1
42.5°	87.5	122.4	200.7	321.3	421.6
45°	47.9	80.1	162.9	289.1	392.2
47.5°	25.8	44.2	126.1	257.8	359.0
50°	19.3	23.9	93.0	224.6	324.1
52.5°	16.6	18.4	64.4	189.6	289.1
55°	13.8	14.7	43.3	159.3	253.2
57.5°	11.0	12.0	32.2	128.9	214.5
60°	8.3	10.1	28.5	99.4	175.8
62.5°	6.4	8.3	26.7	72.7	139.0
65°	4.6	6.4	23.9	49.7	102.2
67.5°	4.6	7.4	20.3	32.2	69.0
70°	3.7	10.1	17.5	21.2	38.7
72.5°	3.7	11.0	14.7	14.7	14.7
75°	3.7	12.0	12.9	12.9	12.9
77.5°	3.7	11.0	12.0	11.0	11.0
80°	3.7	10.1	10.1	10.1	10.1
82.5°	3.7	9.2	10.1	10.1	8.3
85°	3.7	8.3	10.1	10.1	7.4
87.5°	2.8	8.3	9.2	9.2	5.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060968
 CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	15.05	16.32	15.41	16.64	16.95
	3H	0.00	0.24	0.00	0.57	0.94	15.42	16.55	15.80	16.88	17.25
	4H	0.33	1.38	0.73	1.73	2.12	15.40	16.45	15.80	16.80	17.19
	6H	1.51	2.48	1.93	2.85	3.24	15.39	16.35	15.80	16.72	17.12
	8H	2.10	3.02	2.53	3.41	3.81	15.39	16.30	15.82	16.69	17.10
	12H	2.78	3.65	3.21	4.03	4.46	15.40	16.27	15.83	16.66	17.09
4H	2H	1.29	2.34	1.69	2.69	3.07	14.86	15.91	15.26	16.26	16.64
	3H	2.87	3.73	3.28	4.13	4.54	15.28	16.13	15.69	16.54	16.94
	4H	4.17	4.94	4.60	5.36	5.80	15.27	16.04	15.71	16.46	16.91
	6H	5.29	5.96	5.76	6.40	6.87	15.31	15.98	15.78	16.42	16.89
	8H	5.81	6.42	6.28	6.87	7.34	15.34	15.96	15.81	16.41	16.88
	12H	6.36	6.90	6.85	7.39	7.86	15.41	15.95	15.89	16.44	16.91
8H	4H	5.25	5.87	5.72	6.32	6.79	15.18	15.80	15.65	16.25	16.72
	6H	6.79	7.30	7.29	7.79	8.28	15.26	15.77	15.76	16.26	16.75
	8H	7.60	8.06	8.12	8.57	9.06	15.34	15.80	15.87	16.32	16.81
	12H	8.44	8.84	8.95	9.33	9.91	15.51	15.92	16.03	16.41	16.98
12H	4H	5.44	5.99	5.93	6.47	6.95	15.15	15.69	15.63	16.18	16.65
	6H	7.15	7.60	7.67	8.12	8.61	15.23	15.69	15.76	16.21	16.70
	8H	8.16	8.56	8.67	9.06	9.63	15.37	15.77	15.89	16.27	16.84