

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060973

Luminaire Tested: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-76)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S
Description: DEFINE 4 SILVER REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1597.7 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 1.15 / 1.1
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060973

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1060973

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57
5	80	69	60	54	78	68	60	54	65	59	54	64	58	53	62	57	52	50
6	75	62	54	48	73	62	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	53	45	39	64	52	44	39	51	44	39	50	43	39	48	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7557	7557	7557
5°	7323	7419	7562
10°	6958	7159	7513
15°	6528	6848	7422
20°	6061	6491	7225
25°	5550	6049	6992
30°	5003	5598	6705
35°	4410	5106	6430
40°	3753	4602	6174
45°	3047	4066	5949
50°	2638	3501	5570
55°	2444	2970	5164
60°	2282	2678	4531
65°	2137	2512	3767
70°	1992	2316	2848
75°	1896	2143	2049
80°	1780	1964	1736
85°	1640	1818	1363

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5949 cd/sqm



TEST NUMBER: P1060973

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	5.1
10°-20°	217.8	13.6
20°-30°	297.4	18.6
30°-40°	311.6	19.5
40°-50°	269.7	16.9
50°-60°	202.6	12.7
60°-70°	130.7	8.2
70°-80°	67.0	4.2
80°-90°	20.0	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.2	37.3
0°-40°	907.8	56.8
0°-60°	1380.1	86.4
0°-90°	1597.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1597.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	878	878	878	878	878	
5°	847	860	858	865	875	79
15°	732	751	768	803	832	205
25°	584	606	637	686	736	268
35°	420	443	486	550	612	261
45°	250	276	334	416	488	197
55°	163	168	198	282	344	146
65°	105	107	123	149	185	104
75°	57	64	64	64	62	60
85°	17	19	18	18	14	19
90°	0	0	0	0	0	



TEST NUMBER: P1060973

CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	877.6	877.6	877.6	877.6	877.6
2.5°	866.6	877.6	871.2	873.0	875.8
5°	847.2	860.1	858.3	864.7	874.8
7.5°	823.3	837.1	839.9	854.6	869.3
10°	795.7	811.4	818.7	840.8	859.2
12.5°	765.4	781.9	794.8	822.4	849.1
15°	732.3	750.6	768.1	803.1	832.5
17.5°	698.2	716.6	739.6	778.2	811.4
20°	661.4	681.7	708.3	748.8	788.4
22.5°	623.7	644.9	673.4	717.5	763.5
25°	584.1	606.2	636.6	686.3	735.9
27.5°	544.6	566.7	600.7	653.1	707.4
30°	503.2	526.2	563.0	620.0	674.3
32.5°	461.8	486.6	524.4	585.1	643.0
35°	419.5	443.4	485.7	550.1	611.7
37.5°	377.2	402.0	447.1	516.1	580.5
40°	333.9	359.7	409.4	482.0	549.2
42.5°	290.7	318.3	370.7	447.1	517.9
45°	250.2	276.0	333.9	415.8	488.5
47.5°	219.9	237.3	297.1	385.4	455.4
50°	196.9	206.1	261.3	352.3	415.8
52.5°	179.4	185.8	228.1	316.5	383.6
55°	162.8	168.3	197.8	282.4	344.0
57.5°	148.1	150.9	174.8	249.3	306.3
60°	132.5	135.2	155.5	213.4	263.1
62.5°	118.7	120.5	139.8	179.4	223.5
65°	104.9	106.7	123.3	149.0	184.9
67.5°	92.0	94.8	107.6	121.4	147.2
70°	79.1	84.6	92.0	98.4	113.1
72.5°	68.1	73.6	77.3	79.1	80.0
75°	57.0	63.5	64.4	63.5	61.6
77.5°	46.0	51.5	51.5	49.7	47.8
80°	35.9	40.5	39.6	37.7	35.0
82.5°	26.7	29.4	28.5	26.7	23.9
85°	16.6	19.3	18.4	17.5	13.8
87.5°	8.3	11.0	10.1	9.2	5.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060973
 CATALOG NUMBER: S124RDRP-H795D840-X4F0-XX-UDD-WVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.46	14.94	13.83	15.26	15.57	17.23	18.72	17.60	19.03	19.34
	3H	15.12	16.44	15.49	16.77	17.13	18.35	19.68	18.72	20.00	20.37
	4H	15.79	17.03	16.19	17.38	17.76	18.64	19.88	19.04	20.23	20.61
	6H	16.30	17.45	16.71	17.82	18.21	18.83	19.98	19.25	20.35	20.74
	8H	16.48	17.57	16.91	17.96	18.37	18.89	19.98	19.31	20.37	20.77
	12H	16.61	17.65	17.04	18.04	18.46	18.91	19.96	19.34	20.34	20.77
4H	2H	14.24	15.49	14.64	15.84	16.22	17.39	18.64	17.79	18.99	19.37
	3H	16.10	17.14	16.52	17.54	17.94	18.70	19.74	19.11	20.14	20.54
	4H	16.91	17.84	17.35	18.26	18.70	19.11	20.04	19.54	20.46	20.90
	6H	17.56	18.37	18.02	18.81	19.27	19.43	20.23	19.89	20.68	21.14
	8H	17.79	18.54	18.25	18.99	19.46	19.52	20.27	19.98	20.72	21.19
	12H	17.96	18.63	18.44	19.11	19.58	19.58	20.25	20.06	20.73	21.21
8H	4H	17.26	18.02	17.73	18.46	18.93	19.24	20.00	19.71	20.44	20.91
	6H	18.06	18.68	18.55	19.17	19.65	19.66	20.28	20.15	20.77	21.25
	8H	18.38	18.94	18.89	19.45	19.93	19.81	20.37	20.32	20.88	21.37
	12H	18.64	19.14	19.15	19.63	20.19	19.93	20.43	20.44	20.92	21.48
12H	4H	17.29	17.97	17.77	18.44	18.92	19.25	19.92	19.73	20.40	20.87
	6H	18.12	18.68	18.63	19.19	19.68	19.68	20.24	20.19	20.75	21.24
	8H	18.50	19.00	19.01	19.49	20.06	19.88	20.37	20.39	20.87	21.43