

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055372

Luminaire Tested: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1055372  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S  
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 717.4 lumens  
Efficiency: N/A  
Efficacy: 30.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81  
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1055372

CATALOG NUMBER: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

### Luminous Intensity Polar Plot



TEST NUMBER: P1055372

CATALOG NUMBER: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11860	11860	11860
5°	11715	11671	11599
10°	11629	10950	10258
15°	11451	9795	8365
20°	11214	8397	6311
25°	10937	6880	4507
30°	10606	5371	2870
35°	10290	3939	1915
40°	9942	2656	1442
45°	9557	1870	1029
50°	9158	1424	722
55°	8766	988	532
60°	8344	667	436
65°	7738	480	345
70°	7052	382	299
75°	6120	337	227
80°	4855	251	251
85°	2674	326	174

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9557 cd/sqm



TEST NUMBER: P1055372

CATALOG NUMBER: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.2	8.0
10°-20°	140.5	19.6
20°-30°	160.5	22.4
30°-40°	136.1	19.0
40°-50°	101.5	14.2
50°-60°	65.6	9.1
60°-70°	36.6	5.1
70°-80°	16.1	2.2
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.2	49.9
0°-40°	494.2	68.9
0°-60°	661.4	92.2
0°-90°	717.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	626	626	626	626	626	
5°	616	624	614	608	610	58
15°	584	569	499	446	426	164
25°	523	462	329	241	216	241
35°	445	335	170	93	83	278
45°	357	212	70	45	38	275
55°	265	100	30	18	16	237
65°	173	37	11	8	8	172
75°	84	8	5	4	3	89
85°	12	1	2	1	1	18
90°	0	0	0	0	0	



TEST NUMBER: P1055372

CATALOG NUMBER: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	626.0	626.0	626.0	626.0	626.0
2.5°	619.1	628.3	620.6	620.6	622.1
5°	616.0	623.7	613.7	607.6	609.9
7.5°	611.4	616.8	596.1	577.6	576.1
10°	604.5	606.8	569.2	540.8	533.2
12.5°	594.5	589.2	536.2	496.3	483.3
15°	583.8	569.2	499.4	446.5	426.5
17.5°	570.7	544.7	458.7	394.3	369.8
20°	556.2	519.3	416.5	339.8	313.0
22.5°	540.1	491.0	372.8	288.4	261.6
25°	523.2	461.8	329.1	240.9	215.6
27.5°	505.5	431.1	286.1	197.9	170.3
30°	484.8	399.7	245.5	156.5	131.2
32.5°	465.6	366.7	207.9	121.2	99.7
35°	444.9	335.2	170.3	92.8	82.8
37.5°	423.5	303.8	137.3	78.2	69.8
40°	402.0	272.3	107.4	66.0	58.3
42.5°	379.7	241.6	82.8	55.2	47.6
45°	356.7	211.7	69.8	45.3	38.4
47.5°	333.7	181.8	58.3	36.1	30.7
50°	310.7	153.4	48.3	28.4	24.5
52.5°	288.4	126.6	38.4	23.0	19.9
55°	265.4	100.5	29.9	18.4	16.1
57.5°	242.4	78.2	23.0	15.3	13.8
60°	220.2	59.1	17.6	12.3	11.5
62.5°	197.2	47.6	13.8	10.0	9.2
65°	172.6	36.8	10.7	8.4	7.7
67.5°	150.4	26.8	8.4	6.9	6.1
70°	127.3	18.4	6.9	6.1	5.4
72.5°	105.1	11.5	5.4	4.6	4.6
75°	83.6	7.7	4.6	3.8	3.1
77.5°	63.7	4.6	3.1	3.1	2.3
80°	44.5	3.1	2.3	2.3	2.3
82.5°	27.6	2.3	1.5	1.5	1.5
85°	12.3	0.8	1.5	0.8	0.8
87.5°	2.3	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1055372

CATALOG NUMBER: S122R3DR-H675D927-X4F0-XX-UDD-FLL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.84	18.16	17.21	18.47	18.79	3.14	4.46	3.50	4.77	5.09
	3H	19.31	20.48	19.69	20.81	21.18	3.99	5.16	4.37	5.49	5.86
	4H	20.27	21.36	20.67	21.71	22.09	4.27	5.36	4.67	5.71	6.09
	6H	20.96	21.96	21.37	22.33	22.72	4.46	5.46	4.87	5.83	6.23
	8H	21.15	22.10	21.58	22.49	22.90	4.53	5.48	4.96	5.87	6.28
	12H	21.23	22.14	21.67	22.53	22.96	4.56	5.47	4.99	5.85	6.28
4H	2H	16.63	17.72	17.03	18.07	18.45	3.71	4.80	4.11	5.15	5.54
	3H	19.11	20.01	19.52	20.41	20.81	4.74	5.64	5.15	6.04	6.44
	4H	20.06	20.86	20.49	21.27	21.72	5.11	5.91	5.54	6.33	6.77
	6H	20.81	21.50	21.27	21.95	22.41	5.41	6.10	5.87	6.54	7.01
	8H	21.05	21.70	21.52	22.15	22.62	5.50	6.14	5.97	6.59	7.06
	12H	21.18	21.75	21.67	22.24	22.71	5.55	6.12	6.03	6.60	7.07
8H	4H	19.92	20.57	20.39	21.01	21.49	5.49	6.13	5.95	6.58	7.05
	6H	20.66	21.19	21.16	21.68	22.17	5.85	6.37	6.35	6.87	7.35
	8H	20.91	21.38	21.43	21.89	22.39	5.98	6.45	6.50	6.97	7.46
	12H	21.06	21.47	21.57	21.97	22.54	6.07	6.48	6.58	6.98	7.55
12H	4H	19.88	20.45	20.36	20.93	21.40	5.61	6.18	6.09	6.66	7.13
	6H	20.60	21.07	21.12	21.59	22.08	5.97	6.44	6.49	6.95	7.45
	8H	20.87	21.28	21.38	21.77	22.35	6.14	6.56	6.66	7.05	7.62