

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060732

Luminaire Tested: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-39)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B
Description: DEFINE 4 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1374.4 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 0.83 / 0.98
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060732

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1060732

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	90	103	98	93	89	94	91	87	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	69	64	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	47	46
9	67	56	49	44	66	56	49	44	54	48	44	54	48	44	53	48	44	42
10	64	52	46	41	63	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9064	9064	9064
5°	9033	8902	8889
10°	8991	8552	8286
15°	8869	8028	7499
20°	8628	7374	6649
25°	8339	6677	5738
30°	7985	5854	4749
35°	7548	5021	3694
40°	7113	4121	2582
45°	6594	3167	1279
50°	5951	2139	427
55°	5137	1096	297
60°	4113	393	210
65°	2820	216	94
70°	1264	116	76
75°	0	50	50
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6594 cd/sqm



TEST NUMBER: P1060732

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	7.1
10°-20°	254.8	18.5
20°-30°	329.9	24.0
30°-40°	313.4	22.8
40°-50°	221.9	16.1
50°-60°	113.9	8.3
60°-70°	39.8	2.9
70°-80°	3.4	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.9	49.6
0°-40°	995.3	72.4
0°-60°	1331.1	96.9
0°-90°	1374.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1374.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1045	1046	1030	1030	1028	99
15°	995	964	900	858	841	280
25°	878	809	703	628	604	404
35°	718	613	478	385	351	449
45°	542	417	260	149	105	417
55°	342	225	73	21	20	306
65°	138	67	11	6	5	138
75°	0	2	2	2	2	11
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1060732

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1049.5	1052.6	1043.5	1051.1	1052.6
5°	1045.0	1046.5	1029.8	1029.8	1028.3
7.5°	1037.4	1034.3	1007.0	996.3	994.8
10°	1028.3	1017.6	978.1	955.2	947.6
12.5°	1014.6	994.8	941.5	908.1	899.0
15°	994.8	964.4	900.5	857.9	841.2
17.5°	970.4	930.9	854.8	803.1	786.4
20°	941.5	891.4	804.7	746.9	725.6
22.5°	911.1	853.3	752.9	687.5	666.2
25°	877.7	809.2	702.7	628.2	603.9
27.5°	842.7	762.1	648.0	570.4	538.5
30°	803.1	714.9	588.7	508.0	477.6
32.5°	760.5	663.2	535.4	448.7	412.2
35°	718.0	613.0	477.6	384.8	351.4
37.5°	676.9	565.8	419.8	322.5	290.5
40°	632.8	514.1	366.6	266.2	229.7
42.5°	587.1	463.9	311.8	208.4	168.8
45°	541.5	416.8	260.1	149.1	105.0
47.5°	495.9	366.6	209.9	94.3	56.3
50°	444.2	317.9	159.7	50.2	31.9
52.5°	395.5	272.3	114.1	28.9	24.3
55°	342.2	225.1	73.0	21.3	19.8
57.5°	292.0	179.5	41.1	16.7	15.2
60°	238.8	138.4	22.8	13.7	12.2
62.5°	185.6	100.4	15.2	9.1	7.6
65°	138.4	66.9	10.6	6.1	4.6
67.5°	91.3	38.0	7.6	3.0	3.0
70°	50.2	18.3	4.6	3.0	3.0
72.5°	18.3	6.1	3.0	1.5	1.5
75°	0.0	1.5	1.5	1.5	1.5
77.5°	0.0	0.0	0.0	0.0	1.5
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1060732
 CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-BVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.19	17.44	16.55	17.76	18.07	0.00	0.10	0.00	0.41	0.73
	3H	16.47	17.57	16.85	17.90	18.27	0.00	0.02	0.00	0.35	0.72
	4H	16.39	17.41	16.79	17.76	18.15	0.00	0.00	0.00	0.27	0.66
	6H	16.30	17.24	16.72	17.61	18.01	0.00	0.00	0.00	0.15	0.55
	8H	16.26	17.14	16.69	17.53	17.94	0.00	0.00	0.00	0.07	0.48
	12H	16.21	17.06	16.64	17.44	17.87	0.00	0.00	0.00	0.00	0.41
4H	2H	15.96	16.99	16.36	17.34	17.72	0.00	0.33	0.00	0.68	1.06
	3H	16.24	17.07	16.66	17.48	17.88	0.00	0.26	0.00	0.67	1.07
	4H	16.15	16.89	16.59	17.31	17.75	0.00	0.15	0.00	0.57	1.02
	6H	16.06	16.69	16.53	17.14	17.61	0.00	0.00	0.00	0.43	0.90
	8H	16.00	16.59	16.47	17.04	17.51	0.00	0.00	0.00	0.33	0.80
	12H	15.95	16.47	16.44	16.95	17.43	0.00	0.00	0.00	0.24	0.72
8H	4H	16.00	16.59	16.47	17.04	17.51	0.00	0.07	0.00	0.51	0.99
	6H	15.89	16.37	16.40	16.87	17.35	0.00	0.00	0.00	0.37	0.85
	8H	15.83	16.26	16.35	16.77	17.27	0.00	0.00	0.00	0.27	0.77
	12H	15.78	16.16	16.29	16.65	17.23	0.00	0.00	0.00	0.15	0.72
12H	4H	15.95	16.47	16.44	16.95	17.43	0.00	0.00	0.00	0.43	0.90
	6H	15.83	16.26	16.35	16.77	17.27	0.00	0.00	0.00	0.27	0.77
	8H	15.78	16.16	16.29	16.65	17.23	0.00	0.00	0.00	0.15	0.72