

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1060737

Luminaire Tested: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1060737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-74)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W
Description: DEFINE 4 WHITE REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1928.9 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 1.12 / 1.01
Luminous Opening: Rectangular (W 0.31' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1060737

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1060737

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89					89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79					79			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70					70			
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63					63			
5	84	73	66	60	82	72	65	60	70	64	60	69	63	59	67	62	58	57					57			
6	79	67	60	54	77	67	59	54	65	59	54	63	58	53	62	57	53	51					51			
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47					47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43					43			
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39					39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11735	11735	11735
5°	11372	11517	11727
10°	10625	11038	11584
15°	9692	10372	11362
20°	8665	9572	10982
25°	7537	8652	10532
30°	6359	7661	10039
35°	5058	6595	9508
40°	3680	5495	8986
45°	2225	4339	8511
50°	1592	3141	7793
55°	1348	2126	6880
60°	1102	1731	5559
65°	868	1551	4002
70°	728	1304	2107
75°	659	1214	1065
80°	679	1210	1056
85°	899	1808	1205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8511 cd/sqm



TEST NUMBER: P1060737

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.5	6.5
10°-20°	328.8	17.0
20°-30°	426.4	22.1
30°-40°	410.5	21.3
40°-50°	305.4	15.8
50°-60°	187.8	9.7
60°-70°	92.2	4.8
70°-80°	36.0	1.9
80°-90°	16.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	880.7	45.7
0°-40°	1291.1	66.9
0°-60°	1784.3	92.5
0°-90°	1928.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1928.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1316	1335	1332	1345	1357	122
15°	1087	1122	1163	1233	1274	304
25°	793	836	911	1025	1108	363
35°	481	527	627	784	904	301
45°	183	227	356	550	699	152
55°	90	93	142	323	458	81
65°	43	46	76	122	196	44
75°	20	35	36	34	32	22
85°	9	17	18	18	12	9
90°	0	0	0	0	0	

TEST NUMBER: P1060737

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1362.8	1362.8	1362.8	1362.8	1362.8
2.5°	1349.1	1364.3	1352.2	1353.7	1355.2
5°	1315.6	1335.4	1332.4	1344.6	1356.7
7.5°	1269.9	1292.8	1303.4	1327.8	1344.6
10°	1215.1	1241.0	1262.3	1301.9	1324.8
12.5°	1154.2	1184.7	1215.1	1268.4	1303.4
15°	1087.2	1122.2	1163.4	1233.4	1274.5
17.5°	1018.7	1053.7	1107.0	1187.7	1239.5
20°	945.6	983.7	1044.6	1134.4	1198.4
22.5°	869.5	910.6	977.6	1079.6	1155.7
25°	793.3	836.0	910.6	1024.8	1108.5
27.5°	717.2	758.3	839.0	966.9	1058.3
30°	639.5	682.2	770.5	904.5	1009.6
32.5°	564.9	604.5	698.9	845.1	956.3
35°	481.2	526.9	627.4	784.2	904.5
37.5°	409.6	450.7	558.8	723.3	852.7
40°	327.4	373.1	488.8	663.9	799.4
42.5°	251.2	296.9	421.8	604.5	749.2
45°	182.7	226.9	356.3	549.7	698.9
47.5°	138.6	164.5	292.4	496.4	642.6
50°	118.8	126.4	234.5	438.5	581.7
52.5°	105.1	108.1	182.7	380.7	520.8
55°	89.8	92.9	141.6	322.8	458.3
57.5°	76.1	77.7	114.2	268.0	391.3
60°	64.0	65.5	100.5	214.7	322.8
62.5°	53.3	54.8	89.8	166.0	257.3
65°	42.6	45.7	76.1	121.8	196.4
67.5°	35.0	41.1	64.0	85.3	137.0
70°	28.9	39.6	51.8	59.4	83.7
72.5°	24.4	36.5	44.2	42.6	41.1
75°	19.8	35.0	36.5	33.5	32.0
77.5°	16.7	30.5	30.5	27.4	25.9
80°	13.7	24.4	24.4	24.4	21.3
82.5°	12.2	19.8	21.3	21.3	16.7
85°	9.1	16.7	18.3	18.3	12.2
87.5°	6.1	15.2	16.7	15.2	9.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1060737

CATALOG NUMBER: S124RDRP-H1195D850-X4F0-XX-UDD-SVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.34	9.68	8.71	10.00	10.31	17.51	18.85	17.87	19.16	19.48
	3H	9.45	10.64	9.83	10.97	11.34	18.02	19.21	18.39	19.54	19.90
	4H	9.97	11.08	10.37	11.43	11.81	18.04	19.15	18.44	19.50	19.88
	6H	10.40	11.42	10.82	11.79	12.19	18.05	19.07	18.46	19.44	19.83
	8H	10.59	11.56	11.02	11.95	12.36	18.05	19.02	18.48	19.41	19.81
	12H	10.77	11.70	11.21	12.08	12.51	18.05	18.98	18.48	19.36	19.79
4H	2H	9.49	10.60	9.89	10.95	11.33	17.40	18.51	17.80	18.86	19.24
	3H	10.83	11.74	11.24	12.14	12.54	17.99	18.90	18.40	19.30	19.71
	4H	11.56	12.37	12.00	12.79	13.24	18.05	18.86	18.48	19.28	19.72
	6H	12.17	12.87	12.63	13.32	13.78	18.12	18.83	18.59	19.27	19.74
	8H	12.41	13.07	12.88	13.52	13.99	18.15	18.81	18.62	19.26	19.73
	12H	12.65	13.23	13.13	13.71	14.19	18.20	18.78	18.68	19.26	19.73
8H	4H	12.03	12.68	12.50	13.13	13.60	18.01	18.66	18.48	19.11	19.58
	6H	12.88	13.42	13.38	13.91	14.39	18.13	18.67	18.64	19.17	19.65
	8H	13.29	13.77	13.81	14.28	14.78	18.22	18.70	18.74	19.22	19.71
	12H	13.71	14.13	14.22	14.63	15.20	18.34	18.77	18.85	19.26	19.83
12H	4H	12.08	12.66	12.57	13.15	13.62	17.98	18.56	18.47	19.04	19.52
	6H	13.01	13.49	13.53	14.01	14.50	18.12	18.60	18.64	19.11	19.61
	8H	13.53	13.96	14.05	14.46	15.03	18.25	18.68	18.76	19.17	19.74