

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055362

Luminaire Tested: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B
Description: DEFINE 2, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 766.5 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.56 / 0.7
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 23.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P105362

CATALOG NUMBER: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1055362

CATALOG NUMBER: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	106	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	66	63	61
6	82	72	65	60	80	71	64	59	69	63	59	68	62	59	66	62	58	56
7	77	67	60	55	76	66	59	55	65	59	55	63	58	54	62	57	54	52
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49
9	70	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15962	15962	15962
5°	15764	15507	15213
10°	15631	14177	12911
15°	15405	12271	9668
20°	15111	9859	6190
25°	14738	7227	3177
30°	14301	4723	1039
35°	13863	2620	604
40°	13365	1054	336
45°	12869	699	129
50°	12303	401	56
55°	11739	192	33
60°	11117	72	0
65°	10463	45	0
70°	9389	55	0
75°	8081	73	0
80°	6132	0	0
85°	2522	217	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12869 cd/sqm

TEST NUMBER: P1055362

CATALOG NUMBER: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.5	9.9
10°-20°	175.5	22.9
20°-30°	178.2	23.2
30°-40°	133.7	17.4
40°-50°	93.6	12.2
50°-60°	57.3	7.5
60°-70°	34.1	4.5
70°-80°	15.8	2.1
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.2	56.0
0°-40°	562.9	73.4
0°-60°	713.8	93.1
0°-90°	766.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	829	837	815	800	800	79
15°	785	743	626	530	493	221
25°	705	581	346	198	152	325
35°	599	390	113	34	26	375
45°	480	206	26	8	5	370
55°	355	63	6	2	1	318
65°	233	18	1	1	0	230
75°	110	2	1	1	0	117
85°	12	0	1	1	0	20
90°	0	0	0	0	0	



TEST NUMBER: P1055362

CATALOG NUMBER: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	842.5	842.5	842.5	842.5	842.5
2.5°	832.8	845.4	833.8	831.8	832.8
5°	828.9	836.7	815.4	799.9	799.9
7.5°	822.2	822.2	782.4	750.5	740.8
10°	812.5	801.8	736.9	685.6	671.1
12.5°	799.9	774.7	683.7	611.0	587.8
15°	785.4	742.7	625.6	529.7	492.9
17.5°	768.9	706.9	560.7	441.6	399.0
20°	749.5	668.2	489.0	351.5	307.0
22.5°	728.2	625.6	416.4	271.1	223.7
25°	705.0	581.0	345.7	197.5	152.0
27.5°	680.8	534.5	280.8	135.6	93.0
30°	653.7	486.1	215.9	80.4	47.5
32.5°	627.5	439.6	161.7	43.6	34.9
35°	599.4	390.3	113.3	33.9	26.1
37.5°	570.4	343.8	69.7	25.2	19.4
40°	540.4	296.3	42.6	18.4	13.6
42.5°	511.3	251.8	33.9	12.6	8.7
45°	480.3	206.3	26.1	7.7	4.8
47.5°	448.4	164.6	19.4	4.8	2.9
50°	417.4	127.8	13.6	2.9	1.9
52.5°	386.4	93.9	8.7	1.9	1.0
55°	355.4	62.9	5.8	1.9	1.0
57.5°	324.4	44.5	3.9	1.0	1.0
60°	293.4	34.9	1.9	1.0	0.0
62.5°	264.4	27.1	1.9	1.0	1.0
65°	233.4	18.4	1.0	1.0	0.0
67.5°	200.5	11.6	1.0	1.0	0.0
70°	169.5	6.8	1.0	1.0	0.0
72.5°	139.4	3.9	1.0	1.0	0.0
75°	110.4	1.9	1.0	1.0	0.0
77.5°	82.3	1.0	0.0	1.0	0.0
80°	56.2	0.0	0.0	1.0	0.0
82.5°	32.9	0.0	0.0	1.0	0.0
85°	11.6	0.0	1.0	1.0	0.0
87.5°	0.0	0.0	1.0	1.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055362
 CATALOG NUMBER: S122R3DR-H675D835-X4F0-XX-UDD-FLL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.83	17.09	16.20	17.41	17.72	0.00	0.00	0.00	0.00	0.00
	3H	19.58	20.69	19.96	21.03	21.39	0.00	0.00	0.00	0.00	0.00
	4H	20.89	21.93	21.29	22.28	22.66	0.00	0.00	0.00	0.00	0.00
	6H	21.74	22.70	22.16	23.07	23.46	0.00	0.00	0.00	0.00	0.00
	8H	21.96	22.86	22.39	23.25	23.66	0.00	0.00	0.00	0.00	0.00
	12H	22.02	22.88	22.45	23.27	23.70	0.00	0.00	0.00	0.00	0.00
4H	2H	15.59	16.63	15.99	16.98	17.36	0.00	0.00	0.00	0.00	0.00
	3H	19.33	20.18	19.74	20.59	20.99	0.00	0.00	0.00	0.00	0.00
	4H	20.63	21.39	21.06	21.81	22.25	0.00	0.00	0.00	0.00	0.00
	6H	21.55	22.20	22.01	22.65	23.12	0.00	0.00	0.00	0.00	0.00
	8H	21.80	22.42	22.27	22.86	23.34	0.00	0.00	0.00	0.00	0.00
	12H	21.91	22.44	22.39	22.93	23.40	0.00	0.00	0.00	0.00	0.00
8H	4H	20.48	21.09	20.95	21.54	22.01	0.00	0.00	0.00	0.00	0.00
	6H	21.38	21.88	21.89	22.38	22.86	0.00	0.00	0.00	0.00	0.00
	8H	21.64	22.08	22.16	22.60	23.09	0.00	0.00	0.00	0.00	0.00
	12H	21.76	22.15	22.27	22.64	23.22	0.00	0.00	0.00	0.00	0.00
12H	4H	20.43	20.97	20.92	21.46	21.93	0.00	0.00	0.00	0.00	0.00
	6H	21.32	21.76	21.84	22.28	22.77	0.00	0.00	0.00	0.00	0.00
	8H	21.60	21.99	22.11	22.48	23.05	0.00	0.00	0.00	0.00	0.00