

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055355

Luminaire Tested: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W
Description: DEFINE 2, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1115.4 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.71 / 0.9
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 17.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055355

CATALOG NUMBER: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1055355

CATALOG NUMBER: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	91	89					87				
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77					75				
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68					66				
4	87	76	69	63	85	75	68	62	73	66	61	71	65	61	68	64	60					58				
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	54					52				
6	75	63	55	50	74	63	55	49	61	54	49	59	53	49	58	52	48					46				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44					42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40					38				
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37					35				
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34					32				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13971	13971	13971
5°	13813	13767	13638
10°	13724	12916	12301
15°	13569	11839	10582
20°	13389	10528	8639
25°	13122	9100	6896
30°	12842	7688	5382
35°	12550	6432	4522
40°	12245	5216	4026
45°	11928	4560	3601
50°	11578	4035	3289
55°	11181	3647	3055
60°	10795	3319	2849
65°	10284	3039	2681
70°	9528	2836	2526
75°	8440	2569	2394
80°	7201	2422	2215
85°	4956	2152	2000

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11928 cd/sqm



TEST NUMBER: P1055355

CATALOG NUMBER: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.6	6.1
10°-20°	170.6	15.3
20°-30°	210.2	18.8
30°-40°	201.7	18.1
40°-50°	174.0	15.6
50°-60°	135.0	12.1
60°-70°	92.4	8.3
70°-80°	50.2	4.5
80°-90°	13.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.4	40.2
0°-40°	650.1	58.3
0°-60°	959.1	86.0
0°-90°	1115.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1115.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	726	737	724	715	717	69
15°	692	671	604	554	540	195
25°	628	560	435	355	330	289
35°	543	430	278	207	196	339
45°	445	300	170	141	134	343
55°	338	180	110	96	92	303
65°	229	98	68	62	60	226
75°	115	45	35	33	33	124
85°	23	11	10	10	9	29
90°	0	0	0	0	0	



TEST NUMBER: P1055355

CATALOG NUMBER: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.4	737.4	737.4	737.4	737.4
2.5°	729.4	741.7	733.1	733.1	735.0
5°	726.3	736.8	723.9	714.6	717.1
7.5°	720.8	728.2	702.3	682.5	681.9
10°	713.4	714.0	671.4	645.6	639.4
12.5°	704.1	694.3	640.0	601.2	591.9
15°	691.8	670.8	603.6	554.3	539.5
17.5°	678.8	646.8	564.8	503.1	482.8
20°	664.1	617.8	522.2	451.9	428.5
22.5°	647.4	590.1	479.7	402.6	378.0
25°	627.7	560.5	435.3	355.1	329.9
27.5°	608.6	530.3	392.8	313.2	287.3
30°	587.0	497.6	351.4	273.1	246.0
32.5°	565.4	464.3	313.2	234.9	214.6
35°	542.6	430.4	278.1	207.2	195.5
37.5°	519.2	397.1	244.8	188.7	178.2
40°	495.1	363.8	210.9	170.8	162.8
42.5°	470.4	331.1	187.4	156.0	148.6
45°	445.2	299.7	170.2	140.6	134.4
47.5°	418.0	268.2	153.5	127.6	122.1
50°	392.8	238.0	136.9	115.9	111.6
52.5°	365.6	208.4	123.3	105.4	101.7
55°	338.5	180.0	110.4	95.6	92.5
57.5°	312.0	152.9	98.0	86.3	83.9
60°	284.9	131.3	87.6	77.7	75.2
62.5°	257.1	114.1	77.7	69.7	67.2
65°	229.4	98.0	67.8	61.7	59.8
67.5°	200.4	82.6	59.2	54.3	53.0
70°	172.0	69.1	51.2	46.9	45.6
72.5°	144.3	56.1	43.2	40.1	38.8
75°	115.3	45.0	35.1	33.3	32.7
77.5°	90.0	35.1	28.4	27.1	26.5
80°	66.0	25.9	22.2	21.0	20.3
82.5°	43.8	17.9	16.0	15.4	14.8
85°	22.8	11.1	9.9	9.9	9.2
87.5°	7.4	4.9	4.9	4.9	4.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055355
 CATALOG NUMBER: S122R3DR-H485D940-X4F0-XX-UDD-FLL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.77	20.24	19.14	20.55	20.87	13.58	15.04	13.94	15.36	15.67
	3H	21.10	22.42	21.48	22.74	23.11	15.22	16.54	15.60	16.87	17.23
	4H	22.00	23.23	22.40	23.58	23.96	15.86	17.09	16.26	17.44	17.82
	6H	22.66	23.80	23.07	24.17	24.56	16.35	17.49	16.76	17.86	18.25
	8H	22.87	23.95	23.29	24.34	24.74	16.52	17.61	16.95	18.00	18.40
	12H	22.98	24.02	23.41	24.40	24.83	16.64	17.68	17.07	18.06	18.49
4H	2H	18.79	20.02	19.19	20.37	20.75	14.29	15.53	14.69	15.87	16.25
	3H	21.20	22.22	21.61	22.62	23.03	16.14	17.17	16.55	17.57	17.97
	4H	22.13	23.05	22.56	23.47	23.91	16.89	17.81	17.32	18.23	18.67
	6H	22.91	23.71	23.36	24.15	24.61	17.50	18.30	17.96	18.75	19.21
	8H	23.18	23.93	23.64	24.37	24.84	17.72	18.47	18.18	18.91	19.38
	12H	23.35	24.02	23.84	24.50	24.97	17.88	18.55	18.36	19.03	19.50
8H	4H	22.12	22.87	22.59	23.32	23.78	17.27	18.02	17.73	18.46	18.93
	6H	22.93	23.55	23.43	24.04	24.52	18.00	18.62	18.50	19.11	19.59
	8H	23.23	23.79	23.75	24.30	24.79	18.30	18.85	18.81	19.36	19.85
	12H	23.46	23.95	23.97	24.44	25.01	18.54	19.03	19.05	19.52	20.09
12H	4H	22.10	22.77	22.59	23.25	23.72	17.32	17.99	17.81	18.47	18.94
	6H	22.90	23.46	23.42	23.97	24.46	18.09	18.64	18.60	19.15	19.64
	8H	23.24	23.73	23.75	24.22	24.79	18.45	18.93	18.96	19.43	19.99