

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1061842

Luminaire Tested: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1061842  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B  
Description: DEFINE 5 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1290.0 lumens  
Efficiency: N/A  
Efficacy: 41.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01  
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1061842

CATALOG NUMBER: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1061842

CATALOG NUMBER: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90					90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80					80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71					71			
4	90	81	74	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63					63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57					57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	53	52					52			
7	74	62	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47					47			
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43					43			
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39					39			
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36					36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6142	6142	6142
5°	6134	6032	6032
10°	6086	5801	5650
15°	6003	5478	5179
20°	5871	5083	4651
25°	5709	4633	4039
30°	5497	4136	3406
35°	5268	3620	2763
40°	5012	3056	2047
45°	4713	2450	1236
50°	4359	1796	849
55°	3933	1102	707
60°	3341	749	562
65°	2641	572	443
70°	1665	411	364
75°	543	301	301
80°	178	226	270
85°	87	182	182

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4713 cd/sqm



TEST NUMBER: P1061842

CATALOG NUMBER: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.5	6.4
10°-20°	217.9	16.9
20°-30°	286.6	22.2
30°-40°	281.6	21.8
40°-50°	213.0	16.5
50°-60°	129.2	10.0
60°-70°	61.0	4.7
70°-80°	15.9	1.2
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	587.0	45.5
0°-40°	868.5	67.3
0°-60°	1210.7	93.9
0°-90°	1290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1290.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	892	892	892	892	892	
5°	888	885	873	874	873	84
15°	842	820	768	739	726	237
25°	752	695	610	553	532	345
35°	627	543	431	355	329	391
45°	484	381	252	160	127	373
55°	328	224	92	62	59	292
65°	162	83	35	30	27	160
75°	20	14	11	11	11	32
85°	1	1	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P1061842

CATALOG NUMBER: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	892.0	892.0	892.0	892.0	892.0
2.5°	890.9	890.9	884.1	892.0	892.0
5°	887.5	885.2	872.7	873.9	872.7
7.5°	880.7	876.1	854.6	848.9	844.4
10°	870.5	861.4	829.7	816.1	808.1
12.5°	859.1	843.3	800.2	780.9	768.5
15°	842.1	819.5	768.5	739.0	726.5
17.5°	824.0	791.1	731.1	695.9	680.1
20°	801.3	762.8	693.7	650.6	634.7
22.5°	776.4	731.1	650.6	603.0	581.4
25°	751.5	694.8	609.8	553.1	531.6
27.5°	723.1	658.5	563.3	504.4	480.6
30°	691.4	622.3	520.2	459.0	428.4
32.5°	659.7	584.8	474.9	408.0	377.4
35°	626.8	542.9	430.7	354.8	328.7
37.5°	591.6	503.2	385.4	306.0	275.4
40°	557.6	463.6	340.0	256.2	227.8
42.5°	521.4	423.9	294.7	207.4	175.7
45°	484.0	380.8	251.6	159.8	126.9
47.5°	445.4	342.3	208.6	117.9	95.2
50°	406.9	301.5	167.7	87.3	79.3
52.5°	367.2	261.8	126.9	72.5	69.1
55°	327.6	224.4	91.8	62.3	58.9
57.5°	286.8	183.6	69.1	53.3	49.9
60°	242.6	147.3	54.4	44.2	40.8
62.5°	201.7	115.6	44.2	36.3	34.0
65°	162.1	82.7	35.1	29.5	27.2
67.5°	121.3	55.5	27.2	22.7	22.7
70°	82.7	36.3	20.4	18.1	18.1
72.5°	49.9	21.5	14.7	14.7	14.7
75°	20.4	13.6	11.3	11.3	11.3
77.5°	6.8	7.9	7.9	9.1	9.1
80°	4.5	4.5	5.7	6.8	6.8
82.5°	2.3	3.4	3.4	4.5	4.5
85°	1.1	1.1	2.3	2.3	2.3
87.5°	0.0	0.0	0.0	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1061842  
 CATALOG NUMBER: S125RDRP-H1090D830-X4F0-XX-UDD-SVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.64	16.97	16.00	17.28	17.59	6.29	7.63	6.66	7.94	8.25
	3H	16.34	17.52	16.72	17.85	18.21	7.07	8.25	7.45	8.58	8.95
	4H	16.36	17.45	16.76	17.80	18.19	7.32	8.42	7.72	8.77	9.15
	6H	16.29	17.29	16.70	17.66	18.06	7.50	8.51	7.92	8.88	9.27
	8H	16.25	17.20	16.68	17.59	17.99	7.55	8.50	7.98	8.89	9.29
	12H	16.21	17.12	16.64	17.50	17.93	7.55	8.46	7.99	8.85	9.28
4H	2H	15.47	16.56	15.87	16.91	17.30	6.78	7.88	7.18	8.23	8.61
	3H	16.21	17.10	16.63	17.51	17.91	7.69	8.58	8.10	8.98	9.39
	4H	16.23	17.03	16.67	17.44	17.89	8.00	8.79	8.43	9.21	9.65
	6H	16.17	16.85	16.63	17.30	17.77	8.26	8.94	8.72	9.39	9.86
	8H	16.12	16.76	16.59	17.20	17.67	8.32	8.96	8.79	9.41	9.88
	12H	16.07	16.64	16.56	17.12	17.59	8.35	8.91	8.84	9.39	9.87
8H	4H	16.11	16.75	16.58	17.20	17.67	8.11	8.75	8.58	9.19	9.67
	6H	16.04	16.56	16.54	17.05	17.54	8.43	8.95	8.93	9.45	9.93
	8H	15.98	16.45	16.51	16.97	17.46	8.53	9.00	9.06	9.51	10.01
	12H	15.94	16.35	16.46	16.85	17.42	8.60	9.01	9.11	9.50	10.07
12H	4H	16.07	16.63	16.56	17.12	17.59	8.08	8.64	8.57	9.13	9.60
	6H	15.98	16.45	16.50	16.96	17.45	8.40	8.87	8.92	9.38	9.87
	8H	15.95	16.36	16.46	16.85	17.42	8.54	8.95	9.05	9.44	10.02