

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058565

Luminaire Tested: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-57)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H865D930-X4F0-XX-UDD-BVL-W
Description: DEFINE 2 WHITE REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 679.7 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.96 / 0.91
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058565

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

Luminous Intensity Polar Plot





TEST NUMBER: P1058565

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81				
3	98	91	85	80	96	89	84	79	86	82	78	84	80	76	81	78	75	73				
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				
5	87	77	70	65	85	76	70	65	74	69	64	72	67	64	71	66	63	61				
6	82	71	65	60	80	71	64	59	69	63	59	68	62	58	66	62	58	56				
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52				
8	73	62	55	51	72	62	55	51	60	54	50	59	54	50	58	53	50	48				
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45				
10	66	55	48	44	64	54	48	44	53	48	44	53	47	43	52	47	43	42				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11522	11522	11522
5°	11066	11269	11492
10°	10202	10652	11212
15°	9141	9771	10707
20°	8024	8691	9828
25°	6794	7505	8869
30°	5450	6301	7896
35°	4028	5041	6841
40°	2527	3946	5560
45°	992	2972	4118
50°	488	2007	2523
55°	386	1319	1126
60°	295	1070	1033
65°	218	1004	1004
70°	270	1025	1025
75°	285	1141	1069
80°	425	1488	1169
85°	847	2541	1694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 87.5°
 Luminance: 4653 cd/sqm



TEST NUMBER: P1058565

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.0	8.4
10°-20°	144.2	21.2
20°-30°	172.5	25.4
30°-40°	145.2	21.4
40°-50°	82.7	12.2
50°-60°	32.6	4.8
60°-70°	20.5	3.0
70°-80°	15.3	2.2
80°-90°	9.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.7	55.0
0°-40°	518.9	76.3
0°-60°	634.1	93.3
0°-90°	679.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	679.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	597	610	608	615	620	55
15°	478	496	512	542	560	134
25°	334	349	369	407	436	152
35°	179	195	224	272	304	111
45°	38	67	114	143	158	36
55°	12	26	41	42	35	11
65°	5	23	23	22	23	6
75°	4	16	16	15	15	4
85°	4	11	12	11	8	4
90°	0	0	0	0	0	



TEST NUMBER: P1058565

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	624.4	624.4	624.4	624.4	624.4
2.5°	614.4	625.4	618.4	619.4	620.4
5°	597.4	610.4	608.4	615.4	620.4
7.5°	572.5	586.4	591.4	603.4	612.4
10°	544.5	560.5	568.5	587.4	598.4
12.5°	512.5	530.5	542.5	566.5	582.4
15°	478.5	495.5	511.5	541.5	560.5
17.5°	444.6	461.6	478.5	511.5	531.5
20°	408.6	424.6	442.6	477.5	500.5
22.5°	370.6	387.6	405.6	441.6	469.6
25°	333.7	348.7	368.6	406.6	435.6
27.5°	294.7	309.7	331.7	370.6	401.6
30°	255.8	270.7	295.7	335.7	370.6
32.5°	216.8	232.8	259.8	303.7	338.7
35°	178.8	194.8	223.8	271.7	303.7
37.5°	141.9	159.8	191.8	238.8	268.7
40°	104.9	125.9	163.8	205.8	230.8
42.5°	69.9	95.9	137.9	172.8	193.8
45°	38.0	66.9	113.9	142.9	157.8
47.5°	21.0	43.0	90.9	113.9	122.9
50°	17.0	30.0	69.9	86.9	87.9
52.5°	14.0	27.0	52.0	61.9	56.9
55°	12.0	26.0	41.0	42.0	35.0
57.5°	10.0	25.0	34.0	30.0	30.0
60°	8.0	25.0	29.0	27.0	28.0
62.5°	6.0	25.0	26.0	24.0	25.0
65°	5.0	23.0	23.0	22.0	23.0
67.5°	5.0	21.0	21.0	20.0	21.0
70°	5.0	20.0	19.0	19.0	19.0
72.5°	4.0	18.0	18.0	17.0	17.0
75°	4.0	16.0	16.0	15.0	15.0
77.5°	4.0	15.0	15.0	14.0	13.0
80°	4.0	13.0	14.0	13.0	11.0
82.5°	4.0	12.0	13.0	12.0	9.0
85°	4.0	11.0	12.0	11.0	8.0
87.5°	3.0	11.0	11.0	9.0	6.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058565
 CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-BVL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.19	7.41	6.55	7.72	8.04	8.21	9.44	8.58	9.75	10.06
	3H	7.73	8.82	8.11	9.15	9.52	10.19	11.27	10.57	11.60	11.97
	4H	8.29	9.30	8.69	9.65	10.04	11.10	12.11	11.51	12.47	12.85
	6H	8.85	9.78	9.26	10.15	10.54	11.98	12.92	12.40	13.29	13.68
	8H	9.14	10.02	9.57	10.41	10.82	12.39	13.27	12.82	13.66	14.07
	12H	9.50	10.34	9.93	10.73	11.16	12.83	13.67	13.26	14.06	14.49
4H	2H	7.38	8.39	7.78	8.74	9.12	8.83	9.85	9.24	10.20	10.58
	3H	9.58	10.41	9.99	10.82	11.22	11.08	11.91	11.49	12.32	12.72
	4H	10.63	11.38	11.07	11.80	12.24	12.15	12.90	12.59	13.32	13.76
	6H	11.52	12.17	11.99	12.62	13.09	13.26	13.91	13.73	14.36	14.82
	8H	11.91	12.52	12.38	12.96	13.44	13.78	14.39	14.25	14.84	15.31
	12H	12.33	12.87	12.82	13.35	13.82	14.36	14.89	14.85	15.38	15.85
8H	4H	11.43	12.04	11.90	12.48	12.96	12.64	13.25	13.11	13.70	14.17
	6H	12.81	13.31	13.32	13.81	14.29	14.04	14.54	14.54	15.03	15.52
	8H	13.53	13.98	14.06	14.49	14.99	14.78	15.23	15.30	15.74	16.24
	12H	14.28	14.68	14.80	15.17	15.75	15.61	16.00	16.13	16.50	17.07
12H	4H	11.59	12.13	12.08	12.61	13.09	12.74	13.28	13.23	13.76	14.24
	6H	13.14	13.59	13.67	14.11	14.60	14.26	14.70	14.78	15.22	15.71
	8H	14.06	14.45	14.58	14.95	15.52	15.14	15.54	15.66	16.03	16.61