

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1061885

Luminaire Tested: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2024
Report Number: P1061885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-87)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S
Description: DEFINE 5 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1024.8 lumens
Efficiency: N/A
Efficacy: 32.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.14 / 0.98
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1061885

CATALOG NUMBER: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot



TEST NUMBER: P1061885

CATALOG NUMBER: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90					90			
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81					81			
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72					72			
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65					65			
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59					59			
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54					54			
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49					49			
8	71	60	52	47	69	59	52	47	58	52	47	57	51	47	55	50	47	45					45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42					42			
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5486	5486	5486
5°	5303	5385	5473
10°	4884	5118	5433
15°	4385	4763	5344
20°	3839	4357	5198
25°	3242	3891	5017
30°	2613	3386	4813
35°	1921	2854	4586
40°	1199	2302	4348
45°	449	1682	4042
50°	210	1051	3731
55°	154	436	3451
60°	107	230	2987
65°	64	272	2366
70°	58	316	1502
75°	77	314	471
80°	115	389	349
85°	229	616	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4042 cd/sqm



TEST NUMBER: P1061885

CATALOG NUMBER: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	7.1
10°-20°	189.1	18.5
20°-30°	241.0	23.5
30°-40°	224.3	21.9
40°-50°	153.7	15.0
50°-60°	84.6	8.3
60°-70°	40.1	3.9
70°-80°	12.6	1.2
80°-90°	6.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	503.2	49.1
0°-40°	727.4	71.0
0°-60°	965.7	94.2
0°-90°	1024.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	767	777	779	785	792	71
15°	615	635	668	718	750	172
25°	427	453	512	595	660	195
35°	229	261	340	451	546	142
45°	46	78	173	306	415	44
55°	13	15	36	171	288	12
65°	4	5	17	63	145	4
75°	3	5	12	13	18	3
85°	3	7	8	7	6	3
90°	0	0	0	0	0	



TEST NUMBER: P1061885

CATALOG NUMBER: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	796.8	796.8	796.8	796.8	796.8
2.5°	788.9	796.8	790.9	790.9	791.9
5°	767.3	777.1	779.1	785.0	791.9
7.5°	735.9	748.7	758.5	775.2	787.0
10°	698.6	714.3	732.0	759.5	777.1
12.5°	659.4	676.1	702.6	740.8	765.4
15°	615.2	634.9	668.2	718.3	749.7
17.5°	570.1	591.7	632.9	691.8	731.0
20°	524.0	546.6	594.6	660.4	709.4
22.5°	475.9	500.4	553.4	628.0	685.9
25°	426.8	453.3	512.2	594.6	660.4
27.5°	377.8	405.3	470.0	560.3	633.9
30°	328.7	357.2	425.9	525.0	605.4
32.5°	278.7	310.1	382.7	489.6	576.0
35°	228.6	261.0	339.5	451.4	545.6
37.5°	179.6	212.9	297.3	415.1	515.2
40°	133.4	166.8	256.1	378.8	483.8
42.5°	86.3	121.7	212.9	341.5	449.4
45°	46.1	77.5	172.7	306.1	415.1
47.5°	24.5	41.2	134.4	270.8	382.7
50°	19.6	22.6	98.1	235.5	348.3
52.5°	15.7	17.7	62.8	199.2	317.9
55°	12.8	14.7	36.3	170.7	287.5
57.5°	9.8	11.8	20.6	142.3	252.2
60°	7.8	8.8	16.7	113.8	216.9
62.5°	4.9	6.9	16.7	88.3	181.5
65°	3.9	4.9	16.7	62.8	145.2
67.5°	3.9	3.9	16.7	41.2	108.9
70°	2.9	2.9	15.7	26.5	74.6
72.5°	2.9	2.9	13.7	17.7	43.2
75°	2.9	4.9	11.8	12.8	17.7
77.5°	2.9	7.8	10.8	10.8	9.8
80°	2.9	7.8	9.8	8.8	8.8
82.5°	2.9	7.8	7.8	7.8	6.9
85°	2.9	6.9	7.8	6.9	5.9
87.5°	2.9	6.9	6.9	6.9	3.9
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1061885
 CATALOG NUMBER: S125RDRP-H1090D930-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	14.96	16.25	15.33	16.56	16.87
	3H	0.00	0.00	0.00	0.00	0.00	15.75	16.88	16.13	17.21	17.58
	4H	0.00	0.00	0.00	0.00	0.00	15.77	16.83	16.18	17.18	17.57
	6H	0.00	0.00	0.00	0.00	0.35	15.73	16.70	16.14	17.07	17.47
	8H	0.00	0.20	0.00	0.59	1.00	15.71	16.63	16.14	17.02	17.42
	12H	0.03	0.90	0.46	1.29	1.72	15.69	16.57	16.12	16.95	17.38
4H	2H	0.00	0.00	0.00	0.16	0.54	14.74	15.80	15.15	16.15	16.54
	3H	0.00	0.47	0.02	0.88	1.28	15.57	16.43	15.98	16.84	17.24
	4H	0.20	0.97	0.64	1.39	1.83	15.61	16.38	16.04	16.80	17.24
	6H	1.68	2.34	2.14	2.79	3.26	15.59	16.26	16.06	16.70	17.17
	8H	2.41	3.03	2.88	3.48	3.95	15.58	16.20	16.05	16.64	17.12
	12H	3.15	3.70	3.64	4.18	4.66	15.58	16.12	16.07	16.61	17.08
8H	4H	2.25	2.87	2.72	3.31	3.78	15.49	16.11	15.96	16.56	17.03
	6H	3.98	4.48	4.48	4.98	5.46	15.49	16.00	16.00	16.50	16.98
	8H	4.92	5.37	5.44	5.89	6.38	15.50	15.95	16.02	16.47	16.96
	12H	5.86	6.26	6.37	6.75	7.32	15.54	15.95	16.06	16.44	17.01
12H	4H	2.55	3.09	3.03	3.58	4.05	15.45	16.00	15.94	16.48	16.95
	6H	4.43	4.89	4.96	5.40	5.90	15.45	15.90	15.97	16.42	16.91
	8H	5.56	5.96	6.07	6.45	7.03	15.49	15.89	16.00	16.38	16.95