

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058566

Luminaire Tested: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-20)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H865D930-X4F0-XX-UDD-SVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.4 lumens
Efficiency: N/A
Efficacy: 17.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.85 / 0.91
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058566

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058566

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9221	9221	9221
5°	9163	9034	9071
10°	8969	8615	8503
15°	8497	8002	7773
20°	7639	7207	6953
25°	6802	6214	5990
30°	5951	5186	5037
35°	5010	4201	4066
40°	4037	3315	2932
45°	3019	2396	1743
50°	1889	1547	1145
55°	640	833	930
60°	369	517	734
65°	262	349	568
70°	216	270	432
75°	143	214	356
80°	106	213	319
85°	0	0	212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3019 cd/sqm

TEST NUMBER: P1058566

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	8.6
10°-20°	117.9	21.9
20°-30°	142.0	26.4
30°-40°	121.3	22.6
40°-50°	71.1	13.2
50°-60°	25.7	4.8
60°-70°	9.2	1.7
70°-80°	3.7	0.7
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	305.9	56.9
0°-40°	427.2	79.5
0°-60°	524.0	97.5
0°-90°	537.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	500	500	500	500	500	
5°	495	496	488	490	490	47
15°	445	438	419	411	407	124
25°	334	320	305	300	294	153
35°	222	206	186	184	180	139
45°	116	104	92	77	67	89
55°	20	28	26	27	29	25
65°	6	7	8	11	13	6
75°	2	3	3	4	5	3
85°	0	0	0	1	1	0
90°	0	0	0	0	0	



TEST NUMBER: P1058566

CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	499.7	499.7	499.7	499.7	499.7
2.5°	498.7	499.7	494.7	499.7	501.7
5°	494.7	495.7	487.7	489.7	489.7
7.5°	488.7	487.7	476.7	474.7	473.7
10°	478.7	475.7	459.8	456.8	453.8
12.5°	463.8	457.8	440.8	435.8	431.9
15°	444.8	437.8	418.9	410.9	406.9
17.5°	418.9	410.9	393.0	385.0	381.0
20°	389.0	381.0	367.0	358.1	354.1
22.5°	364.0	351.1	336.1	330.1	325.1
25°	334.1	320.2	305.2	300.2	294.2
27.5°	306.2	289.2	274.3	270.3	265.3
30°	279.3	261.3	243.4	243.4	236.4
32.5°	250.3	233.4	214.4	213.4	209.4
35°	222.4	205.5	186.5	184.5	180.5
37.5°	196.5	179.5	161.6	155.6	150.6
40°	167.6	152.6	137.6	127.7	121.7
42.5°	144.6	127.7	112.7	100.7	92.8
45°	115.7	103.7	91.8	76.8	66.8
47.5°	89.8	81.8	71.8	54.9	49.9
50°	65.8	61.8	53.9	40.9	39.9
52.5°	41.9	43.9	38.9	31.9	34.9
55°	19.9	27.9	25.9	26.9	28.9
57.5°	13.0	14.0	18.9	21.9	23.9
60°	10.0	10.0	14.0	18.0	19.9
62.5°	8.0	8.0	11.0	15.0	16.0
65°	6.0	7.0	8.0	11.0	13.0
67.5°	5.0	5.0	6.0	9.0	10.0
70°	4.0	4.0	5.0	7.0	8.0
72.5°	3.0	3.0	4.0	6.0	6.0
75°	2.0	3.0	3.0	4.0	5.0
77.5°	2.0	2.0	2.0	3.0	4.0
80°	1.0	1.0	2.0	2.0	3.0
82.5°	1.0	1.0	1.0	1.0	2.0
85°	0.0	0.0	0.0	1.0	1.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058566
 CATALOG NUMBER: S122RDR-H865D930-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.62	4.78	3.98	5.09	5.41	6.99	8.15	7.35	8.46	8.78
	3H	4.14	5.16	4.52	5.49	5.86	7.72	8.74	8.10	9.08	9.44
	4H	4.27	5.22	4.68	5.57	5.96	7.94	8.89	8.35	9.24	9.63
	6H	4.35	5.21	4.76	5.59	5.98	8.09	8.96	8.51	9.33	9.73
	8H	4.35	5.17	4.79	5.56	5.97	8.12	8.94	8.56	9.33	9.74
	12H	4.32	5.10	4.75	5.48	5.91	8.12	8.91	8.56	9.29	9.72
4H	2H	3.93	4.88	4.33	5.23	5.61	6.96	7.90	7.36	8.26	8.64
	3H	4.59	5.36	5.00	5.76	6.17	7.84	8.61	8.25	9.01	9.42
	4H	4.83	5.51	5.27	5.93	6.38	8.12	8.80	8.56	9.23	9.67
	6H	4.95	5.53	5.41	5.98	6.45	8.35	8.93	8.81	9.38	9.85
	8H	4.96	5.51	5.44	5.96	6.43	8.39	8.94	8.87	9.39	9.86
	12H	4.93	5.41	5.42	5.89	6.37	8.41	8.89	8.90	9.38	9.85
8H	4H	4.93	5.48	5.41	5.93	6.40	8.05	8.60	8.52	9.05	9.52
	6H	5.10	5.54	5.61	6.04	6.53	8.31	8.75	8.82	9.25	9.74
	8H	5.15	5.54	5.67	6.06	6.56	8.38	8.77	8.90	9.29	9.79
	12H	5.12	5.47	5.64	5.97	6.54	8.44	8.78	8.96	9.28	9.86
12H	4H	4.92	5.40	5.41	5.88	6.36	8.00	8.48	8.49	8.97	9.44
	6H	5.10	5.50	5.63	6.01	6.51	8.26	8.66	8.79	9.18	9.67
	8H	5.17	5.52	5.69	6.02	6.59	8.35	8.70	8.87	9.19	9.77