

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058366

Luminaire Tested: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-60)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H485D835-X4F0-XX-UDD-BVL-S
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 381.7 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.95 / 0.9
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058366

CATALOG NUMBER: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1058366

CATALOG NUMBER: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81				81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61				61
6	82	72	65	60	80	71	64	59	69	63	59	68	63	59	66	62	58	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48				48
9	69	58	52	47	68	58	51	47	57	51	47	56	51	47	55	50	47	45				45
10	66	55	48	44	65	54	48	44	54	48	44	53	47	44	52	47	44	42				42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6534	6534	6534
5°	6307	6407	6509
10°	5809	6063	6367
15°	5223	5572	6065
20°	4556	4968	5541
25°	3852	4282	4958
30°	3079	3556	4394
35°	2277	2856	3773
40°	1438	2238	3006
45°	566	1681	2213
50°	293	1128	1364
55°	241	743	611
60°	173	602	550
65°	148	563	563
70°	146	588	550
75°	192	677	577
80°	287	861	648
85°	423	1440	868

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 87.5°
 Luminance: 2877 cd/sqm



TEST NUMBER: P1058366

CATALOG NUMBER: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.4	8.5
10°-20°	81.8	21.4
20°-30°	97.2	25.5
30°-40°	80.9	21.2
40°-50°	45.2	11.8
50°-60°	18.2	4.8
60°-70°	11.7	3.1
70°-80°	8.8	2.3
80°-90°	5.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.4	55.4
0°-40°	292.3	76.6
0°-60°	355.7	93.2
0°-90°	381.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	381.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	354	354	354	354	354	
5°	340	347	346	349	351	32
15°	273	282	292	307	318	76
25°	189	197	210	227	244	86
35°	101	111	127	148	168	63
45°	22	37	64	75	85	20
55°	8	16	23	22	19	6
65°	3	14	13	12	13	3
75°	3	10	10	9	8	3
85°	2	6	7	6	4	2
90°	0	0	0	0	0	



TEST NUMBER: P1058366

CATALOG NUMBER: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	354.1	354.1	354.1	354.1	354.1
2.5°	349.3	354.8	352.0	352.0	352.7
5°	340.5	346.6	345.9	348.7	351.4
7.5°	326.3	333.1	336.4	342.5	347.3
10°	310.0	317.5	323.6	333.1	339.8
12.5°	292.4	299.8	308.6	320.8	329.7
15°	273.4	281.5	291.7	306.6	317.5
17.5°	252.3	261.2	272.7	289.0	300.5
20°	232.0	240.8	253.0	269.3	282.2
22.5°	211.0	218.4	231.3	247.6	263.2
25°	189.2	196.7	210.3	226.6	243.5
27.5°	167.5	175.0	188.6	205.5	224.5
30°	144.5	152.6	166.9	185.9	206.2
32.5°	122.8	130.9	145.8	166.9	187.2
35°	101.1	110.6	126.8	147.9	167.5
37.5°	80.0	90.9	109.2	128.9	146.5
40°	59.7	71.2	92.9	109.9	124.8
42.5°	39.3	52.9	78.0	92.3	103.8
45°	21.7	36.6	64.4	75.3	84.8
47.5°	12.2	23.7	50.9	59.7	65.1
50°	10.2	17.6	39.3	45.4	47.5
52.5°	8.1	16.3	29.8	33.2	31.9
55°	7.5	15.6	23.1	22.4	19.0
57.5°	6.1	15.6	18.3	16.3	16.3
60°	4.7	14.9	16.3	14.2	14.9
62.5°	4.1	14.2	14.9	13.6	13.6
65°	3.4	13.6	12.9	12.2	12.9
67.5°	2.7	12.2	12.2	11.5	11.5
70°	2.7	11.5	10.9	10.2	10.2
72.5°	2.7	10.2	10.2	9.5	9.5
75°	2.7	9.5	9.5	8.8	8.1
77.5°	2.7	8.1	8.8	8.1	7.5
80°	2.7	7.5	8.1	7.5	6.1
82.5°	2.7	6.8	7.5	6.8	5.4
85°	2.0	6.1	6.8	6.1	4.1
87.5°	2.0	6.1	6.8	5.4	3.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058366
 CATALOG NUMBER: S122RDR-H485D835-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.88	6.10	5.25	6.42	6.73	5.97	7.19	6.33	7.50	7.82
	3H	6.21	7.30	6.59	7.63	7.99	7.99	9.08	8.37	9.41	9.77
	4H	6.79	7.80	7.19	8.15	8.53	8.94	9.95	9.35	10.31	10.69
	6H	7.35	8.28	7.77	8.65	9.05	9.89	10.82	10.31	11.19	11.59
	8H	7.68	8.55	8.11	8.95	9.35	10.34	11.22	10.77	11.61	12.02
	12H	7.98	8.82	8.41	9.20	9.63	10.77	11.61	11.20	11.99	12.42
4H	2H	5.85	6.86	6.25	7.21	7.60	6.65	7.66	7.05	8.01	8.39
	3H	7.88	8.71	8.29	9.11	9.52	8.93	9.76	9.34	10.16	10.57
	4H	8.96	9.70	9.39	10.12	10.57	10.07	10.82	10.50	11.24	11.68
	6H	9.83	10.47	10.29	10.92	11.39	11.24	11.89	11.71	12.34	12.80
	8H	10.24	10.84	10.71	11.29	11.76	11.80	12.41	12.27	12.86	13.33
	12H	10.61	11.15	11.10	11.63	12.11	12.35	12.88	12.84	13.37	13.84
8H	4H	9.73	10.33	10.20	10.78	11.25	10.62	11.22	11.09	11.67	12.14
	6H	11.07	11.56	11.57	12.06	12.54	12.08	12.57	12.58	13.07	13.55
	8H	11.79	12.23	12.31	12.75	13.24	12.84	13.29	13.36	13.80	14.30
	12H	12.47	12.87	12.99	13.36	13.94	13.63	14.02	14.15	14.52	15.09
12H	4H	9.88	10.42	10.37	10.90	11.38	10.73	11.26	11.21	11.74	12.22
	6H	11.39	11.84	11.91	12.35	12.85	12.30	12.75	12.83	13.27	13.76
	8H	12.30	12.69	12.81	13.19	13.76	13.21	13.61	13.73	14.10	14.67