

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058587

Luminaire Tested: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-19)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H865D940-X4F0-XX-UDD-WVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH WHITE STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1040.4 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.92 / 1.02
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058587

CATALOG NUMBER: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058587

CATALOG NUMBER: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100														
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88						88														
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77						77														
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68						68														
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61						61														
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54						54														
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49						49														
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	44						44														
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41						41														
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37						37														
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34						34														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12642	12642	12642
5°	12570	12386	12468
10°	12346	11917	11816
15°	11900	11275	11046
20°	11010	10455	10219
25°	10107	9439	9262
30°	9228	8414	8320
35°	8355	7445	7274
40°	7436	6492	6150
45°	6407	5579	4924
50°	5294	4696	4134
55°	3825	3896	3719
60°	3181	3340	3380
65°	2716	2904	3096
70°	2239	2590	2827
75°	1868	2174	2567
80°	1392	1743	2317
85°	466	932	2075

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6407 cd/sqm

TEST NUMBER: P1058587

CATALOG NUMBER: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.3	6.1
10°-20°	166.8	16.0
20°-30°	215.8	20.7
30°-40°	211.7	20.3
40°-50°	166.7	16.0
50°-60°	109.2	10.5
60°-70°	66.5	6.4
70°-80°	33.2	3.2
80°-90°	7.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.9	42.9
0°-40°	657.6	63.2
0°-60°	933.5	89.7
0°-90°	1040.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	685	685	685	685	685	
5°	679	679	669	673	673	64
15°	623	614	590	583	578	174
25°	496	480	464	462	455	228
35°	371	350	330	330	323	231
45°	246	230	214	198	189	189
55°	119	126	121	117	116	113
65°	62	63	66	70	71	62
75°	26	27	30	35	36	28
85°	2	3	4	8	10	4
90°	0	0	0	0	0	



TEST NUMBER: P1058587

CATALOG NUMBER: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	685.1	685.1	685.1	685.1	685.1
2.5°	682.9	684.0	677.5	684.0	686.2
5°	678.6	678.6	668.7	673.1	673.1
7.5°	670.9	669.8	654.6	654.6	653.5
10°	658.9	654.6	636.0	632.7	630.6
12.5°	643.6	636.0	614.2	608.7	605.5
15°	622.9	614.2	590.2	582.6	578.2
17.5°	592.4	583.6	562.9	554.2	549.8
20°	560.7	547.6	532.4	524.7	520.4
22.5°	528.0	512.7	498.5	493.1	488.7
25°	496.4	480.0	463.6	461.5	454.9
27.5°	465.8	446.2	429.8	428.7	423.3
30°	433.1	412.4	394.9	396.0	390.5
32.5°	402.5	382.9	362.2	363.3	356.7
35°	370.9	350.2	330.5	329.5	322.9
37.5°	338.2	318.5	300.0	295.6	289.1
40°	308.7	289.1	269.5	261.8	255.3
42.5°	277.1	259.6	242.2	230.2	221.5
45°	245.5	230.2	213.8	198.5	188.7
47.5°	214.9	202.9	188.7	170.2	163.6
50°	184.4	175.6	163.6	147.3	144.0
52.5°	152.7	149.5	141.8	130.9	129.8
55°	118.9	125.5	121.1	116.7	115.6
57.5°	100.4	101.5	104.7	103.6	103.6
60°	86.2	86.2	90.5	91.6	91.6
62.5°	73.1	74.2	78.5	80.7	80.7
65°	62.2	63.3	66.5	69.8	70.9
67.5°	51.3	53.5	56.7	60.0	61.1
70°	41.5	43.6	48.0	51.3	52.4
72.5°	33.8	34.9	39.3	42.5	43.6
75°	26.2	27.3	30.5	34.9	36.0
77.5°	18.5	20.7	24.0	27.3	29.5
80°	13.1	14.2	16.4	20.7	21.8
82.5°	7.6	8.7	10.9	14.2	15.3
85°	2.2	3.3	4.4	7.6	9.8
87.5°	0.0	0.0	0.0	2.2	4.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058587
 CATALOG NUMBER: S122RDR-H865D940-X4F0-XX-UDD-WVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.94	16.34	15.30	16.65	16.96	15.11	16.51	15.48	16.82	17.14
	3H	16.07	17.32	16.45	17.65	18.01	16.58	17.82	16.95	18.15	18.51
	4H	16.42	17.59	16.83	17.94	18.32	17.12	18.28	17.52	18.63	19.01
	6H	16.61	17.68	17.02	18.05	18.44	17.53	18.60	17.94	18.97	19.36
	8H	16.63	17.65	17.06	18.04	18.44	17.66	18.67	18.09	19.07	19.47
	12H	16.62	17.59	17.05	17.97	18.40	17.74	18.71	18.17	19.10	19.53
4H	2H	15.40	16.56	15.80	16.91	17.29	15.54	16.70	15.94	17.05	17.43
	3H	16.74	17.69	17.15	18.10	18.50	17.21	18.17	17.63	18.57	18.98
	4H	17.18	18.04	17.61	18.46	18.90	17.88	18.74	18.31	19.16	19.60
	6H	17.45	18.19	17.91	18.64	19.10	18.41	19.16	18.87	19.60	20.07
	8H	17.50	18.19	17.96	18.63	19.10	18.58	19.28	19.05	19.72	20.19
	12H	17.49	18.11	17.97	18.59	19.06	18.70	19.32	19.19	19.80	20.27
8H	4H	17.39	18.09	17.86	18.53	19.00	18.03	18.72	18.49	19.17	19.64
	6H	17.74	18.31	18.24	18.80	19.28	18.66	19.23	19.16	19.72	20.20
	8H	17.82	18.33	18.34	18.84	19.33	18.89	19.40	19.41	19.92	20.41
	12H	17.83	18.28	18.35	18.78	19.35	19.08	19.53	19.59	20.02	20.59
12H	4H	17.41	18.02	17.89	18.50	18.97	18.01	18.63	18.50	19.11	19.58
	6H	17.76	18.28	18.28	18.79	19.28	18.65	19.16	19.17	19.68	20.17
	8H	17.88	18.33	18.39	18.82	19.39	18.93	19.38	19.44	19.87	20.44