

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P995775

Luminaire Tested: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P995775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-14)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct Perimeter with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1154.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 13
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P995775

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P995775

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	112	112	112	112	105	105	105	98	98	98	92	92	92	89			
1	104	98	93	88	100	95	90	86	88	85	81	82	79	77	77	75	72	69			
2	94	84	77	70	90	81	74	68	76	70	65	71	66	62	66	62	59	56			
3	85	73	64	57	81	71	63	56	66	59	54	62	56	51	58	53	49	46			
4	77	64	55	48	74	62	54	47	58	51	45	55	48	43	51	46	42	39			
5	71	57	48	41	68	56	47	40	52	44	39	49	42	37	46	40	36	33			
6	65	51	42	35	63	50	41	35	47	39	34	44	37	32	42	36	31	29			
7	60	46	37	31	58	45	37	31	43	35	30	40	34	29	38	32	28	25			
8	56	42	34	28	54	41	33	27	39	32	26	37	30	25	35	29	25	23			
9	52	39	30	25	50	38	30	24	36	29	24	34	27	23	32	26	22	20			
10	49	36	28	22	47	35	27	22	33	26	21	31	25	21	30	24	20	18			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4787	4787	4787
5°	4819	4757	4792
10°	4798	4763	4812
15°	4741	4756	4813
20°	4666	4733	4814
25°	4593	4716	4831
30°	4487	4696	4847
35°	4379	4684	4930
40°	4265	4709	5027
45°	4159	4768	5171
50°	4049	4869	5354
55°	3933	4995	5588
60°	3790	5176	5898
65°	3644	5416	6304
70°	3490	5804	6919
75°	3297	6514	8018
80°	2999	8031	10264
85°	2870	12895	17363

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 31826 cd/sqm

TEST NUMBER: P995775

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.7	2.5
10°-20°	82.2	7.1
20°-30°	124.6	10.8
30°-40°	151.7	13.1
40°-50°	163.2	14.1
50°-60°	158.5	13.7
60°-70°	138.4	12.0
70°-80°	106.6	9.2
80°-90°	71.4	6.2
90°-100°	49.2	4.3
100°-110°	36.0	3.1
110°-120°	23.7	2.1
120°-130°	13.2	1.1
130°-140°	5.5	0.5
140°-150°	0.9	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.5	20.4
0°-40°	387.2	33.6
0°-60°	709.0	61.4
0°-90°	1025.4	88.9
90°-120°	108.9	9.4
90°-150°	128.6	11.1
90°-180°	129.0	11.2
0°-180°	1154.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	302	302	302	302	302	
5°	303	302	299	302	302	29
15°	289	290	290	294	294	81
25°	263	266	270	275	277	121
35°	227	234	242	252	255	142
45°	186	198	213	227	231	143
55°	142	158	181	197	202	127
65°	97	119	145	163	168	97
75°	54	78	106	125	131	57
85°	16	43	71	89	96	17
90°	4	30	58	75	81	3
95°	4	24	50	67	72	3
105°	2	15	38	53	58	3
115°	2	7	26	39	44	2
125°	1	1	15	27	31	1
135°	0	0	5	14	18	0
145°	0	0	0	3	5	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P995775

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	302.4	302.4	302.4	302.4	302.4
2.5°	304.6	303.3	300.2	302.4	301.6
5°	303.3	302.0	299.4	302.0	301.6
7.5°	301.1	300.2	298.1	301.1	300.7
10°	298.5	297.6	296.3	299.8	299.4
12.5°	294.1	294.5	293.7	297.2	296.7
15°	289.3	290.2	290.2	294.1	293.7
17.5°	283.2	284.9	286.2	290.2	290.2
20°	277.0	279.2	281.0	285.8	285.8
22.5°	270.4	273.1	275.7	280.5	281.4
25°	263.0	266.1	270.0	275.3	276.6
27.5°	254.2	259.0	263.4	270.0	270.9
30°	245.5	251.2	256.9	263.9	265.2
32.5°	235.8	242.4	249.4	257.7	260.4
35°	226.6	234.1	242.4	252.0	255.1
37.5°	216.5	224.9	235.4	245.9	249.0
40°	206.4	216.1	227.9	239.3	243.3
42.5°	196.8	206.4	220.5	233.2	237.1
45°	185.8	197.7	213.0	226.6	231.0
47.5°	175.3	188.0	205.6	219.6	224.4
50°	164.4	178.0	197.7	212.6	217.4
52.5°	153.8	168.3	189.4	204.7	210.0
55°	142.5	158.2	181.0	196.8	202.5
57.5°	131.5	149.0	171.8	188.9	194.6
60°	119.7	138.5	163.5	180.1	186.3
62.5°	109.1	128.9	153.8	171.8	177.5
65°	97.3	118.8	144.6	162.6	168.3
67.5°	86.8	109.1	135.4	153.4	159.5
70°	75.4	98.2	125.4	144.2	149.5
72.5°	64.9	88.5	116.2	134.6	141.1
75°	53.9	78.5	106.5	125.4	131.1
77.5°	43.4	68.8	97.3	116.2	122.3
80°	32.9	59.6	88.1	106.5	112.6
82.5°	24.1	50.4	79.3	97.7	103.4
85°	15.8	43.0	71.0	89.4	95.6
87.5°	9.6	35.9	64.0	82.0	87.7
90°	4.4	29.8	57.9	75.4	80.7
92.5°	3.9	27.2	53.9	71.0	76.3
95°	3.5	24.1	50.4	67.1	72.3
97.5°	3.1	21.9	47.3	63.6	68.8
100°	3.1	19.3	43.8	60.0	64.9
102.5°	2.6	17.1	40.8	56.5	61.4
105°	2.2	14.9	37.7	53.0	57.9
107.5°	2.2	12.7	34.6	49.5	54.4
110°	1.8	10.5	32.0	46.0	50.8

TEST NUMBER: P995775

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.8	8.8	28.9	43.0	47.8
115°	1.8	6.6	26.3	39.4	44.3
117.5°	1.3	4.8	23.2	36.4	40.8
120°	1.3	3.1	20.6	32.9	37.7
122.5°	1.3	1.8	18.0	29.8	33.8
125°	0.9	0.9	14.9	26.7	30.7
127.5°	0.9	0.4	12.3	23.2	27.2
130°	0.9	0.4	9.6	20.2	23.7
132.5°	0.9	0.4	7.0	17.1	20.6
135°	0.4	0.4	4.8	14.0	17.5
137.5°	0.4	0.4	2.6	11.0	14.0
140°	0.4	0.0	0.9	7.9	10.5
142.5°	0.4	0.0	0.0	5.3	7.5
145°	0.0	0.0	0.0	2.6	4.8
147.5°	0.0	0.0	0.0	0.4	1.8
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)