

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P995776

Luminaire Tested: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P995776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-14)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct Perimeter with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1164.0 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P995776

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P995776

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	112	112	112	112	105	105	105	98	98	98	92	92	92	89			
1	104	98	93	88	100	95	90	86	88	85	81	82	79	77	77	75	72	69			
2	94	84	77	70	90	81	74	68	76	70	65	71	66	62	66	62	59	56			
3	85	73	64	57	81	71	63	56	66	59	54	62	56	51	58	53	49	46			
4	77	64	55	48	74	62	54	47	58	51	45	55	48	43	51	46	42	39			
5	71	57	48	41	68	56	47	40	52	44	39	49	42	37	46	40	36	33			
6	65	51	42	35	63	50	41	35	47	39	34	44	37	32	42	36	31	29			
7	60	46	37	31	58	45	37	31	43	35	30	40	34	29	38	32	28	25			
8	56	42	34	28	54	41	33	27	39	32	26	37	30	25	35	29	25	23			
9	52	39	30	25	50	38	30	24	36	29	24	34	27	23	32	26	22	20			
10	49	36	28	22	47	35	27	22	33	26	21	31	25	21	30	24	20	18			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4830	4830	4830
5°	4861	4799	4834
10°	4840	4804	4854
15°	4782	4797	4854
20°	4707	4774	4856
25°	4634	4756	4873
30°	4526	4736	4889
35°	4417	4725	4972
40°	4302	4751	5071
45°	4197	4811	5216
50°	4083	4910	5400
55°	3966	5039	5638
60°	3821	5220	5949
65°	3674	5465	6360
70°	3517	5850	6979
75°	3327	6569	8085
80°	3026	8104	10355
85°	2888	13004	17508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 32080 cd/sqm

TEST NUMBER: P995776

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	2.5
10°-20°	82.9	7.1
20°-30°	125.7	10.8
30°-40°	153.0	13.1
40°-50°	164.7	14.1
50°-60°	159.9	13.7
60°-70°	139.6	12.0
70°-80°	107.5	9.2
80°-90°	72.0	6.2
90°-100°	49.6	4.3
100°-110°	36.3	3.1
110°-120°	23.9	2.1
120°-130°	13.3	1.1
130°-140°	5.6	0.5
140°-150°	0.9	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.5	20.4
0°-40°	390.6	33.6
0°-60°	715.1	61.4
0°-90°	1034.2	88.9
90°-120°	109.9	9.4
90°-150°	129.7	11.1
90°-180°	130.0	11.2
0°-180°	1164.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	305	305	305	305	305	
5°	306	305	302	305	304	29
15°	292	293	293	297	296	82
25°	265	268	272	278	279	122
35°	229	236	244	254	257	143
45°	188	199	215	229	233	145
55°	144	160	183	198	204	129
65°	98	120	146	164	170	98
75°	54	79	107	126	132	58
85°	16	43	72	90	96	17
90°	4	30	58	76	81	3
95°	4	24	51	68	73	3
105°	2	15	38	54	58	3
115°	2	7	26	40	45	2
125°	1	1	15	27	31	1
135°	0	0	5	14	18	0
145°	0	0	0	3	5	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P995776

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	305.1	305.1	305.1	305.1	305.1
2.5°	307.3	305.9	302.8	305.1	304.2
5°	305.9	304.6	302.0	304.6	304.2
7.5°	303.7	302.8	300.6	303.7	303.3
10°	301.1	300.2	298.9	302.4	302.0
12.5°	296.7	297.1	296.2	299.8	299.3
15°	291.8	292.7	292.7	296.7	296.2
17.5°	285.6	287.4	288.7	292.7	292.7
20°	279.4	281.6	283.4	288.3	288.3
22.5°	272.8	275.4	278.1	283.0	283.8
25°	265.3	268.4	272.3	277.6	279.0
27.5°	256.4	261.3	265.7	272.3	273.2
30°	247.6	253.3	259.1	266.2	267.5
32.5°	237.9	244.5	251.6	260.0	262.6
35°	228.6	236.1	244.5	254.2	257.3
37.5°	218.4	226.8	237.4	248.0	251.1
40°	208.2	218.0	229.9	241.4	245.4
42.5°	198.5	208.2	222.4	235.2	239.2
45°	187.5	199.4	214.9	228.6	233.0
47.5°	176.8	189.7	207.4	221.5	226.4
50°	165.8	179.5	199.4	214.4	219.3
52.5°	155.2	169.8	191.0	206.5	211.8
55°	143.7	159.6	182.6	198.5	204.3
57.5°	132.6	150.3	173.3	190.6	196.3
60°	120.7	139.7	164.9	181.7	187.9
62.5°	110.1	130.0	155.2	173.3	179.1
65°	98.1	119.8	145.9	164.0	169.8
67.5°	87.5	110.1	136.6	154.7	160.9
70°	76.0	99.0	126.4	145.5	150.8
72.5°	65.4	89.3	117.2	135.7	142.4
75°	54.4	79.1	107.4	126.4	132.2
77.5°	43.8	69.4	98.1	117.2	123.4
80°	33.2	60.1	88.9	107.4	113.6
82.5°	24.3	50.8	80.0	98.6	104.3
85°	15.9	43.3	71.6	90.2	96.4
87.5°	9.7	36.3	64.5	82.7	88.4
90°	4.4	30.1	58.4	76.0	81.3
92.5°	4.0	27.4	54.4	71.6	76.9
95°	3.5	24.3	50.8	67.6	72.9
97.5°	3.1	22.1	47.7	64.1	69.4
100°	3.1	19.5	44.2	60.6	65.4
102.5°	2.7	17.2	41.1	57.0	61.9
105°	2.2	15.0	38.0	53.5	58.4
107.5°	2.2	12.8	34.9	50.0	54.8
110°	1.8	10.6	32.3	46.4	51.3

TEST NUMBER: P995776

CATALOG NUMBER: S122DRP-B290DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.8	8.8	29.2	43.3	48.2
115°	1.8	6.6	26.5	39.8	44.7
117.5°	1.3	4.9	23.4	36.7	41.1
120°	1.3	3.1	20.8	33.2	38.0
122.5°	1.3	1.8	18.1	30.1	34.0
125°	0.9	0.9	15.0	27.0	30.9
127.5°	0.9	0.4	12.4	23.4	27.4
130°	0.9	0.4	9.7	20.3	23.9
132.5°	0.9	0.4	7.1	17.2	20.8
135°	0.4	0.4	4.9	14.1	17.7
137.5°	0.4	0.4	2.7	11.1	14.1
140°	0.4	0.0	0.9	8.0	10.6
142.5°	0.4	0.0	0.0	5.3	7.5
145°	0.0	0.0	0.0	2.7	4.9
147.5°	0.0	0.0	0.0	0.4	1.8
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)