

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996130

Luminaire Tested: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct Perimeter with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4768.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996130

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P996130

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19719	19719	19719
5°	19812	19540	19676
10°	19679	19370	19490
15°	19450	19151	19187
20°	19181	18838	18857
25°	18821	18466	18428
30°	18424	18052	17915
35°	18009	17616	17387
40°	17575	17133	16867
45°	17098	16690	16282
50°	16618	16145	15696
55°	15993	15580	15107
60°	15362	14921	14447
65°	14805	14202	13761
70°	13980	13385	12790
75°	12776	12319	11790
80°	11523	11034	10934
85°	10115	9732	9337

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17098 cd/sqm

TEST NUMBER: P996130

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	3.6
10°-20°	487.7	10.2
20°-30°	720.3	15.1
30°-40°	841.2	17.6
40°-50°	845.7	17.7
50°-60°	742.9	15.6
60°-70°	553.3	11.6
70°-80°	314.9	6.6
80°-90°	89.5	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.7	29.0
0°-40°	2221.8	46.6
0°-60°	3810.4	79.9
0°-90°	4768.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4768.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1832	1832	1832	1832	1832	
5°	1834	1826	1808	1824	1821	174
15°	1745	1739	1719	1731	1722	492
25°	1585	1575	1555	1556	1552	730
35°	1370	1361	1341	1331	1323	857
45°	1123	1117	1096	1078	1070	867
55°	852	851	830	813	805	763
65°	581	573	558	545	540	573
75°	307	301	296	288	284	328
85°	82	79	79	76	76	93
90°	0	0	0	0	0	



TEST NUMBER: P996130

CATALOG NUMBER: S123DRP-B1165DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.0	1832.0	1832.0	1832.0	1832.0
2.5°	1839.9	1833.6	1816.3	1832.0	1830.5
5°	1833.6	1825.7	1808.4	1824.2	1821.0
7.5°	1819.4	1811.6	1794.2	1808.4	1806.8
10°	1800.5	1792.7	1772.2	1786.4	1783.2
12.5°	1775.3	1769.0	1750.1	1759.6	1758.0
15°	1745.4	1739.1	1718.6	1731.2	1721.8
17.5°	1712.3	1704.4	1684.0	1693.4	1690.3
20°	1674.5	1665.1	1644.6	1650.9	1646.2
22.5°	1632.0	1622.5	1602.1	1606.8	1600.5
25°	1584.7	1575.3	1554.8	1556.4	1551.6
27.5°	1535.9	1526.4	1504.4	1506.0	1501.2
30°	1482.3	1474.5	1452.4	1452.4	1441.4
32.5°	1428.8	1417.7	1402.0	1391.0	1386.2
35°	1370.5	1361.0	1340.6	1331.1	1323.2
37.5°	1312.2	1299.6	1279.1	1268.1	1263.4
40°	1250.8	1241.3	1219.3	1206.7	1200.4
42.5°	1189.3	1178.3	1156.3	1143.6	1137.3
45°	1123.2	1116.9	1096.4	1077.5	1069.6
47.5°	1058.6	1049.1	1030.2	1011.3	1005.0
50°	992.4	984.5	964.1	946.7	937.3
52.5°	923.1	918.4	896.3	882.2	872.7
55°	852.2	850.6	830.2	812.8	805.0
57.5°	786.1	779.8	764.0	748.3	738.8
60°	713.6	712.0	693.1	678.9	671.1
62.5°	649.0	644.3	625.4	611.2	606.5
65°	581.3	573.4	557.6	545.0	540.3
67.5°	508.8	502.5	489.9	478.9	472.6
70°	444.2	434.8	425.3	414.3	406.4
72.5°	376.5	370.2	359.2	349.7	346.6
75°	307.2	300.9	296.2	288.3	283.5
77.5°	245.7	242.6	236.3	230.0	230.0
80°	185.9	181.2	178.0	176.4	176.4
82.5°	127.6	127.6	127.6	124.4	122.9
85°	81.9	78.8	78.8	75.6	75.6
87.5°	41.0	36.2	34.7	33.1	33.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)