

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996155

Luminaire Tested: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-15)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct Perimeter with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1399.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996155

CATALOG NUMBER: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P996155

CATALOG NUMBER: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	113	113	113	113	106	106	106	100	100	100	94	94	94	94	94	92
1	105	100	95	90	102	97	92	88	91	87	84	85	82	80	80	78	76	76	76	73
2	95	86	79	72	92	83	77	71	79	73	68	74	69	65	70	66	63	63	63	60
3	86	75	67	60	83	73	65	59	69	62	56	65	59	54	61	56	52	52	52	50
4	79	66	57	50	76	64	56	49	61	54	48	57	51	46	54	49	45	45	45	42
5	72	59	50	43	70	58	49	42	54	47	41	52	45	40	49	43	39	39	39	36
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	44	38	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	42	36	31	40	35	30	30	30	28
8	58	44	35	29	56	43	35	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	37	30	25	36	29	25	34	28	24	24	24	22
10	50	37	29	24	49	36	29	24	35	28	23	33	27	23	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4481	4481	4481
5°	4502	4464	4498
10°	4470	4456	4495
15°	4422	4432	4478
20°	4347	4389	4441
25°	4254	4324	4394
30°	4160	4278	4345
35°	4051	4225	4338
40°	3950	4193	4326
45°	3838	4176	4363
50°	3728	4176	4404
55°	3609	4196	4493
60°	3494	4247	4626
65°	3385	4343	4804
70°	3210	4510	5108
75°	2999	4828	5677
80°	2783	5622	6856
85°	2742	8509	10979

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 19593 cd/sqm

TEST NUMBER: P996155

CATALOG NUMBER: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	2.8
10°-20°	112.6	8.0
20°-30°	168.3	12.0
30°-40°	201.0	14.4
40°-50°	210.3	15.0
50°-60°	197.3	14.1
60°-70°	164.8	11.8
70°-80°	117.9	8.4
80°-90°	70.1	5.0
90°-100°	44.1	3.2
100°-110°	32.4	2.3
110°-120°	21.6	1.5
120°-130°	12.3	0.9
130°-140°	5.5	0.4
140°-150°	1.2	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.4	22.9
0°-40°	521.4	37.3
0°-60°	929.0	66.4
0°-90°	1281.8	91.6
90°-120°	98.1	7.0
90°-150°	117.1	8.4
90°-180°	117.0	8.4
0°-180°	1399.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	416	416	416	416	416	
5°	417	416	413	417	416	40
15°	397	398	398	402	402	112
25°	358	363	364	370	370	165
35°	308	316	322	328	330	193
45°	252	263	274	283	287	194
55°	192	207	224	236	239	172
65°	133	150	170	184	189	131
75°	72	93	116	131	136	77
85°	22	45	69	84	89	23
90°	6	28	51	67	71	4
95°	5	23	45	59	64	4
105°	4	14	34	47	51	4
115°	2	8	24	35	38	2
125°	1	1	14	24	27	1
135°	1	0	5	14	16	1
145°	0	0	0	4	5	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P996155

CATALOG NUMBER: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	416.3	416.3	416.3	416.3	416.3
2.5°	418.5	417.2	413.6	417.2	416.7
5°	416.7	415.8	413.1	416.7	416.3
7.5°	413.6	413.6	410.8	415.4	414.9
10°	409.0	409.9	407.7	412.2	411.3
12.5°	403.6	404.9	403.6	407.7	406.7
15°	396.8	398.1	397.7	402.2	401.8
17.5°	388.6	391.3	390.9	395.0	394.1
20°	379.5	382.3	383.2	387.3	387.7
22.5°	370.0	372.7	374.1	379.5	379.1
25°	358.2	362.8	364.1	370.0	370.0
27.5°	346.9	351.9	354.6	359.6	360.0
30°	334.7	340.5	344.2	349.6	349.6
32.5°	321.0	327.8	332.8	338.7	340.1
35°	308.3	315.6	321.5	328.3	330.1
37.5°	294.7	302.9	309.7	317.4	318.8
40°	281.1	289.3	298.4	306.1	307.9
42.5°	266.2	276.6	286.1	294.7	297.5
45°	252.1	263.0	274.3	283.0	286.6
47.5°	237.2	249.4	262.1	271.6	274.3
50°	222.6	235.3	249.4	259.8	263.0
52.5°	207.2	220.8	236.7	247.6	251.7
55°	192.3	207.2	223.6	235.8	239.4
57.5°	177.8	193.2	210.9	223.1	227.2
60°	162.3	178.7	197.3	209.9	214.9
62.5°	147.8	164.6	184.6	197.3	201.8
65°	132.9	150.5	170.5	184.1	188.6
67.5°	117.9	136.5	156.4	171.4	175.0
70°	102.0	121.5	143.3	157.8	162.3
72.5°	87.5	107.0	129.7	144.7	149.2
75°	72.1	93.4	116.1	131.0	136.5
77.5°	58.9	80.3	102.9	118.8	122.9
80°	44.9	67.1	90.7	106.1	110.6
82.5°	32.6	55.3	79.4	94.8	99.3
85°	22.2	44.9	68.9	84.3	88.9
87.5°	13.6	36.3	59.4	74.8	79.4
90°	5.9	28.1	51.2	66.7	71.2
92.5°	5.4	24.9	47.6	62.6	66.7
95°	5.0	22.7	44.9	58.9	63.5
97.5°	4.5	20.9	42.2	55.8	60.3
100°	4.1	18.6	39.5	52.6	57.1
102.5°	3.6	16.3	36.7	49.4	54.0
105°	3.6	14.5	34.0	46.7	50.8
107.5°	3.2	12.7	31.3	43.5	47.6
110°	2.7	10.9	29.0	40.8	44.4



TEST NUMBER: P996155

CATALOG NUMBER: S123DRP-B340DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	2.7	9.1	26.3	37.6	41.7
115°	2.3	7.7	24.0	34.9	38.5
117.5°	2.3	5.9	21.3	32.2	35.8
120°	1.8	4.1	19.0	29.5	32.6
122.5°	1.8	2.7	16.8	26.8	29.9
125°	1.4	1.4	14.5	24.0	27.2
127.5°	1.4	0.9	12.2	21.3	24.5
130°	1.4	0.9	10.0	18.6	21.3
132.5°	0.9	0.9	7.7	15.9	19.0
135°	0.9	0.5	5.4	13.6	15.9
137.5°	0.9	0.5	3.6	10.9	13.2
140°	0.5	0.5	1.8	8.6	10.9
142.5°	0.5	0.0	0.0	5.9	8.2
145°	0.5	0.0	0.0	3.6	5.4
147.5°	0.0	0.0	0.0	1.4	3.2
150°	0.0	0.0	0.0	0.0	0.9
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)