

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996483

Luminaire Tested: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct Perimeter with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4929.0 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996483

CATALOG NUMBER: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P996483

CATALOG NUMBER: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70
4	83	71	63	56	81	70	62	56	67	60	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	52	43	37	50	43	37		49	42	37		47
8	61	48	39	34	60	47	39	34	46	39	33		45	38	33		43
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15707	15517	15631
10°	15608	15391	15468
15°	15420	15173	15212
20°	15169	14902	14915
25°	14884	14592	14551
30°	14533	14228	14098
35°	14170	13847	13664
40°	13792	13415	13170
45°	13398	12990	12741
50°	12961	12610	12221
55°	12491	12120	11726
60°	12021	11570	11217
65°	11490	11045	10599
70°	10896	10345	9942
75°	9988	9502	9260
80°	8889	8528	8312
85°	7775	7485	7345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13398 cd/sqm

TEST NUMBER: P996483

CATALOG NUMBER: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	3.7
10°-20°	509.9	10.3
20°-30°	750.5	15.2
30°-40°	872.4	17.7
40°-50°	872.3	17.7
50°-60°	763.0	15.5
60°-70°	566.4	11.5
70°-80°	321.4	6.5
80°-90°	92.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1441.4	29.2
0°-40°	2313.8	46.9
0°-60°	3949.1	80.1
0°-90°	4929.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4929.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	95
90°	0	0	0	0	0	



TEST NUMBER: P996483

CATALOG NUMBER: S124DRP-B1195DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)