

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996696

Luminaire Tested: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct Perimeter with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4124.0 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996696

CATALOG NUMBER: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P996696

CATALOG NUMBER: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	110	105	101	98	107	103	99	96	99	96	93		95	92	90		91	89	87		85
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	74		72
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64		62
4	84	73	65	58	82	72	64	58	69	62	57		67	61	56		65	60	56		54
5	78	66	57	51	76	65	56	50	62	55	50		61	54	49		59	53	49		47
6	72	59	51	45	70	58	50	44	57	49	44		55	49	44		53	48	43		41
7	67	54	46	40	65	53	45	40	52	45	39		50	44	39		49	43	39		37
8	63	50	41	36	61	49	41	36	48	40	35		46	40	35		45	39	35		33
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42	36	32		30
10	55	42	35	29	54	42	34	29	41	34	29		40	33	29		39	33	29		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14554	14554	14554
5°	14588	14408	14498
10°	14495	14235	14235
15°	14329	13937	13833
20°	14101	13543	13294
25°	13808	13083	12751
30°	13524	12598	12070
35°	13210	12094	11387
40°	12831	11522	10649
45°	12482	10953	9897
50°	12084	10299	9102
55°	11658	9618	8237
60°	11188	8870	7355
65°	10759	7938	6487
70°	10133	6907	5508
75°	9345	5728	4477
80°	8152	4363	4109
85°	6905	3967	3705

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12482 cd/sqm

TEST NUMBER: P996696

CATALOG NUMBER: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.8	4.1
10°-20°	467.9	11.3
20°-30°	675.6	16.4
30°-40°	765.7	18.6
40°-50°	739.3	17.9
50°-60°	614.6	14.9
60°-70°	424.2	10.3
70°-80°	214.4	5.2
80°-90°	54.4	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1311.4	31.8
0°-40°	2077.1	50.4
0°-60°	3431.0	83.2
0°-90°	4124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4124.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1785	1785	1785	1785	1785	
5°	1782	1777	1760	1774	1771	169
15°	1697	1685	1651	1648	1639	478
25°	1535	1510	1454	1431	1417	707
35°	1327	1283	1215	1168	1144	829
45°	1082	1032	950	883	858	835
55°	820	765	676	605	579	734
65°	558	499	411	353	336	551
75°	297	246	182	150	142	313
85°	74	46	42	40	40	85
90°	0	0	0	0	0	

TEST NUMBER: P996696

CATALOG NUMBER: S124RDRP-B1020DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.8	1784.8	1784.8	1784.8	1784.8
2.5°	1790.3	1784.8	1769.8	1784.8	1783.4
5°	1782.1	1776.6	1760.2	1773.9	1771.1
7.5°	1769.8	1764.3	1743.8	1753.4	1749.3
10°	1750.6	1743.8	1719.2	1724.7	1719.2
12.5°	1726.0	1717.8	1687.8	1690.5	1682.3
15°	1697.3	1685.0	1650.9	1648.2	1638.6
17.5°	1664.5	1646.8	1607.2	1600.3	1586.7
20°	1624.9	1607.2	1560.7	1549.8	1532.0
22.5°	1581.2	1560.7	1510.1	1492.4	1478.7
25°	1534.7	1510.1	1454.1	1430.9	1417.2
27.5°	1486.9	1456.8	1398.1	1370.7	1351.6
30°	1436.3	1402.2	1337.9	1303.8	1281.9
32.5°	1383.0	1343.4	1276.4	1235.4	1214.9
35°	1327.0	1283.3	1214.9	1168.5	1143.9
37.5°	1268.2	1223.1	1148.0	1097.4	1072.8
40°	1205.4	1160.3	1082.4	1025.0	1000.4
42.5°	1145.2	1097.4	1015.4	956.6	930.7
45°	1082.4	1031.8	949.8	882.8	858.2
47.5°	1018.1	966.2	881.5	811.8	784.4
50°	952.5	899.2	811.8	743.4	717.5
52.5°	885.6	833.6	743.4	673.7	646.4
55°	820.0	765.3	676.5	605.4	579.4
57.5°	755.7	698.3	610.9	538.5	519.3
60°	686.0	631.4	543.9	472.9	451.0
62.5°	623.2	565.8	475.6	411.4	395.0
65°	557.6	498.8	411.4	352.6	336.2
67.5°	489.3	433.2	351.2	299.3	280.2
70°	425.0	367.6	289.7	244.6	231.0
72.5°	356.7	306.1	233.7	196.8	184.5
75°	296.6	246.0	181.8	150.3	142.1
77.5°	233.7	190.0	135.3	113.4	110.7
80°	173.6	133.9	92.9	88.8	87.5
82.5°	121.6	86.1	67.0	64.2	62.9
85°	73.8	46.5	42.4	39.6	39.6
87.5°	31.4	20.5	19.1	17.8	19.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)