

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055614

Luminaire Tested: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B
Description: DEFINE 3, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
CORE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 389.0 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 0.7 / 0.86
Luminous Opening: Rectangular (W 0.23' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 12.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055614

CATALOG NUMBER: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1055614

CATALOG NUMBER: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | |
| 1 | 112 | 108 | 105 | 103 | 109 | 106 | 104 | 101 | 102 | 100 | 98 | 98 | 97 | 95 | 95 | 93 | 92 | 90 | | | | |
| 2 | 105 | 99 | 94 | 89 | 102 | 97 | 92 | 88 | 93 | 90 | 86 | 90 | 87 | 84 | 88 | 85 | 83 | 81 | | | | |
| 3 | 98 | 90 | 84 | 79 | 96 | 88 | 83 | 78 | 86 | 81 | 77 | 83 | 79 | 76 | 81 | 77 | 74 | 73 | | | | |
| 4 | 92 | 82 | 75 | 70 | 90 | 81 | 75 | 70 | 79 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 67 | 65 | | | | |
| 5 | 86 | 76 | 69 | 63 | 84 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 66 | 62 | 69 | 65 | 61 | 59 | | | | |
| 6 | 81 | 70 | 63 | 58 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | 66 | 61 | 56 | 64 | 60 | 56 | 54 | | | | |
| 7 | 76 | 65 | 58 | 53 | 74 | 64 | 57 | 52 | 63 | 57 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 50 | | | | |
| 8 | 71 | 60 | 53 | 48 | 70 | 60 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 46 | | | | |
| 9 | 68 | 56 | 49 | 45 | 66 | 56 | 49 | 45 | 55 | 49 | 45 | 54 | 48 | 44 | 53 | 48 | 44 | 43 | | | | |
| 10 | 64 | 53 | 46 | 42 | 63 | 52 | 46 | 42 | 51 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 40 | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|------|------|------|
| 0° | 4008 | 4008 | 4008 |
| 5° | 3965 | 3927 | 3914 |
| 10° | 3935 | 3728 | 3571 |
| 15° | 3878 | 3435 | 3077 |
| 20° | 3809 | 3048 | 2451 |
| 25° | 3729 | 2582 | 1808 |
| 30° | 3629 | 2092 | 1186 |
| 35° | 3522 | 1594 | 649 |
| 40° | 3407 | 1102 | 222 |
| 45° | 3275 | 641 | 130 |
| 50° | 3144 | 251 | 77 |
| 55° | 3008 | 160 | 36 |
| 60° | 2853 | 99 | 17 |
| 65° | 2656 | 48 | 9 |
| 70° | 2383 | 25 | 11 |
| 75° | 2022 | 14 | 14 |
| 80° | 1507 | 21 | 0 |
| 85° | 567 | 0 | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3275 cd/sqm



TEST NUMBER: P1055614

CATALOG NUMBER: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 30.5 | 7.8 |
| 10°-20° | 77.3 | 19.9 |
| 20°-30° | 92.3 | 23.7 |
| 30°-40° | 78.3 | 20.1 |
| 40°-50° | 53.2 | 13.7 |
| 50°-60° | 33.0 | 8.5 |
| 60°-70° | 16.7 | 4.3 |
| 70°-80° | 6.8 | 1.7 |
| 80°-90° | 1.0 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 200.1 | 51.4 |
| 0°-40° | 278.3 | 71.6 |
| 0°-60° | 364.5 | 93.7 |
| 0°-90° | 389.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 389.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0° | 332 | 332 | 332 | 332 | 332 | |
| 5° | 328 | 331 | 324 | 322 | 323 | 31 |
| 15° | 311 | 303 | 275 | 253 | 246 | 88 |
| 25° | 280 | 254 | 194 | 150 | 136 | 129 |
| 35° | 239 | 192 | 108 | 58 | 44 | 150 |
| 45° | 192 | 126 | 38 | 9 | 8 | 148 |
| 55° | 143 | 63 | 8 | 3 | 2 | 128 |
| 65° | 93 | 16 | 2 | 0 | 0 | 92 |
| 75° | 43 | 3 | 0 | 0 | 0 | 46 |
| 85° | 4 | 0 | 0 | 0 | 0 | 7 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P1055614

CATALOG NUMBER: S123R3DR-S340D927-X4F0-XX-UDD-FLL-B

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° |
|-------|-------|-------|-------|-------|-------|
| 0° | 332.4 | 332.4 | 332.4 | 332.4 | 332.4 |
| 2.5° | 329.3 | 333.8 | 330.0 | 329.6 | 330.0 |
| 5° | 327.6 | 330.7 | 324.5 | 322.0 | 323.4 |
| 7.5° | 325.1 | 326.5 | 316.2 | 310.0 | 310.0 |
| 10° | 321.4 | 320.3 | 304.5 | 294.1 | 291.7 |
| 12.5° | 316.2 | 312.0 | 291.4 | 275.2 | 270.7 |
| 15° | 310.7 | 302.7 | 275.2 | 253.4 | 246.5 |
| 17.5° | 304.5 | 292.4 | 257.6 | 229.3 | 219.3 |
| 20° | 296.9 | 280.7 | 237.6 | 203.1 | 191.0 |
| 22.5° | 288.9 | 267.9 | 216.5 | 176.2 | 162.7 |
| 25° | 280.3 | 254.1 | 194.1 | 150.0 | 135.9 |
| 27.5° | 270.7 | 239.6 | 172.1 | 124.8 | 109.3 |
| 30° | 260.7 | 224.5 | 150.3 | 100.7 | 85.2 |
| 32.5° | 250.0 | 208.6 | 128.6 | 78.6 | 64.1 |
| 35° | 239.3 | 192.1 | 108.3 | 58.3 | 44.1 |
| 37.5° | 227.9 | 175.5 | 88.6 | 40.3 | 27.9 |
| 40° | 216.5 | 159.3 | 70.0 | 25.5 | 14.1 |
| 42.5° | 204.8 | 142.4 | 53.1 | 12.8 | 9.7 |
| 45° | 192.1 | 125.9 | 37.6 | 9.3 | 7.6 |
| 47.5° | 180.0 | 110.0 | 24.8 | 7.6 | 5.9 |
| 50° | 167.6 | 94.1 | 13.4 | 5.5 | 4.1 |
| 52.5° | 155.2 | 79.0 | 9.7 | 4.1 | 2.8 |
| 55° | 143.1 | 63.4 | 7.6 | 2.8 | 1.7 |
| 57.5° | 130.7 | 50.0 | 5.9 | 1.7 | 1.0 |
| 60° | 118.3 | 36.9 | 4.1 | 1.0 | 0.7 |
| 62.5° | 105.9 | 25.5 | 2.8 | 0.7 | 0.3 |
| 65° | 93.1 | 15.5 | 1.7 | 0.3 | 0.3 |
| 67.5° | 80.0 | 10.7 | 1.0 | 0.3 | 0.3 |
| 70° | 67.6 | 7.6 | 0.7 | 0.3 | 0.3 |
| 72.5° | 55.2 | 4.8 | 0.3 | 0.3 | 0.0 |
| 75° | 43.4 | 2.8 | 0.3 | 0.3 | 0.3 |
| 77.5° | 32.1 | 1.0 | 0.3 | 0.3 | 0.0 |
| 80° | 21.7 | 0.3 | 0.3 | 0.3 | 0.0 |
| 82.5° | 12.1 | 0.0 | 0.3 | 0.3 | 0.0 |
| 85° | 4.1 | 0.0 | 0.0 | 0.3 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.3 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)