

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996858

Luminaire Tested: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-17)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K
Description: Define 5 Direct Perimeter with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1367.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996858

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P996858

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	94
1	106	101	96	92	103	98	94	90	93	89	86	88	85	82	83	81	79	79	79	76
2	96	88	80	74	93	85	78	73	81	75	70	76	72	68	72	69	65	65	65	63
3	88	77	68	61	84	75	67	60	71	64	59	67	61	57	64	59	55	55	55	53
4	80	68	59	52	77	66	58	51	63	55	50	60	53	48	57	51	47	47	47	45
5	74	60	51	44	71	59	50	44	56	49	43	53	47	42	51	45	41	41	41	39
6	68	54	45	39	66	53	45	38	51	43	38	48	42	37	46	40	36	36	36	34
7	63	49	40	34	61	48	40	34	46	39	33	44	37	33	42	36	32	32	32	30
8	59	45	36	30	57	44	36	30	42	35	30	40	34	29	39	33	29	29	29	27
9	55	41	33	27	53	40	33	27	39	32	27	37	31	26	36	30	26	26	26	24
10	51	38	30	25	50	37	30	25	36	29	24	35	28	24	33	28	23	23	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2827	2827	2827
5°	2838	2813	2832
10°	2823	2801	2818
15°	2795	2778	2783
20°	2755	2740	2749
25°	2707	2698	2694
30°	2647	2647	2650
35°	2592	2605	2616
40°	2537	2562	2584
45°	2474	2536	2568
50°	2415	2510	2570
55°	2344	2499	2571
60°	2267	2489	2588
65°	2191	2498	2623
70°	2107	2505	2707
75°	1971	2592	2859
80°	1804	2826	3240
85°	1750	3911	4867

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 8328 cd/sqm

TEST NUMBER: P996858

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.8	3.1
10°-20°	118.5	8.7
20°-30°	176.3	12.9
30°-40°	208.8	15.3
40°-50°	215.8	15.8
50°-60°	198.8	14.5
60°-70°	160.7	11.8
70°-80°	107.6	7.9
80°-90°	55.6	4.1
90°-100°	31.3	2.3
100°-110°	23.1	1.7
110°-120°	15.5	1.1
120°-130°	8.8	0.6
130°-140°	3.8	0.3
140°-150°	0.8	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.6	24.6
0°-40°	545.3	39.9
0°-60°	960.0	70.2
0°-90°	1283.8	93.9
90°-120°	69.8	5.1
90°-150°	83.2	6.1
90°-180°	83.0	6.1
0°-180°	1367.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	441	441	441	441	441	
5°	441	440	437	441	440	42
15°	421	422	419	421	420	119
25°	383	384	382	383	381	176
35°	331	334	333	334	334	207
45°	273	278	280	283	283	211
55°	210	217	224	228	230	188
65°	144	154	165	171	173	143
75°	80	91	105	113	116	84
85°	24	38	53	63	66	25
90°	7	21	36	45	48	5
95°	6	17	32	41	44	4
105°	4	11	24	32	36	4
115°	3	6	17	25	27	3
125°	2	1	10	17	19	1
135°	1	0	4	9	11	1
145°	0	0	0	2	4	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P996858

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	441.3	441.3	441.3	441.3	441.3
2.5°	442.6	441.7	438.7	441.7	441.3
5°	441.3	440.4	437.4	440.8	440.4
7.5°	438.2	437.8	434.8	437.8	437.4
10°	433.9	433.9	430.5	433.5	433.1
12.5°	427.9	428.3	425.7	427.9	426.6
15°	421.4	421.8	418.8	421.4	419.6
17.5°	413.2	414.0	411.0	413.2	411.9
20°	404.1	404.9	401.9	403.2	403.2
22.5°	393.7	395.4	392.0	393.7	392.4
25°	382.9	384.2	381.6	383.3	381.1
27.5°	371.2	372.9	369.9	371.2	370.3
30°	357.8	360.4	357.8	358.6	358.2
32.5°	345.7	347.8	346.1	347.0	346.5
35°	331.4	334.4	333.1	334.4	334.4
37.5°	317.5	320.1	319.7	321.4	321.0
40°	303.3	306.7	306.3	308.0	308.9
42.5°	287.7	292.5	293.8	295.9	295.9
45°	273.0	277.7	279.9	282.9	283.4
47.5°	257.8	262.2	265.6	270.0	270.8
50°	242.3	247.0	251.8	256.5	257.8
52.5°	225.8	231.9	237.9	243.1	244.0
55°	209.8	216.7	223.7	228.4	230.2
57.5°	193.4	201.6	209.4	214.6	215.9
60°	176.9	185.6	194.2	200.7	202.0
62.5°	160.9	169.6	179.1	186.5	188.2
65°	144.5	154.4	164.8	171.3	173.0
67.5°	129.4	138.9	149.3	157.0	159.2
70°	112.5	122.4	133.7	141.9	144.5
72.5°	96.0	106.4	119.0	128.1	129.8
75°	79.6	90.9	104.7	113.3	115.5
77.5°	63.6	76.6	89.6	99.1	100.8
80°	48.9	61.9	76.6	86.1	87.8
82.5°	35.5	49.3	64.5	73.5	77.0
85°	23.8	38.1	53.2	62.7	66.2
87.5°	15.1	29.0	43.7	53.6	56.7
90°	6.9	20.8	35.5	45.4	48.5
92.5°	6.1	18.6	33.7	43.3	46.3
95°	5.6	16.9	31.6	41.1	44.1
97.5°	5.2	15.6	29.9	38.9	42.0
100°	4.8	13.8	27.7	36.8	39.4
102.5°	4.3	12.5	26.0	34.6	37.2
105°	3.9	10.8	23.8	32.4	35.5
107.5°	3.5	9.5	22.1	30.7	33.3
110°	3.0	8.2	20.3	28.6	31.6

TEST NUMBER: P996858

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	3.0	6.9	18.6	26.4	29.4
115°	2.6	5.6	16.9	24.7	27.3
117.5°	2.2	4.3	15.1	22.5	25.5
120°	2.2	3.5	13.4	20.8	23.4
122.5°	1.7	2.2	11.7	18.6	21.2
125°	1.7	1.3	10.0	16.9	19.0
127.5°	1.3	0.9	8.2	14.7	17.3
130°	1.3	0.9	6.9	13.0	15.1
132.5°	0.9	0.9	5.2	11.2	13.0
135°	0.9	0.4	3.5	9.1	11.2
137.5°	0.9	0.4	2.2	7.4	9.1
140°	0.4	0.4	0.9	5.6	7.4
142.5°	0.4	0.0	0.0	3.9	5.6
145°	0.4	0.0	0.0	2.2	3.9
147.5°	0.0	0.0	0.0	0.9	1.7
150°	0.0	0.0	0.0	0.0	0.4
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)