

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996861

Luminaire Tested: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct Perimeter with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1486.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996861

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P996861

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84		
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70		
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59		
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51		
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44		
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39		
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34		
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31		
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28		
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3666	3631	3654
10°	3644	3606	3626
15°	3604	3563	3577
20°	3548	3502	3508
25°	3487	3429	3427
30°	3412	3351	3335
35°	3331	3268	3222
40°	3249	3177	3131
45°	3160	3094	3033
50°	3061	2994	2904
55°	2967	2881	2800
60°	2854	2767	2668
65°	2718	2629	2541
70°	2589	2471	2387
75°	2359	2280	2203
80°	2099	2066	2018
85°	1823	1860	1757

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3160 cd/sqm

TEST NUMBER: P996861

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	3.6
10°-20°	152.2	10.2
20°-30°	224.7	15.1
30°-40°	262.1	17.6
40°-50°	263.3	17.7
50°-60°	231.1	15.6
60°-70°	172.1	11.6
70°-80°	98.3	6.6
80°-90°	28.4	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.7	29.0
0°-40°	692.8	46.6
0°-60°	1187.2	79.9
0°-90°	1486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	29
90°	0	0	0	0	0	

TEST NUMBER: P996861

CATALOG NUMBER: S125DRP-B375DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)