

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P996885

Luminaire Tested: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P996885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-17)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct Perimeter with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2391.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P996885

CATALOG NUMBER: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P996885

CATALOG NUMBER: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	96	94
1	106	101	96	92	103	98	94	90	93	89	86	88	85	82	83	81	79	79	79	79	76
2	96	88	80	74	93	85	78	73	81	75	70	76	72	68	72	69	65	65	65	65	63
3	88	77	68	61	84	75	67	60	71	64	59	67	61	57	64	59	55	55	55	55	53
4	80	68	59	52	77	66	58	51	63	55	50	60	53	48	57	51	47	47	47	47	45
5	74	60	51	44	71	59	50	44	56	49	43	53	47	42	51	45	41	41	41	41	39
6	68	54	45	39	66	53	45	38	51	43	38	48	42	37	46	40	36	36	36	36	34
7	63	49	40	34	61	48	40	34	46	39	33	44	37	33	42	36	32	32	32	32	30
8	59	45	36	30	57	44	36	30	42	35	30	40	34	29	39	33	29	29	29	29	27
9	55	41	33	27	53	40	33	27	39	32	27	37	31	26	36	30	26	26	26	26	24
10	51	38	30	25	50	37	30	25	36	29	24	35	28	24	33	28	23	23	23	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4945	4945	4945
5°	4964	4920	4954
10°	4938	4898	4928
15°	4889	4859	4869
20°	4819	4793	4808
25°	4734	4718	4713
30°	4630	4630	4635
35°	4533	4558	4575
40°	4436	4481	4519
45°	4327	4436	4491
50°	4224	4390	4495
55°	4100	4370	4497
60°	3966	4354	4529
65°	3831	4371	4589
70°	3685	4380	4734
75°	3446	4533	5001
80°	3155	4941	5667
85°	3058	6844	8513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 14556 cd/sqm

TEST NUMBER: P996885

CATALOG NUMBER: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	3.1
10°-20°	207.3	8.7
20°-30°	308.3	12.9
30°-40°	365.1	15.3
40°-50°	377.5	15.8
50°-60°	347.7	14.5
60°-70°	281.1	11.8
70°-80°	188.1	7.9
80°-90°	97.2	4.1
90°-100°	54.8	2.3
100°-110°	40.4	1.7
110°-120°	27.0	1.1
120°-130°	15.3	0.6
130°-140°	6.7	0.3
140°-150°	1.3	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.7	24.6
0°-40°	953.8	39.9
0°-60°	1679.1	70.2
0°-90°	2245.5	93.9
90°-120°	122.1	5.1
90°-150°	145.5	6.1
90°-180°	145.0	6.1
0°-180°	2391.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	772	772	772	772	772	
5°	772	770	765	771	770	73
15°	737	738	732	737	734	208
25°	670	672	667	670	667	308
35°	580	585	583	585	585	363
45°	478	486	490	495	496	368
55°	367	379	391	400	403	328
65°	253	270	288	300	303	251
75°	139	159	183	198	202	148
85°	42	67	93	110	116	43
90°	12	36	62	80	85	8
95°	10	30	55	72	77	8
105°	7	19	42	57	62	7
115°	4	10	30	43	48	5
125°	3	2	17	30	33	3
135°	2	1	6	16	20	1
145°	1	0	0	4	7	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P996885

CATALOG NUMBER: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	771.8	771.8	771.8	771.8	771.8
2.5°	774.1	772.6	767.3	772.6	771.8
5°	771.8	770.3	765.0	771.1	770.3
7.5°	766.5	765.8	760.5	765.8	765.0
10°	759.0	759.0	752.9	758.2	757.5
12.5°	748.4	749.1	744.6	748.4	746.1
15°	737.0	737.8	732.5	737.0	734.0
17.5°	722.6	724.2	718.9	722.6	720.4
20°	706.8	708.3	703.0	705.2	705.2
22.5°	688.6	691.6	685.6	688.6	686.3
25°	669.7	671.9	667.4	670.4	666.7
27.5°	649.2	652.3	647.0	649.2	647.7
30°	625.8	630.3	625.8	627.3	626.5
32.5°	604.6	608.4	605.4	606.9	606.1
35°	579.6	584.9	582.7	584.9	584.9
37.5°	555.4	560.0	559.2	562.2	561.5
40°	530.4	536.5	535.7	538.8	540.3
42.5°	503.2	511.5	513.8	517.6	517.6
45°	477.5	485.8	489.6	494.9	495.6
47.5°	451.0	458.6	464.6	472.2	473.7
50°	423.8	432.1	440.4	448.7	451.0
52.5°	395.0	405.6	416.2	425.3	426.8
55°	367.0	379.1	391.2	399.5	402.6
57.5°	338.2	352.6	366.2	375.3	377.6
60°	309.5	324.6	339.8	351.1	353.4
62.5°	281.5	296.6	313.3	326.1	329.2
65°	252.7	270.1	288.3	299.7	302.7
67.5°	226.3	242.9	261.1	274.7	278.5
70°	196.7	214.1	233.8	248.2	252.7
72.5°	168.0	186.1	208.1	224.0	227.0
75°	139.2	158.9	183.1	198.3	202.0
77.5°	111.2	133.9	156.6	173.3	176.3
80°	85.5	108.2	133.9	150.6	153.6
82.5°	62.0	86.3	112.7	128.6	134.7
85°	41.6	66.6	93.1	109.7	115.8
87.5°	26.5	50.7	76.4	93.8	99.1
90°	12.1	36.3	62.0	79.5	84.8
92.5°	10.6	32.5	59.0	75.7	81.0
95°	9.8	29.5	55.2	71.9	77.2
97.5°	9.1	27.2	52.2	68.1	73.4
100°	8.3	24.2	48.4	64.3	68.9
102.5°	7.6	21.9	45.4	60.5	65.1
105°	6.8	18.9	41.6	56.8	62.0
107.5°	6.1	16.6	38.6	53.7	58.3
110°	5.3	14.4	35.6	49.9	55.2

TEST NUMBER: P996885

CATALOG NUMBER: S125DRP-B610DB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	5.3	12.1	32.5	46.2	51.5
115°	4.5	9.8	29.5	43.1	47.7
117.5°	3.8	7.6	26.5	39.3	44.6
120°	3.8	6.1	23.5	36.3	40.9
122.5°	3.0	3.8	20.4	32.5	37.1
125°	3.0	2.3	17.4	29.5	33.3
127.5°	2.3	1.5	14.4	25.7	30.3
130°	2.3	1.5	12.1	22.7	26.5
132.5°	1.5	1.5	9.1	19.7	22.7
135°	1.5	0.8	6.1	15.9	19.7
137.5°	1.5	0.8	3.8	12.9	15.9
140°	0.8	0.8	1.5	9.8	12.9
142.5°	0.8	0.0	0.0	6.8	9.8
145°	0.8	0.0	0.0	3.8	6.8
147.5°	0.0	0.0	0.0	1.5	3.0
150°	0.0	0.0	0.0	0.0	0.8
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)