

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055746

Luminaire Tested: S123R3DR-H340D850-X4F0-XX-UDD-F-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1055746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123R3DR-H340D850-X4F0-XX-UDD-F-B
Description: DEFINE 3, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 543.3 lumens
Efficiency: N/A
Efficacy: 46.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 0.7 / 0.86
Luminous Opening: Rectangular (W 0.23' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055746

CATALOG NUMBER: S123R3DR-H340D850-X4F0-XX-UDD-F-B

Luminous Intensity Polar Plot





TEST NUMBER: P1055746

CATALOG NUMBER: S123R3DR-H340D850-X4F0-XX-UDD-F-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	87	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	76	69	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	76	65	58	53	74	64	57	52	63	57	52	61	56	52	60	55	52	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	68	56	49	45	66	56	49	45	55	49	45	54	48	44	53	48	44	43
10	64	53	46	42	63	52	46	42	51	46	41	51	45	41	50	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5597	5597	5597
5°	5536	5484	5467
10°	5494	5205	4988
15°	5415	4797	4297
20°	5319	4257	3423
25°	5208	3606	2524
30°	5067	2922	1655
35°	4919	2225	907
40°	4759	1538	310
45°	4573	895	181
50°	4389	353	109
55°	4200	223	50
60°	3983	140	24
65°	3709	68	14
70°	3328	35	18
75°	2828	23	23
80°	2104	35	0
85°	802	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4573 cd/sqm



TEST NUMBER: P1055746

CATALOG NUMBER: S123R3DR-H340D850-X4F0-XX-UDD-F-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.6	7.8
10°-20°	108.0	19.9
20°-30°	128.8	23.7
30°-40°	109.3	20.1
40°-50°	74.3	13.7
50°-60°	46.0	8.5
60°-70°	23.3	4.3
70°-80°	9.5	1.8
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.4	51.4
0°-40°	388.7	71.5
0°-60°	509.0	93.7
0°-90°	543.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	464	464	464	464	464	
5°	457	462	453	450	452	43
15°	434	423	384	354	344	122
25°	392	355	271	210	190	180
35°	334	268	151	81	62	209
45°	268	176	52	13	11	207
55°	200	89	11	4	2	179
65°	130	22	2	0	0	128
75°	61	4	0	0	0	65
85°	6	0	0	0	0	10
90°	0	0	0	0	0	



TEST NUMBER: P1055746

CATALOG NUMBER: S123R3DR-H340D850-X4F0-XX-UDD-F-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	464.2	464.2	464.2	464.2	464.2
2.5°	459.8	466.1	460.8	460.3	460.8
5°	457.4	461.8	453.1	449.7	451.7
7.5°	454.1	456.0	441.6	432.9	432.9
10°	448.8	447.3	425.2	410.7	407.4
12.5°	441.6	435.8	406.9	384.3	378.0
15°	433.8	422.8	384.3	353.9	344.3
17.5°	425.2	408.3	359.7	320.2	306.2
20°	414.6	392.0	331.8	283.6	266.8
22.5°	403.5	374.1	302.4	246.1	227.3
25°	391.5	354.9	271.1	209.5	189.7
27.5°	378.0	334.7	240.3	174.3	152.6
30°	364.0	313.5	209.9	140.6	118.9
32.5°	349.1	291.3	179.6	109.8	89.6
35°	334.2	268.2	151.2	81.4	61.6
37.5°	318.3	245.1	123.8	56.3	39.0
40°	302.4	222.5	97.7	35.6	19.7
42.5°	286.0	198.9	74.2	17.8	13.5
45°	268.2	175.8	52.5	13.0	10.6
47.5°	251.4	153.6	34.7	10.6	8.2
50°	234.0	131.5	18.8	7.7	5.8
52.5°	216.7	110.3	13.5	5.8	3.9
55°	199.8	88.6	10.6	3.9	2.4
57.5°	182.5	69.8	8.2	2.4	1.4
60°	165.2	51.5	5.8	1.4	1.0
62.5°	147.8	35.6	3.9	1.0	0.5
65°	130.0	21.7	2.4	0.5	0.5
67.5°	111.7	14.9	1.4	0.5	0.5
70°	94.4	10.6	1.0	0.5	0.5
72.5°	77.0	6.7	0.5	0.5	0.0
75°	60.7	3.9	0.5	0.5	0.5
77.5°	44.8	1.4	0.5	0.5	0.0
80°	30.3	0.5	0.5	0.5	0.0
82.5°	16.9	0.0	0.5	0.5	0.0
85°	5.8	0.0	0.0	0.5	0.0
87.5°	0.0	0.0	0.0	0.5	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055746
 CATALOG NUMBER: S123R3DR-H340D850-X4F0-XX-UDD-F-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.03	16.31	15.39	16.62	16.94	0.00	0.00	0.00	0.00	0.00
	3H	16.97	18.11	17.35	18.44	18.80	0.00	0.00	0.00	0.00	0.00
	4H	17.80	18.86	18.21	19.21	19.59	0.00	0.00	0.00	0.00	0.00
	6H	18.36	19.33	18.77	19.70	20.09	0.00	0.00	0.00	0.00	0.00
	8H	18.48	19.40	18.91	19.79	20.20	0.00	0.00	0.00	0.00	0.00
	12H	18.51	19.38	18.94	19.77	20.20	0.00	0.00	0.00	0.00	0.00
4H	2H	14.79	15.85	15.20	16.20	16.58	0.00	0.00	0.00	0.00	0.00
	3H	16.75	17.61	17.16	18.01	18.42	0.00	0.00	0.00	0.00	0.00
	4H	17.56	18.33	18.00	18.75	19.19	0.00	0.00	0.00	0.00	0.00
	6H	18.16	18.82	18.63	19.27	19.74	0.00	0.00	0.00	0.00	0.00
	8H	18.31	18.93	18.78	19.38	19.85	0.00	0.00	0.00	0.00	0.00
	12H	18.36	18.91	18.85	19.39	19.86	0.00	0.00	0.00	0.00	0.00
8H	4H	17.42	18.04	17.89	18.48	18.96	0.00	0.00	0.00	0.00	0.00
	6H	18.00	18.50	18.50	19.00	19.48	0.00	0.00	0.00	0.00	0.00
	8H	18.15	18.60	18.67	19.12	19.61	0.00	0.00	0.00	0.00	0.00
	12H	18.21	18.60	18.72	19.10	19.67	0.00	0.00	0.00	0.00	0.00
12H	4H	17.37	17.91	17.86	18.40	18.87	0.00	0.00	0.00	0.00	0.00
	6H	17.94	18.39	18.46	18.90	19.40	0.00	0.00	0.00	0.00	0.00
	8H	18.10	18.50	18.62	19.00	19.57	0.00	0.00	0.00	0.00	0.00