

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055345

Luminaire Tested: S122R3DR-H485D927-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2024  
Report Number: P1055345  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122R3DR-H485D927-X4F0-XX-UDD-F-S  
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 512.2 lumens  
Efficiency: N/A  
Efficacy: 29.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81  
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1055345

CATALOG NUMBER: S122R3DR-H485D927-X4F0-XX-UDD-F-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1055345

CATALOG NUMBER: S122R3DR-H485D927-X4F0-XX-UDD-F-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8469	8469	8469
5°	8364	8334	8282
10°	8303	7818	7324
15°	8175	6994	5974
20°	8006	5996	4506
25°	7810	4913	3217
30°	7574	3835	2050
35°	7348	2812	1369
40°	7098	1897	1029
45°	6824	1334	734
50°	6537	1017	516
55°	6259	707	380
60°	5957	477	311
65°	5523	345	247
70°	5035	271	210
75°	4370	242	161
80°	3470	175	175
85°	1913	239	109

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6824 cd/sqm



TEST NUMBER: P1055345

CATALOG NUMBER: S122R3DR-H485D927-X4F0-XX-UDD-F-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.9	8.0
10°-20°	100.3	19.6
20°-30°	114.6	22.4
30°-40°	97.2	19.0
40°-50°	72.5	14.2
50°-60°	46.9	9.1
60°-70°	26.1	5.1
70°-80°	11.5	2.2
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.7	49.9
0°-40°	352.9	68.9
0°-60°	472.3	92.2
0°-90°	512.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	512.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	447	447	447	447	447	
5°	440	445	438	434	436	42
15°	417	406	357	319	305	117
25°	374	330	235	172	154	172
35°	318	239	122	66	59	199
45°	255	151	50	32	27	197
55°	190	72	21	13	12	169
65°	123	26	8	6	6	123
75°	60	6	3	3	2	64
85°	9	0	1	0	0	13
90°	0	0	0	0	0	



TEST NUMBER: P1055345

CATALOG NUMBER: S122R3DR-H485D927-X4F0-XX-UDD-F-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	447.0	447.0	447.0	447.0	447.0
2.5°	442.0	448.6	443.1	443.1	444.2
5°	439.8	445.3	438.2	433.8	435.5
7.5°	436.6	440.4	425.6	412.5	411.4
10°	431.6	433.3	406.4	386.2	380.7
12.5°	424.5	420.7	382.9	354.4	345.1
15°	416.8	406.4	356.6	318.8	304.6
17.5°	407.5	388.9	327.6	281.5	264.0
20°	397.1	370.8	297.4	242.7	223.5
22.5°	385.6	350.6	266.2	206.0	186.8
25°	373.6	329.7	235.0	172.0	153.9
27.5°	361.0	307.8	204.3	141.3	121.6
30°	346.2	285.4	175.3	111.7	93.7
32.5°	332.5	261.8	148.4	86.5	71.2
35°	317.7	239.4	121.6	66.3	59.2
37.5°	302.4	216.9	98.0	55.9	49.8
40°	287.0	194.5	76.7	47.1	41.6
42.5°	271.1	172.5	59.2	39.4	34.0
45°	254.7	151.2	49.8	32.3	27.4
47.5°	238.3	129.8	41.6	25.7	21.9
50°	221.8	109.6	34.5	20.3	17.5
52.5°	206.0	90.4	27.4	16.4	14.2
55°	189.5	71.8	21.4	13.1	11.5
57.5°	173.1	55.9	16.4	11.0	9.9
60°	157.2	42.2	12.6	8.8	8.2
62.5°	140.8	34.0	9.9	7.1	6.6
65°	123.2	26.3	7.7	6.0	5.5
67.5°	107.4	19.2	6.0	4.9	4.4
70°	90.9	13.1	4.9	4.4	3.8
72.5°	75.0	8.2	3.8	3.3	3.3
75°	59.7	5.5	3.3	2.7	2.2
77.5°	45.5	3.3	2.2	2.2	1.6
80°	31.8	2.2	1.6	1.6	1.6
82.5°	19.7	1.6	1.1	1.1	1.1
85°	8.8	0.5	1.1	0.5	0.5
87.5°	1.6	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055345  
 CATALOG NUMBER: S122R3DR-H485D927-X4F0-XX-UDD-F-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.68	17.00	16.04	17.31	17.62	2.01	3.33	2.38	3.64	3.96
	3H	18.14	19.32	18.52	19.65	20.01	2.85	4.02	3.23	4.35	4.72
	4H	19.10	20.19	19.50	20.54	20.93	3.12	4.22	3.53	4.57	4.95
	6H	19.79	20.79	20.20	21.16	21.56	3.30	4.31	3.72	4.68	5.07
	8H	19.98	20.93	20.41	21.33	21.73	3.38	4.33	3.81	4.72	5.12
	12H	20.07	20.97	20.50	21.36	21.79	3.40	4.31	3.83	4.69	5.12
4H	2H	15.46	16.55	15.86	16.90	17.29	2.58	3.68	2.99	4.03	4.41
	3H	17.94	18.84	18.36	19.24	19.65	3.61	4.50	4.02	4.90	5.31
	4H	18.89	19.69	19.32	20.11	20.55	3.97	4.77	4.40	5.19	5.63
	6H	19.64	20.33	20.11	20.78	21.25	4.25	4.94	4.71	5.38	5.85
	8H	19.89	20.53	20.36	20.98	21.45	4.34	4.99	4.81	5.43	5.90
	12H	20.01	20.58	20.50	21.07	21.54	4.38	4.95	4.87	5.43	5.91
8H	4H	18.75	19.40	19.22	19.85	20.32	4.34	4.98	4.80	5.43	5.90
	6H	19.49	20.02	20.00	20.52	21.00	4.68	5.20	5.18	5.70	6.18
	8H	19.74	20.21	20.26	20.72	21.22	4.82	5.29	5.34	5.80	6.30
	12H	19.89	20.30	20.40	20.80	21.37	4.89	5.30	5.41	5.80	6.37
12H	4H	18.71	19.28	19.20	19.76	20.24	4.46	5.03	4.94	5.51	5.98
	6H	19.43	19.90	19.96	20.42	20.91	4.80	5.27	5.32	5.79	6.28
	8H	19.70	20.11	20.21	20.61	21.18	4.98	5.39	5.49	5.89	6.46