

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055399

Luminaire Tested: S122R3DR-H865D927-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1055399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122R3DR-H865D927-X4F0-XX-UDD-F-S
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 925.2 lumens
Efficiency: N/A
Efficacy: 29.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055399

CATALOG NUMBER: S122R3DR-H865D927-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot





TEST NUMBER: P1055399

CATALOG NUMBER: S122R3DR-H865D927-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15295	15295	15295
5°	15108	15051	14958
10°	14998	14123	13228
15°	14768	12632	10790
20°	14462	10831	8137
25°	14104	8872	5811
30°	13677	6926	3702
35°	13271	5079	2470
40°	12821	3425	1860
45°	12325	2411	1326
50°	11810	1836	934
55°	11307	1275	687
60°	10757	864	561
65°	9979	623	444
70°	9096	493	382
75°	7891	432	293
80°	6263	327	327
85°	3435	435	217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12325 cd/sqm



TEST NUMBER: P1055399

CATALOG NUMBER: S122R3DR-H865D927-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	8.0
10°-20°	181.2	19.6
20°-30°	206.9	22.4
30°-40°	175.5	19.0
40°-50°	130.9	14.2
50°-60°	84.6	9.1
60°-70°	47.2	5.1
70°-80°	20.7	2.2
80°-90°	4.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.9	49.9
0°-40°	637.4	68.9
0°-60°	853.0	92.2
0°-90°	925.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	925.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	807	807	807	807	807	
5°	794	804	791	784	786	75
15°	753	734	644	576	550	212
25°	675	596	424	311	278	311
35°	574	432	220	120	107	359
45°	460	273	90	58	50	355
55°	342	130	39	24	21	306
65°	223	48	14	11	10	221
75°	108	10	6	5	4	115
85°	16	1	2	1	1	23
90°	0	0	0	0	0	



TEST NUMBER: P1055399

CATALOG NUMBER: S122R3DR-H865D927-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	807.3	807.3	807.3	807.3	807.3
2.5°	798.4	810.2	800.4	800.4	802.3
5°	794.4	804.3	791.4	783.5	786.5
7.5°	788.5	795.4	768.7	745.0	743.0
10°	779.6	782.5	734.1	697.5	687.6
12.5°	766.7	759.8	691.5	640.1	623.3
15°	752.9	734.1	644.0	575.8	550.1
17.5°	736.0	702.4	591.6	508.5	476.8
20°	717.3	669.8	537.2	438.3	403.6
22.5°	696.5	633.2	480.8	372.0	337.4
25°	674.7	595.6	424.4	310.6	278.0
27.5°	652.0	556.0	369.0	255.2	219.6
30°	625.2	515.4	316.6	201.8	169.2
32.5°	600.5	472.9	268.1	156.3	128.6
35°	573.8	432.3	219.6	119.7	106.8
37.5°	546.1	391.8	177.1	100.9	90.0
40°	518.4	351.2	138.5	85.1	75.2
42.5°	489.7	311.6	106.8	71.2	61.3
45°	460.0	273.0	90.0	58.4	49.5
47.5°	430.4	234.5	75.2	46.5	39.6
50°	400.7	197.9	62.3	36.6	31.7
52.5°	372.0	163.2	49.5	29.7	25.7
55°	342.3	129.6	38.6	23.7	20.8
57.5°	312.6	100.9	29.7	19.8	17.8
60°	283.9	76.2	22.8	15.8	14.8
62.5°	254.3	61.3	17.8	12.9	11.9
65°	222.6	47.5	13.9	10.9	9.9
67.5°	193.9	34.6	10.9	8.9	7.9
70°	164.2	23.7	8.9	7.9	6.9
72.5°	135.5	14.8	6.9	5.9	5.9
75°	107.8	9.9	5.9	4.9	4.0
77.5°	82.1	5.9	4.0	4.0	3.0
80°	57.4	4.0	3.0	3.0	3.0
82.5°	35.6	3.0	2.0	2.0	2.0
85°	15.8	1.0	2.0	1.0	1.0
87.5°	3.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055399

CATALOG NUMBER: S122R3DR-H865D927-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.73	19.05	18.09	19.36	19.67	4.04	5.36	4.41	5.67	5.99
	3H	20.20	21.37	20.58	21.70	22.06	4.89	6.06	5.27	6.39	6.75
	4H	21.15	22.24	21.55	22.59	22.98	5.16	6.25	5.56	6.60	6.99
	6H	21.84	22.84	22.25	23.21	23.61	5.36	6.36	5.77	6.73	7.13
	8H	22.03	22.99	22.47	23.38	23.78	5.44	6.39	5.87	6.78	7.18
	12H	22.12	23.03	22.55	23.41	23.84	5.46	6.37	5.89	6.75	7.18
4H	2H	17.51	18.60	17.91	18.96	19.34	4.62	5.71	5.02	6.06	6.44
	3H	20.00	20.89	20.41	21.29	21.70	5.64	6.54	6.05	6.94	7.34
	4H	20.94	21.74	21.37	22.16	22.60	6.01	6.81	6.44	7.23	7.67
	6H	21.69	22.38	22.16	22.83	23.30	6.31	7.00	6.77	7.44	7.91
	8H	21.94	22.58	22.41	23.03	23.50	6.41	7.05	6.88	7.50	7.97
	12H	22.07	22.63	22.55	23.12	23.59	6.46	7.02	6.94	7.51	7.98
8H	4H	20.81	21.45	21.28	21.90	22.37	6.38	7.02	6.85	7.47	7.94
	6H	21.55	22.07	22.05	22.57	23.05	6.75	7.27	7.25	7.77	8.25
	8H	21.79	22.26	22.31	22.78	23.27	6.89	7.36	7.41	7.88	8.37
	12H	21.94	22.35	22.46	22.85	23.42	6.98	7.39	7.49	7.89	8.46
12H	4H	20.76	21.33	21.25	21.81	22.29	6.50	7.07	6.99	7.55	8.03
	6H	21.48	21.96	22.01	22.47	22.96	6.87	7.34	7.39	7.85	8.35
	8H	21.75	22.16	22.26	22.66	23.23	7.05	7.47	7.57	7.96	8.53