

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055333

Luminaire Tested: S122R3DR-H485D830-X4F0-XX-UDD-F-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1055333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122R3DR-H485D830-X4F0-XX-UDD-F-S
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 609.5 lumens
Efficiency: N/A
Efficacy: 35.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 17.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055333

CATALOG NUMBER: S122R3DR-H485D830-X4F0-XX-UDD-F-S

Luminous Intensity Polar Plot



TEST NUMBER: P1055333

CATALOG NUMBER: S122R3DR-H485D830-X4F0-XX-UDD-F-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10075	10075	10075
5°	9952	9916	9853
10°	9881	9304	8713
15°	9729	8322	7108
20°	9526	7135	5361
25°	9292	5845	3828
30°	9011	4563	2437
35°	8743	3347	1628
40°	8446	2256	1224
45°	8121	1589	873
50°	7778	1211	616
55°	7449	839	453
60°	7086	568	371
65°	6572	408	291
70°	5994	327	255
75°	5197	285	190
80°	4124	218	218
85°	2261	283	152

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8121 cd/sqm



TEST NUMBER: P1055333

CATALOG NUMBER: S122R3DR-H485D830-X4F0-XX-UDD-F-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	8.0
10°-20°	119.3	19.6
20°-30°	136.3	22.4
30°-40°	115.6	19.0
40°-50°	86.3	14.2
50°-60°	55.7	9.1
60°-70°	31.1	5.1
70°-80°	13.7	2.2
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.3	49.9
0°-40°	419.9	68.9
0°-60°	561.9	92.2
0°-90°	609.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	523	530	521	516	518	50
15°	496	484	424	379	362	140
25°	444	392	280	205	183	205
35°	378	285	145	79	70	236
45°	303	180	59	38	33	234
55°	226	85	25	16	14	202
65°	147	31	9	7	6	146
75°	71	6	4	3	3	76
85°	10	1	1	1	1	15
90°	0	0	0	0	0	



TEST NUMBER: P1055333

CATALOG NUMBER: S122R3DR-H485D830-X4F0-XX-UDD-F-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	531.8	531.8	531.8	531.8	531.8
2.5°	525.9	533.8	527.2	527.2	528.5
5°	523.3	529.8	521.4	516.2	518.1
7.5°	519.4	524.0	506.4	490.7	489.4
10°	513.6	515.5	483.6	459.5	452.9
12.5°	505.1	500.5	455.6	421.7	410.6
15°	496.0	483.6	424.3	379.3	362.4
17.5°	484.9	462.7	389.7	335.0	314.1
20°	472.5	441.2	353.9	288.7	265.9
22.5°	458.8	417.1	316.7	245.0	222.2
25°	444.5	392.3	279.6	204.6	183.1
27.5°	429.5	366.3	243.1	168.1	144.7
30°	411.9	339.5	208.6	133.0	111.4
32.5°	395.6	311.5	176.6	103.0	84.7
35°	378.0	284.8	144.7	78.9	70.4
37.5°	359.8	258.1	116.7	66.5	59.3
40°	341.5	231.4	91.2	56.0	49.5
42.5°	322.6	205.3	70.4	46.9	40.4
45°	303.1	179.9	59.3	38.5	32.6
47.5°	283.5	154.5	49.5	30.6	26.1
50°	263.9	130.3	41.1	24.1	20.9
52.5°	245.0	107.5	32.6	19.6	16.9
55°	225.5	85.4	25.4	15.6	13.7
57.5°	205.9	66.5	19.6	13.0	11.7
60°	187.0	50.2	15.0	10.4	9.8
62.5°	167.5	40.4	11.7	8.5	7.8
65°	146.6	31.3	9.1	7.2	6.5
67.5°	127.7	22.8	7.2	5.9	5.2
70°	108.2	15.6	5.9	5.2	4.6
72.5°	89.3	9.8	4.6	3.9	3.9
75°	71.0	6.5	3.9	3.3	2.6
77.5°	54.1	3.9	2.6	2.6	2.0
80°	37.8	2.6	2.0	2.0	2.0
82.5°	23.5	2.0	1.3	1.3	1.3
85°	10.4	0.7	1.3	0.7	0.7
87.5°	2.0	0.7	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055333
 CATALOG NUMBER: S122R3DR-H485D830-X4F0-XX-UDD-F-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.28	17.60	16.64	17.91	18.23	2.57	3.89	2.93	4.20	4.52
	3H	18.75	19.92	19.13	20.25	20.61	3.43	4.60	3.81	4.93	5.29
	4H	19.70	20.79	20.10	21.14	21.53	3.70	4.80	4.11	5.15	5.53
	6H	20.39	21.39	20.80	21.76	22.16	3.91	4.91	4.32	5.28	5.67
	8H	20.59	21.54	21.02	21.93	22.33	3.98	4.93	4.41	5.32	5.73
	12H	20.67	21.58	21.10	21.96	22.39	4.01	4.92	4.44	5.30	5.73
4H	2H	16.06	17.16	16.47	17.51	17.89	3.14	4.23	3.54	4.58	4.97
	3H	18.55	19.44	18.96	19.84	20.25	4.18	5.08	4.59	5.48	5.88
	4H	19.49	20.29	19.92	20.71	21.15	4.56	5.36	4.99	5.77	6.22
	6H	20.24	20.93	20.71	21.38	21.85	4.86	5.55	5.32	6.00	6.46
	8H	20.49	21.13	20.96	21.58	22.05	4.96	5.60	5.43	6.05	6.52
	12H	20.62	21.19	21.10	21.67	22.14	5.01	5.58	5.50	6.06	6.54
8H	4H	19.36	20.00	19.83	20.45	20.92	4.93	5.57	5.40	6.02	6.49
	6H	20.10	20.62	20.60	21.12	21.60	5.30	5.83	5.80	6.32	6.80
	8H	20.34	20.81	20.86	21.33	21.82	5.44	5.91	5.96	6.43	6.92
	12H	20.49	20.91	21.01	21.40	21.97	5.53	5.95	6.05	6.44	7.02
12H	4H	19.31	19.88	19.80	20.36	20.84	5.05	5.62	5.54	6.10	6.58
	6H	20.03	20.51	20.56	21.02	21.51	5.42	5.89	5.94	6.41	6.90
	8H	20.30	20.71	20.81	21.21	21.78	5.60	6.02	6.12	6.51	7.08