

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056093

Luminaire Tested: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DR-H1020D835-X4F0-XX-UDD-F-W
Description: DEFINE 4, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3380.4 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.95 / 1.12
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056093

CATALOG NUMBER: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P1056093

CATALOG NUMBER: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	105	102	98	107	103	100	97	99	96	93	95	93	91	92	90	88					86				
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	76					73				
3	93	83	75	69	90	81	74	69	79	73	68	76	71	67	73	69	65					63				
4	85	74	66	60	83	73	65	60	71	64	59	68	63	58	66	61	57					55				
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51					49				
6	73	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45					43				
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41					39				
8	64	51	43	38	62	51	43	38	49	42	37	48	42	37	47	41	37					35				
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34					32				
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31					29				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15006	15006	15006
5°	14885	14853	14841
10°	14800	14408	14228
15°	14643	13866	13442
20°	14453	13207	12467
25°	14217	12451	11330
30°	13935	11589	10174
35°	13641	10689	9058
40°	13333	9758	8014
45°	13007	8854	7042
50°	12609	7902	6081
55°	12224	6949	5525
60°	11793	5963	5123
65°	11261	5408	4780
70°	10459	5005	4519
75°	9469	4608	4267
80°	8269	4262	4007
85°	6330	3926	3672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13007 cd/sqm



TEST NUMBER: P1056093

CATALOG NUMBER: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.0	4.7
10°-20°	428.6	12.7
20°-30°	593.5	17.6
30°-40°	637.0	18.8
40°-50°	579.3	17.1
50°-60°	456.2	13.5
60°-70°	312.2	9.2
70°-80°	168.1	5.0
80°-90°	47.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1180.1	34.9
0°-40°	1817.1	53.8
0°-60°	2852.5	84.4
0°-90°	3380.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3380.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1677	1696	1674	1665	1672	159
15°	1600	1582	1515	1474	1469	451
25°	1457	1398	1276	1184	1161	671
35°	1264	1165	990	870	839	791
45°	1040	908	708	586	563	802
55°	793	642	451	363	358	709
65°	538	385	258	230	228	531
75°	277	169	135	124	125	296
85°	62	42	39	36	36	75
90°	0	0	0	0	0	



TEST NUMBER: P1056093

CATALOG NUMBER: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1697.2	1697.2	1697.2	1697.2	1697.2
2.5°	1684.7	1704.7	1689.7	1692.2	1694.7
5°	1677.2	1695.9	1673.5	1664.7	1672.2
7.5°	1664.7	1677.2	1642.2	1626.0	1633.5
10°	1648.5	1651.0	1604.8	1581.0	1584.8
12.5°	1626.0	1619.8	1563.6	1529.8	1532.3
15°	1599.8	1582.3	1514.9	1473.6	1468.6
17.5°	1569.8	1541.1	1461.2	1408.7	1398.7
20°	1536.1	1497.4	1403.7	1336.3	1325.0
22.5°	1498.6	1448.7	1341.3	1261.3	1245.1
25°	1457.4	1397.5	1276.3	1183.9	1161.4
27.5°	1412.4	1342.5	1206.4	1105.2	1076.5
30°	1365.0	1285.1	1135.2	1026.6	996.6
32.5°	1316.3	1226.4	1062.8	947.9	916.7
35°	1263.8	1165.2	990.3	870.4	839.2
37.5°	1210.1	1101.5	916.7	795.5	763.0
40°	1155.2	1037.8	845.5	720.6	694.4
42.5°	1099.0	972.9	775.5	650.6	626.9
45°	1040.3	907.9	708.1	585.7	563.2
47.5°	980.3	841.7	639.4	524.5	503.3
50°	916.7	775.5	574.5	464.6	442.1
52.5°	855.5	708.1	512.0	405.9	394.6
55°	793.0	641.9	450.8	363.4	358.4
57.5°	730.6	575.7	394.6	329.7	324.7
60°	666.9	510.8	337.2	294.7	289.7
62.5°	603.2	447.1	294.7	261.0	258.5
65°	538.3	384.6	258.5	229.8	228.5
67.5°	469.6	324.7	226.0	202.3	201.1
70°	404.6	264.8	193.6	174.8	174.8
72.5°	343.4	209.8	163.6	148.6	148.6
75°	277.2	168.6	134.9	123.6	124.9
77.5°	218.5	132.4	108.6	101.2	101.2
80°	162.4	98.7	83.7	77.4	78.7
82.5°	109.9	68.7	59.9	56.2	56.2
85°	62.4	42.5	38.7	36.2	36.2
87.5°	22.5	20.0	18.7	16.2	17.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056093

CATALOG NUMBER: S124R3DR-H1020D835-X4F0-XX-UDD-F-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.55	22.08	20.92	22.39	22.70	16.33	17.85	16.69	18.17	18.48
	3H	22.33	23.70	22.70	24.02	24.39	17.94	19.31	18.32	19.64	20.00
	4H	23.00	24.28	23.40	24.63	25.01	18.57	19.86	18.97	20.21	20.58
	6H	23.51	24.70	23.92	25.06	25.45	19.07	20.26	19.48	20.63	21.02
	8H	23.67	24.80	24.10	25.19	25.59	19.24	20.37	19.67	20.76	21.16
	12H	23.77	24.85	24.20	25.24	25.67	19.36	20.45	19.79	20.83	21.26
4H	2H	20.65	21.93	21.05	22.28	22.66	17.05	18.33	17.45	18.68	19.06
	3H	22.59	23.66	23.00	24.06	24.46	18.85	19.92	19.27	20.32	20.73
	4H	23.35	24.31	23.78	24.73	25.16	19.59	20.56	20.02	20.97	21.41
	6H	23.98	24.82	24.44	25.26	25.72	20.21	21.05	20.67	21.49	21.95
	8H	24.20	24.99	24.66	25.43	25.90	20.42	21.21	20.89	21.65	22.12
	12H	24.36	25.06	24.84	25.54	26.01	20.59	21.29	21.07	21.77	22.24
8H	4H	23.40	24.19	23.87	24.63	25.10	19.98	20.77	20.44	21.21	21.68
	6H	24.10	24.75	24.60	25.24	25.72	20.71	21.36	21.21	21.85	22.33
	8H	24.37	24.95	24.89	25.46	25.95	21.00	21.58	21.51	22.09	22.58
	12H	24.59	25.10	25.10	25.60	26.16	21.25	21.76	21.76	22.25	22.82
12H	4H	23.40	24.10	23.88	24.58	25.05	20.04	20.74	20.52	21.22	21.69
	6H	24.10	24.68	24.61	25.19	25.68	20.79	21.38	21.31	21.89	22.38
	8H	24.41	24.92	24.91	25.41	25.98	21.14	21.66	21.65	22.15	22.72