

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055309

Luminaire Tested: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1055309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 406.0 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1055309

CATALOG NUMBER: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1055309

CATALOG NUMBER: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90					90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80					80			
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71					71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64					64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58					58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49					49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45					45			
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42					42			
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6713	6713	6713
5°	6632	6607	6565
10°	6581	6199	5806
15°	6481	5545	4735
20°	6347	4754	3573
25°	6190	3894	2550
30°	6003	3039	1623
35°	5824	2230	1085
40°	5627	1504	816
45°	5410	1058	581
50°	5182	808	410
55°	4961	558	301
60°	4721	379	246
65°	4380	273	193
70°	3994	216	166
75°	3462	190	124
80°	2749	142	142
85°	1500	196	87

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5410 cd/sqm



TEST NUMBER: P1055309

CATALOG NUMBER: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.4	8.0
10°-20°	79.5	19.6
20°-30°	90.8	22.4
30°-40°	77.0	19.0
40°-50°	57.5	14.2
50°-60°	37.1	9.1
60°-70°	20.7	5.1
70°-80°	9.1	2.2
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.7	49.9
0°-40°	279.7	68.9
0°-60°	374.3	92.2
0°-90°	406.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	406.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	354	354	354	354	354	
5°	349	353	347	344	345	33
15°	330	322	283	253	241	93
25°	296	261	186	136	122	136
35°	252	190	96	52	47	157
45°	202	120	40	26	22	156
55°	150	57	17	10	9	134
65°	98	21	6	5	4	97
75°	47	4	3	2	2	50
85°	7	0	1	0	0	10
90°	0	0	0	0	0	



TEST NUMBER: P1055309

CATALOG NUMBER: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	354.3	354.3	354.3	354.3	354.3
2.5°	350.4	355.6	351.3	351.3	352.1
5°	348.7	353.0	347.4	343.9	345.2
7.5°	346.1	349.1	337.4	326.9	326.1
10°	342.1	343.4	322.2	306.1	301.8
12.5°	336.5	333.5	303.5	280.9	273.5
15°	330.4	322.2	282.7	252.7	241.4
17.5°	323.0	308.3	259.6	223.2	209.3
20°	314.8	293.9	235.8	192.3	177.2
22.5°	305.7	277.9	211.0	163.3	148.1
25°	296.1	261.4	186.3	136.3	122.0
27.5°	286.1	244.0	162.0	112.0	96.4
30°	274.4	226.2	138.9	88.6	74.2
32.5°	263.6	207.5	117.7	68.6	56.4
35°	251.8	189.7	96.4	52.5	46.9
37.5°	239.7	171.9	77.7	44.3	39.5
40°	227.5	154.1	60.8	37.3	33.0
42.5°	214.9	136.8	46.9	31.3	26.9
45°	201.9	119.8	39.5	25.6	21.7
47.5°	188.9	102.9	33.0	20.4	17.4
50°	175.8	86.8	27.4	16.1	13.9
52.5°	163.3	71.6	21.7	13.0	11.3
55°	150.2	56.9	16.9	10.4	9.1
57.5°	137.2	44.3	13.0	8.7	7.8
60°	124.6	33.4	10.0	6.9	6.5
62.5°	111.6	26.9	7.8	5.6	5.2
65°	97.7	20.8	6.1	4.8	4.3
67.5°	85.1	15.2	4.8	3.9	3.5
70°	72.1	10.4	3.9	3.5	3.0
72.5°	59.5	6.5	3.0	2.6	2.6
75°	47.3	4.3	2.6	2.2	1.7
77.5°	36.0	2.6	1.7	1.7	1.3
80°	25.2	1.7	1.3	1.3	1.3
82.5°	15.6	1.3	0.9	0.9	0.9
85°	6.9	0.4	0.9	0.4	0.4
87.5°	1.3	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055309

CATALOG NUMBER: S122R3DR-H290D835-X4F0-XX-UDD-FLL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.87	16.19	15.23	16.50	16.82	1.18	2.50	1.55	2.81	3.13
	3H	17.34	18.51	17.72	18.84	19.20	2.03	3.20	2.41	3.53	3.90
	4H	18.29	19.38	18.69	19.73	20.12	2.30	3.40	2.71	3.75	4.13
	6H	18.98	19.98	19.39	20.35	20.75	2.49	3.49	2.91	3.87	4.26
	8H	19.17	20.12	19.60	20.51	20.92	2.57	3.52	3.00	3.91	4.32
	12H	19.25	20.16	19.69	20.55	20.98	2.59	3.50	3.03	3.89	4.32
4H	2H	14.65	15.74	15.06	16.10	16.48	1.76	2.85	2.16	3.20	3.58
	3H	17.14	18.03	17.55	18.44	18.84	2.79	3.68	3.20	4.09	4.49
	4H	18.08	18.88	18.51	19.30	19.74	3.16	3.96	3.59	4.38	4.82
	6H	18.83	19.52	19.30	19.97	20.44	3.44	4.13	3.90	4.58	5.05
	8H	19.08	19.72	19.54	20.17	20.64	3.55	4.19	4.02	4.64	5.11
	12H	19.20	19.77	19.69	20.25	20.73	3.59	4.16	4.08	4.64	5.12
8H	4H	17.95	18.59	18.42	19.04	19.51	3.52	4.16	3.99	4.61	5.08
	6H	18.68	19.21	19.19	19.70	20.19	3.88	4.40	4.38	4.90	5.38
	8H	18.93	19.40	19.45	19.91	20.41	4.02	4.50	4.55	5.01	5.50
	12H	19.08	19.49	19.59	19.98	20.56	4.10	4.52	4.62	5.01	5.58
12H	4H	17.90	18.47	18.39	18.95	19.43	3.64	4.21	4.13	4.69	5.17
	6H	18.62	19.09	19.15	19.61	20.10	4.00	4.47	4.52	4.98	5.47
	8H	18.89	19.30	19.40	19.80	20.37	4.19	4.60	4.70	5.10	5.67