

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1055366

Luminaire Tested: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

Issue Date: 7/25/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1055366  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/25/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S  
Description: DEFINE 2, SILVER 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 914.5 lumens  
Efficiency: N/A  
Efficacy: 38.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 0.64 / 0.81  
Luminous Opening: Rectangular (W 0.15' x L: 3.9' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P105366

CATALOG NUMBER: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

### Luminous Intensity Polar Plot





TEST NUMBER: P1055366

CATALOG NUMBER: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42
10	63	52	45	41	62	52	45	41	51	45	41	50	44	40	49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15119	15119	15119
5°	14935	14878	14785
10°	14825	13959	13076
15°	14597	12486	10664
20°	14295	10706	8045
25°	13941	8769	5745
30°	13520	6845	3658
35°	13119	5021	2442
40°	12673	3386	1838
45°	12183	2385	1310
50°	11675	1816	923
55°	11178	1258	677
60°	10636	853	557
65°	9863	614	439
70°	8990	487	377
75°	7803	432	285
80°	6186	316	316
85°	3391	435	217

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12183 cd/sqm



TEST NUMBER: P1055366

CATALOG NUMBER: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.0	8.0
10°-20°	179.1	19.6
20°-30°	204.6	22.4
30°-40°	173.5	19.0
40°-50°	129.4	14.2
50°-60°	83.7	9.1
60°-70°	46.6	5.1
70°-80°	20.5	2.2
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.6	49.9
0°-40°	630.1	68.9
0°-60°	843.2	92.2
0°-90°	914.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	798	798	798	798	798	
5°	785	795	782	774	777	75
15°	744	726	637	569	544	210
25°	667	589	420	307	275	307
35°	567	427	217	118	106	355
45°	455	270	89	58	49	351
55°	338	128	38	24	20	303
65°	220	47	14	11	10	219
75°	107	10	6	5	4	114
85°	16	1	2	1	1	22
90°	0	0	0	0	0	



TEST NUMBER: P1055366

CATALOG NUMBER: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	798.0	798.0	798.0	798.0	798.0
2.5°	789.2	800.9	791.1	791.1	793.1
5°	785.3	795.1	782.3	774.5	777.4
7.5°	779.4	786.3	759.8	736.4	734.4
10°	770.6	773.5	725.6	689.4	679.7
12.5°	757.9	751.0	683.6	632.7	616.1
15°	744.2	725.6	636.6	569.2	543.7
17.5°	727.6	694.3	584.8	502.7	471.4
20°	709.0	662.1	531.0	433.2	399.0
22.5°	688.5	625.9	475.3	367.7	333.5
25°	666.9	588.7	419.5	307.1	274.8
27.5°	644.5	549.6	364.8	252.3	217.1
30°	618.0	509.5	312.9	199.5	167.2
32.5°	593.6	467.4	265.0	154.5	127.1
35°	567.2	427.4	217.1	118.3	105.6
37.5°	539.8	387.3	175.0	99.7	89.0
40°	512.4	347.2	136.9	84.1	74.3
42.5°	484.1	308.0	105.6	70.4	60.6
45°	454.7	269.9	89.0	57.7	48.9
47.5°	425.4	231.8	74.3	46.0	39.1
50°	396.1	195.6	61.6	36.2	31.3
52.5°	367.7	161.4	48.9	29.3	25.4
55°	338.4	128.1	38.1	23.5	20.5
57.5°	309.0	99.7	29.3	19.6	17.6
60°	280.7	75.3	22.5	15.6	14.7
62.5°	251.3	60.6	17.6	12.7	11.7
65°	220.0	46.9	13.7	10.8	9.8
67.5°	191.7	34.2	10.8	8.8	7.8
70°	162.3	23.5	8.8	7.8	6.8
72.5°	134.0	14.7	6.8	5.9	5.9
75°	106.6	9.8	5.9	4.9	3.9
77.5°	81.2	5.9	3.9	3.9	2.9
80°	56.7	3.9	2.9	2.9	2.9
82.5°	35.2	2.9	2.0	2.0	2.0
85°	15.6	1.0	2.0	1.0	1.0
87.5°	2.9	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1055366  
 CATALOG NUMBER: S122R3DR-H675D840-X4F0-XX-UDD-FLL-S

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.69	19.01	18.05	19.32	19.63	4.01	5.33	4.37	5.64	5.96
	3H	20.16	21.33	20.54	21.66	22.02	4.85	6.02	5.23	6.35	6.72
	4H	21.11	22.20	21.52	22.56	22.94	5.13	6.22	5.53	6.57	6.95
	6H	21.80	22.80	22.22	23.17	23.57	5.31	6.32	5.73	6.69	7.08
	8H	22.00	22.95	22.43	23.34	23.74	5.39	6.34	5.82	6.73	7.14
	12H	22.08	22.99	22.51	23.37	23.80	5.42	6.32	5.85	6.71	7.14
4H	2H	17.47	18.56	17.87	18.91	19.30	4.58	5.67	4.98	6.02	6.40
	3H	19.96	20.85	20.37	21.25	21.66	5.60	6.50	6.02	6.90	7.31
	4H	20.90	21.70	21.33	22.12	22.56	5.97	6.77	6.41	7.19	7.63
	6H	21.66	22.35	22.12	22.79	23.26	6.26	6.95	6.72	7.39	7.86
	8H	21.90	22.54	22.37	22.99	23.46	6.36	7.00	6.83	7.45	7.92
	12H	22.03	22.60	22.51	23.08	23.55	6.41	6.98	6.90	7.46	7.94
8H	4H	20.77	21.41	21.24	21.86	22.33	6.34	6.99	6.81	7.44	7.91
	6H	21.51	22.03	22.01	22.53	23.01	6.70	7.22	7.20	7.72	8.20
	8H	21.75	22.22	22.27	22.74	23.23	6.84	7.31	7.36	7.83	8.32
	12H	21.90	22.31	22.42	22.81	23.38	6.93	7.34	7.45	7.84	8.41
12H	4H	20.72	21.29	21.21	21.77	22.25	6.47	7.03	6.95	7.52	7.99
	6H	21.45	21.92	21.97	22.43	22.92	6.82	7.29	7.34	7.80	8.30
	8H	21.71	22.12	22.22	22.62	23.19	7.00	7.42	7.52	7.91	8.48