

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058231

Luminaire Tested: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-60)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 637.9 lumens
Efficiency: N/A
Efficacy: 17.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.95 / 0.9
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058231

CATALOG NUMBER: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1058231

CATALOG NUMBER: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81				81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61				61
6	82	72	65	60	80	71	64	59	69	63	59	68	63	59	66	62	58	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48				48
9	69	58	52	47	68	58	51	47	57	51	47	56	51	47	55	50	47	45				45
10	66	55	48	44	65	54	48	44	54	48	44	53	47	44	52	47	44	42				42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10920	10920	10920
5°	10541	10710	10879
10°	9708	10133	10643
15°	8728	9313	10136
20°	7613	8304	9261
25°	6440	7157	8287
30°	5146	5943	7345
35°	3805	4776	6307
40°	2404	3741	5025
45°	947	2811	3698
50°	488	1889	2279
55°	402	1239	1020
60°	292	1004	919
65°	249	939	939
70°	243	977	917
75°	321	1134	970
80°	478	1445	1084
85°	720	2392	1440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 87.5°
 Luminance: 4780 cd/sqm

TEST NUMBER: P1058231

CATALOG NUMBER: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	8.5
10°-20°	136.7	21.4
20°-30°	162.5	25.5
30°-40°	135.2	21.2
40°-50°	75.5	11.8
50°-60°	30.5	4.8
60°-70°	19.5	3.1
70°-80°	14.6	2.3
80°-90°	9.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.3	55.4
0°-40°	488.5	76.6
0°-60°	594.5	93.2
0°-90°	637.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	637.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	592	592	592	592	592	
5°	569	579	578	583	587	53
15°	457	470	488	512	531	127
25°	316	329	352	379	407	144
35°	169	185	212	247	280	105
45°	36	61	108	126	142	34
55°	12	26	38	37	32	11
65°	6	23	22	20	22	6
75°	4	16	16	15	14	5
85°	3	10	11	10	7	4
90°	0	0	0	0	0	



TEST NUMBER: P1058231

CATALOG NUMBER: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	591.8	591.8	591.8	591.8	591.8
2.5°	583.9	592.9	588.4	588.4	589.5
5°	569.1	579.3	578.2	582.7	587.3
7.5°	545.3	556.7	562.3	572.5	580.5
10°	518.1	530.6	540.8	556.7	568.0
12.5°	488.6	501.1	515.9	536.3	551.0
15°	456.9	470.5	487.5	512.5	530.6
17.5°	421.8	436.5	455.8	483.0	502.2
20°	387.7	402.5	422.9	450.1	471.6
22.5°	352.6	365.1	386.6	413.8	439.9
25°	316.3	328.8	351.5	378.7	407.0
27.5°	280.0	292.5	315.2	343.5	375.3
30°	241.5	255.1	278.9	310.6	344.7
32.5°	205.2	218.8	243.8	278.9	312.9
35°	168.9	184.8	212.0	247.2	280.0
37.5°	133.8	151.9	182.5	215.4	244.9
40°	99.8	119.0	155.3	183.7	208.6
42.5°	65.8	88.4	130.4	154.2	173.5
45°	36.3	61.2	107.7	125.8	141.7
47.5°	20.4	39.7	85.0	99.8	108.8
50°	17.0	29.5	65.8	76.0	79.4
52.5°	13.6	27.2	49.9	55.6	53.3
55°	12.5	26.1	38.5	37.4	31.7
57.5°	10.2	26.1	30.6	27.2	27.2
60°	7.9	24.9	27.2	23.8	24.9
62.5°	6.8	23.8	24.9	22.7	22.7
65°	5.7	22.7	21.5	20.4	21.5
67.5°	4.5	20.4	20.4	19.3	19.3
70°	4.5	19.3	18.1	17.0	17.0
72.5°	4.5	17.0	17.0	15.9	15.9
75°	4.5	15.9	15.9	14.7	13.6
77.5°	4.5	13.6	14.7	13.6	12.5
80°	4.5	12.5	13.6	12.5	10.2
82.5°	4.5	11.3	12.5	11.3	9.1
85°	3.4	10.2	11.3	10.2	6.8
87.5°	3.4	10.2	11.3	9.1	5.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058231
 CATALOG NUMBER: S122RDR-H1005D927-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.68	7.90	7.04	8.21	8.52	7.74	8.96	8.11	9.27	9.59
	3H	8.00	9.09	8.39	9.42	9.78	9.78	10.86	10.16	11.19	11.56
	4H	8.58	9.59	8.98	9.94	10.32	10.73	11.74	11.14	12.09	12.48
	6H	9.14	10.07	9.55	10.44	10.83	11.68	12.61	12.10	12.98	13.38
	8H	9.46	10.34	9.89	10.73	11.14	12.13	13.01	12.56	13.40	13.81
	12H	9.77	10.61	10.20	10.99	11.42	12.55	13.39	12.99	13.78	14.21
4H	2H	7.63	8.64	8.04	9.00	9.38	8.42	9.43	8.82	9.78	10.17
	3H	9.66	10.49	10.07	10.90	11.30	10.70	11.54	11.12	11.94	12.35
	4H	10.74	11.49	11.18	11.91	12.36	11.85	12.60	12.29	13.02	13.46
	6H	11.61	12.26	12.08	12.71	13.18	13.02	13.67	13.49	14.12	14.59
	8H	12.02	12.63	12.49	13.07	13.55	13.59	14.19	14.06	14.64	15.11
	12H	12.40	12.93	12.89	13.42	13.89	14.13	14.67	14.62	15.15	15.63
8H	4H	11.51	12.12	11.98	12.57	13.04	12.40	13.01	12.87	13.46	13.93
	6H	12.85	13.35	13.36	13.85	14.33	13.86	14.36	14.36	14.85	15.34
	8H	13.56	14.01	14.09	14.53	15.02	14.62	15.07	15.15	15.59	16.08
	12H	14.26	14.65	14.77	15.14	15.72	15.41	15.80	15.93	16.30	16.87
12H	4H	11.67	12.20	12.16	12.69	13.16	12.51	13.04	13.00	13.53	14.00
	6H	13.17	13.62	13.70	14.14	14.63	14.09	14.53	14.61	15.05	15.54
	8H	14.07	14.47	14.59	14.96	15.54	14.99	15.39	15.51	15.88	16.45