

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056507

Luminaire Tested: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DR-H1090D927-X4F0-XX-UDD-F-W
Description: DEFINE 5, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2816.1 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.01 / 1.17
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056507

CATALOG NUMBER: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P1056507

CATALOG NUMBER: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	101	93	87	81	98	91	85	80	88	83	79	84	80	77	81	78	75	73
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63
4	85	74	66	59	83	73	65	59	70	63	58	68	62	57	66	61	57	55
5	79	67	58	52	77	66	58	52	63	56	51	62	55	51	60	54	50	48
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	55	49	45	43
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34
9	59	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31
10	56	43	36	31	55	43	35	30	42	35	30	41	35	30	40	34	30	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9392	9392	9392
5°	9337	9330	9337
10°	9274	9104	9019
15°	9181	8826	8645
20°	9058	8484	8180
25°	8920	8079	7624
30°	8746	7640	7034
35°	8555	7163	6421
40°	8363	6674	5816
45°	8160	6161	5213
50°	7943	5636	4614
55°	7743	5061	4012
60°	7469	4448	3525
65°	7099	3774	3277
70°	6666	3373	3067
75°	6025	3108	2893
80°	5235	2821	2699
85°	4096	2490	2490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8160 cd/sqm



TEST NUMBER: P1056507

CATALOG NUMBER: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.3	4.4
10°-20°	341.3	12.1
20°-30°	482.2	17.1
30°-40°	530.8	18.8
40°-50°	495.1	17.6
50°-60°	395.3	14.0
60°-70°	266.0	9.4
70°-80°	141.7	5.0
80°-90°	39.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.8	33.7
0°-40°	1478.6	52.5
0°-60°	2369.0	84.1
0°-90°	2816.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2816.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1316	1327	1315	1311	1316	125
15°	1254	1248	1206	1185	1181	354
25°	1144	1109	1036	990	977	526
35°	991	933	830	765	744	620
45°	816	739	616	541	521	630
55°	628	533	411	345	326	561
65°	424	331	226	200	196	421
75°	221	146	114	107	106	235
85°	50	35	31	32	31	60
90°	0	0	0	0	0	



TEST NUMBER: P1056507

CATALOG NUMBER: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1328.6	1328.6	1328.6	1328.6	1328.6
2.5°	1321.7	1332.6	1323.7	1325.7	1327.7
5°	1315.8	1326.7	1314.8	1310.8	1315.8
7.5°	1305.9	1314.8	1295.0	1286.1	1290.1
10°	1292.0	1298.0	1268.3	1256.4	1256.4
12.5°	1275.2	1275.2	1239.6	1222.8	1222.8
15°	1254.4	1247.5	1206.0	1185.2	1181.2
17.5°	1230.7	1217.8	1168.4	1141.7	1136.7
20°	1204.0	1183.2	1127.8	1093.2	1087.3
22.5°	1174.3	1147.6	1083.3	1040.8	1033.8
25°	1143.6	1109.0	1035.8	990.3	977.4
27.5°	1109.0	1067.5	987.3	935.9	920.1
30°	1071.4	1023.9	935.9	878.5	861.7
32.5°	1032.8	979.4	883.5	822.1	803.3
35°	991.3	932.9	830.0	764.7	744.0
37.5°	949.7	886.4	777.6	709.3	687.6
40°	906.2	837.0	723.2	652.9	630.2
42.5°	862.7	788.5	669.8	598.5	574.8
45°	816.2	739.0	616.3	541.2	521.4
47.5°	771.7	688.6	563.9	490.7	468.9
50°	722.2	636.1	512.5	439.3	419.5
52.5°	676.7	584.7	461.0	392.8	372.0
55°	628.2	533.2	410.6	345.3	325.5
57.5°	577.8	481.8	362.1	300.8	282.0
60°	528.3	430.4	314.6	258.2	249.3
62.5°	477.8	381.9	270.1	226.6	220.6
65°	424.4	331.4	225.6	199.8	195.9
67.5°	374.0	282.9	189.9	175.1	171.2
70°	322.5	234.5	163.2	150.4	148.4
72.5°	272.1	188.0	137.5	128.6	126.6
75°	220.6	146.4	113.8	106.8	105.9
77.5°	173.1	109.8	90.0	87.1	85.1
80°	128.6	82.1	69.3	67.3	66.3
82.5°	88.0	56.4	49.5	49.5	47.5
85°	50.5	34.6	30.7	31.7	30.7
87.5°	18.8	14.8	13.9	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056507

CATALOG NUMBER: S125R3DR-H1090D927-X4F0-XX-UDD-F-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.07	20.61	19.44	20.92	21.24	15.45	16.99	15.82	17.31	17.62
	3H	20.86	22.24	21.23	22.57	22.93	16.93	18.31	17.31	18.64	19.00
	4H	21.51	22.81	21.91	23.16	23.53	17.52	18.82	17.92	19.17	19.55
	6H	21.99	23.19	22.40	23.55	23.94	17.98	19.18	18.39	19.55	19.94
	8H	22.14	23.28	22.57	23.67	24.07	18.14	19.29	18.57	19.68	20.08
	12H	22.24	23.33	22.67	23.71	24.14	18.26	19.35	18.69	19.74	20.16
4H	2H	19.21	20.50	19.60	20.85	21.23	16.13	17.43	16.53	17.78	18.16
	3H	21.18	22.26	21.59	22.66	23.06	17.81	18.89	18.22	19.29	19.69
	4H	21.92	22.89	22.35	23.31	23.75	18.51	19.48	18.94	19.90	20.34
	6H	22.52	23.36	22.97	23.81	24.26	19.10	19.94	19.55	20.39	20.85
	8H	22.72	23.51	23.18	23.96	24.42	19.30	20.10	19.77	20.54	21.01
	12H	22.87	23.58	23.35	24.06	24.53	19.47	20.18	19.95	20.65	21.12
8H	4H	21.98	22.78	22.45	23.22	23.69	18.87	19.67	19.34	20.11	20.58
	6H	22.64	23.30	23.14	23.79	24.27	19.58	20.23	20.07	20.72	21.20
	8H	22.90	23.49	23.41	24.00	24.48	19.86	20.45	20.37	20.96	21.45
	12H	23.11	23.63	23.61	24.12	24.68	20.10	20.62	20.61	21.12	21.68
12H	4H	21.98	22.69	22.46	23.16	23.63	18.92	19.63	19.40	20.11	20.58
	6H	22.64	23.23	23.15	23.74	24.22	19.65	20.24	20.16	20.75	21.24
	8H	22.93	23.45	23.44	23.94	24.51	19.99	20.51	20.50	21.00	21.57