

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058573

Luminaire Tested: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-60)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H865D935-X4F0-XX-UDD-BVL-S
Description: DEFINE 2 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 593.5 lumens
Efficiency: N/A
Efficacy: 19.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.95 / 0.9
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058573

CATALOG NUMBER: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1058573

CATALOG NUMBER: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61
6	82	72	65	60	80	71	64	59	69	63	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48
9	69	58	52	47	68	58	51	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	54	48	44	53	47	44	52	47	44	42

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10160	10160	10160
5°	9808	9965	10121
10°	9033	9429	9903
15°	8121	8665	9431
20°	7083	7725	8617
25°	5992	6658	7710
30°	4788	5529	6833
35°	3541	4444	5868
40°	2235	3481	4675
45°	882	2615	3442
50°	454	1757	2119
55°	373	1155	949
60°	273	934	856
65°	231	873	873
70°	227	912	852
75°	299	1055	905
80°	446	1350	1010
85°	677	2223	1334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 87.5°
 Luminance: 4442 cd/sqm

TEST NUMBER: P1058573

CATALOG NUMBER: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	8.5
10°-20°	127.2	21.4
20°-30°	151.2	25.5
30°-40°	125.7	21.2
40°-50°	70.2	11.8
50°-60°	28.4	4.8
60°-70°	18.1	3.1
70°-80°	13.6	2.3
80°-90°	8.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.7	55.4
0°-40°	454.5	76.6
0°-60°	553.1	93.2
0°-90°	593.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	530	539	538	542	546	49
15°	425	438	454	477	494	118
25°	294	306	327	352	379	134
35°	157	172	197	230	260	98
45°	34	57	100	117	132	32
55°	12	24	36	35	30	10
65°	5	21	20	19	20	5
75°	4	15	15	14	13	4
85°	3	10	10	10	6	3
90°	0	0	0	0	0	

TEST NUMBER: P1058573

CATALOG NUMBER: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	550.6	550.6	550.6	550.6	550.6
2.5°	543.2	551.7	547.5	547.5	548.5
5°	529.5	539.0	538.0	542.2	546.4
7.5°	507.4	517.9	523.2	532.7	540.1
10°	482.1	493.7	503.2	517.9	528.5
12.5°	454.6	466.2	479.9	498.9	512.6
15°	425.1	437.8	453.6	476.8	493.7
17.5°	392.4	406.1	424.0	449.4	467.3
20°	360.7	374.5	393.4	418.8	438.8
22.5°	328.0	339.7	359.7	385.0	409.3
25°	294.3	305.9	327.0	352.3	378.7
27.5°	260.5	272.1	293.2	319.6	349.1
30°	224.7	237.3	259.5	289.0	320.7
32.5°	190.9	203.6	226.8	259.5	291.1
35°	157.2	171.9	197.3	230.0	260.5
37.5°	124.5	141.3	169.8	200.4	227.8
40°	92.8	110.8	144.5	170.9	194.1
42.5°	61.2	82.3	121.3	143.5	161.4
45°	33.8	57.0	100.2	117.1	131.9
47.5°	19.0	36.9	79.1	92.8	101.3
50°	15.8	27.4	61.2	70.7	73.8
52.5°	12.7	25.3	46.4	51.7	49.6
55°	11.6	24.3	35.9	34.8	29.5
57.5°	9.5	24.3	28.5	25.3	25.3
60°	7.4	23.2	25.3	22.2	23.2
62.5°	6.3	22.2	23.2	21.1	21.1
65°	5.3	21.1	20.0	19.0	20.0
67.5°	4.2	19.0	19.0	17.9	17.9
70°	4.2	17.9	16.9	15.8	15.8
72.5°	4.2	15.8	15.8	14.8	14.8
75°	4.2	14.8	14.8	13.7	12.7
77.5°	4.2	12.7	13.7	12.7	11.6
80°	4.2	11.6	12.7	11.6	9.5
82.5°	4.2	10.5	11.6	10.5	8.4
85°	3.2	9.5	10.5	9.5	6.3
87.5°	3.2	9.5	10.5	8.4	5.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058573
 CATALOG NUMBER: S122RDR-H865D935-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.43	7.65	6.80	7.96	8.28	7.49	8.71	7.86	9.02	9.34
	3H	7.76	8.84	8.14	9.17	9.54	9.52	10.60	9.90	10.93	11.30
	4H	8.33	9.34	8.73	9.69	10.08	10.48	11.49	10.88	11.84	12.23
	6H	8.89	9.82	9.31	10.19	10.59	11.43	12.36	11.84	12.73	13.12
	8H	9.22	10.10	9.65	10.49	10.89	11.87	12.75	12.31	13.14	13.55
	12H	9.53	10.37	9.96	10.75	11.18	12.29	13.13	12.73	13.52	13.95
4H	2H	7.39	8.40	7.79	8.75	9.13	8.17	9.18	8.57	9.53	9.91
	3H	9.41	10.24	9.82	10.65	11.05	10.45	11.28	10.86	11.69	12.09
	4H	10.49	11.24	10.93	11.66	12.11	11.60	12.35	12.04	12.77	13.21
	6H	11.36	12.01	11.83	12.46	12.93	12.77	13.42	13.24	13.87	14.34
	8H	11.77	12.38	12.24	12.83	13.30	13.33	13.94	13.80	14.39	14.86
	12H	12.15	12.69	12.64	13.17	13.65	13.87	14.41	14.36	14.89	15.37
8H	4H	11.27	11.87	11.74	12.32	12.79	12.15	12.76	12.62	13.21	13.68
	6H	12.61	13.10	13.11	13.60	14.08	13.61	14.11	14.11	14.60	15.09
	8H	13.32	13.76	13.84	14.28	14.77	14.37	14.82	14.89	15.33	15.82
	12H	14.01	14.40	14.53	14.90	15.47	15.15	15.55	15.67	16.04	16.62
12H	4H	11.42	11.96	11.91	12.44	12.92	12.26	12.80	12.75	13.28	13.75
	6H	12.93	13.37	13.45	13.89	14.38	13.84	14.28	14.36	14.80	15.29
	8H	13.82	14.22	14.34	14.71	15.29	14.74	15.13	15.25	15.63	16.20