

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056588

Luminaire Tested: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W
Description: DEFINE 5, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1559.2 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.01 / 1.17
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 17.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056588

CATALOG NUMBER: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

Luminous Intensity Polar Plot



TEST NUMBER: P1056588

CATALOG NUMBER: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	101	93	87	81	98	91	85	80	88	83	79	84	80	77	81	78	75	73
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63
4	85	74	66	59	83	73	65	59	70	63	58	68	62	57	66	61	57	55
5	79	67	58	52	77	66	58	52	63	56	51	62	55	51	60	54	50	48
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	55	49	45	43
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34
9	59	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31
10	56	43	36	31	55	43	35	30	42	35	30	41	35	30	40	34	30	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5200	5200	5200
5°	5170	5166	5170
10°	5135	5041	4993
15°	5084	4887	4786
20°	5015	4697	4529
25°	4939	4473	4221
30°	4842	4230	3895
35°	4736	3966	3555
40°	4630	3695	3220
45°	4518	3412	2886
50°	4398	3120	2554
55°	4287	2801	2221
60°	4136	2463	1951
65°	3931	2089	1815
70°	3692	1869	1699
75°	3335	1721	1601
80°	2899	1559	1494
85°	2263	1379	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4518 cd/sqm



TEST NUMBER: P1056588

CATALOG NUMBER: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	4.4
10°-20°	189.0	12.1
20°-30°	267.0	17.1
30°-40°	293.9	18.8
40°-50°	274.1	17.6
50°-60°	218.9	14.0
60°-70°	147.3	9.4
70°-80°	78.4	5.0
80°-90°	21.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.8	33.7
0°-40°	818.7	52.5
0°-60°	1311.6	84.1
0°-90°	1559.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1559.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	728	734	728	726	728	69
15°	695	691	668	656	654	196
25°	633	614	574	548	541	291
35°	549	516	460	423	412	343
45°	452	409	341	300	289	349
55°	348	295	227	191	180	311
65°	235	184	125	111	108	233
75°	122	81	63	59	59	130
85°	28	19	17	18	17	33
90°	0	0	0	0	0	



TEST NUMBER: P1056588

CATALOG NUMBER: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	735.6	735.6	735.6	735.6	735.6
2.5°	731.8	737.8	732.9	734.0	735.1
5°	728.5	734.5	728.0	725.8	728.5
7.5°	723.0	728.0	717.0	712.1	714.3
10°	715.4	718.7	702.2	695.6	695.6
12.5°	706.1	706.1	686.3	677.0	677.0
15°	694.6	690.7	667.7	656.2	654.0
17.5°	681.4	674.3	646.9	632.1	629.4
20°	666.6	655.1	624.4	605.3	602.0
22.5°	650.2	635.4	599.8	576.2	572.4
25°	633.2	614.0	573.5	548.3	541.2
27.5°	614.0	591.0	546.7	518.2	509.4
30°	593.2	566.9	518.2	486.4	477.1
32.5°	571.9	542.3	489.1	455.2	444.8
35°	548.8	516.5	459.6	423.4	411.9
37.5°	525.8	490.8	430.5	392.7	380.7
40°	501.7	463.4	400.4	361.5	348.9
42.5°	477.6	436.6	370.8	331.4	318.2
45°	451.9	409.2	341.3	299.6	288.7
47.5°	427.2	381.2	312.2	271.7	259.6
50°	399.9	352.2	283.7	243.2	232.2
52.5°	374.7	323.7	255.3	217.5	206.0
55°	347.8	295.2	227.3	191.2	180.2
57.5°	319.9	266.8	200.5	166.5	156.1
60°	292.5	238.3	174.2	143.0	138.0
62.5°	264.6	211.4	149.5	125.4	122.1
65°	235.0	183.5	124.9	110.6	108.5
67.5°	207.1	156.7	105.2	97.0	94.8
70°	178.6	129.8	90.4	83.3	82.2
72.5°	150.6	104.1	76.1	71.2	70.1
75°	122.1	81.1	63.0	59.2	58.6
77.5°	95.9	60.8	49.8	48.2	47.1
80°	71.2	45.5	38.3	37.2	36.7
82.5°	48.8	31.2	27.4	27.4	26.3
85°	27.9	19.2	17.0	17.5	17.0
87.5°	10.4	8.2	7.7	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056588

CATALOG NUMBER: S125R3DR-H610D927-X4F0-XX-UDD-FLL-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.02	18.56	17.38	18.87	19.19	13.40	14.94	13.76	15.25	15.57
	3H	18.80	20.19	19.18	20.51	20.88	14.88	16.26	15.25	16.59	16.95
	4H	19.46	20.75	19.86	21.10	21.48	15.47	16.76	15.87	17.11	17.49
	6H	19.93	21.13	20.34	21.50	21.89	15.93	17.13	16.34	17.50	17.89
	8H	20.09	21.23	20.51	21.62	22.02	16.09	17.23	16.51	17.62	18.02
	12H	20.18	21.28	20.61	21.66	22.09	16.20	17.30	16.63	17.68	18.11
4H	2H	17.15	18.45	17.55	18.80	19.18	14.08	15.37	14.47	15.72	16.10
	3H	19.12	20.20	19.53	20.60	21.00	15.75	16.83	16.16	17.23	17.63
	4H	19.87	20.84	20.30	21.26	21.69	16.46	17.43	16.89	17.85	18.28
	6H	20.46	21.31	20.92	21.75	22.21	17.04	17.89	17.50	18.33	18.79
	8H	20.67	21.46	21.13	21.90	22.37	17.25	18.04	17.71	18.49	18.95
	12H	20.82	21.52	21.30	22.00	22.47	17.41	18.12	17.89	18.60	19.07
8H	4H	19.93	20.72	20.39	21.17	21.63	16.82	17.61	17.28	18.06	18.52
	6H	20.59	21.25	21.09	21.74	22.21	17.52	18.18	18.02	18.67	19.15
	8H	20.84	21.43	21.36	21.94	22.43	17.81	18.40	18.32	18.90	19.39
	12H	21.05	21.57	21.56	22.07	22.63	18.05	18.57	18.56	19.06	19.62
12H	4H	19.92	20.63	20.41	21.11	21.58	16.87	17.58	17.35	18.06	18.53
	6H	20.58	21.17	21.10	21.68	22.17	17.59	18.18	18.11	18.69	19.18
	8H	20.88	21.40	21.39	21.89	22.46	17.94	18.46	18.45	18.95	19.51