

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058374

Luminaire Tested: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

Issue Date: 8/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1058374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122RDR-H485D840-X4F0-XX-UDD-BVL-B  
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE  
LOUVER WITH DIFFUSER  
HIGH PERFORMANCE LIGHT ENGINE  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 304.3 lumens  
Efficiency: N/A  
Efficacy: 17.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.8 / 0.88  
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1058374

CATALOG NUMBER: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

### Luminous Intensity Polar Plot





TEST NUMBER: P1058374

CATALOG NUMBER: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	101	95	89	85	99	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54
9	73	63	57	53	72	62	57	52	61	56	52	61	56	52	60	55	52	51
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5969	5969	5969
5°	5929	5840	5866
10°	5807	5563	5421
15°	5462	5083	4873
20°	4876	4513	4257
25°	4261	3815	3620
30°	3658	3119	2915
35°	3050	2435	2187
40°	2373	1797	1400
45°	1660	1195	608
50°	904	629	215
55°	132	219	154
60°	26	52	100
65°	0	31	61
70°	0	0	38
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1660 cd/sqm



TEST NUMBER: P1058374

CATALOG NUMBER: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.7	9.8
10°-20°	74.9	24.6
20°-30°	87.3	28.7
30°-40°	70.0	23.0
40°-50°	34.8	11.4
50°-60°	6.9	2.3
60°-70°	0.6	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.0	63.1
0°-40°	262.0	86.1
0°-60°	303.6	99.8
0°-90°	304.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	324	324	324	324	324	
5°	320	320	315	316	317	30
15°	286	280	266	259	255	79
25°	209	199	187	183	178	96
35°	135	122	108	103	97	84
45°	64	56	46	31	23	49
55°	4	8	7	4	5	8
65°	0	0	1	1	1	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1058374

CATALOG NUMBER: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	323.5	323.5	323.5	323.5	323.5
2.5°	322.2	323.5	320.1	323.5	324.2
5°	320.1	320.1	315.3	316.0	316.7
7.5°	316.7	315.3	307.1	305.8	304.4
10°	309.9	307.1	296.9	291.4	289.3
12.5°	300.3	296.2	282.5	276.3	272.9
15°	285.9	280.4	266.1	259.2	255.1
17.5°	267.5	262.7	249.0	241.5	237.4
20°	248.3	241.5	229.8	222.3	216.8
22.5°	229.8	220.9	208.6	203.2	197.7
25°	209.3	199.0	187.4	183.3	177.8
27.5°	192.2	179.2	165.5	162.8	158.0
30°	171.7	159.4	146.4	142.3	136.8
32.5°	153.9	140.2	127.2	122.4	117.7
35°	135.4	121.8	108.1	103.3	97.1
37.5°	117.7	104.7	91.0	83.5	78.0
40°	98.5	87.6	74.6	65.0	58.1
42.5°	81.4	71.8	59.5	47.2	40.4
45°	63.6	56.1	45.8	30.8	23.3
47.5°	47.2	41.7	33.5	17.8	12.3
50°	31.5	29.4	21.9	8.9	7.5
52.5°	17.1	18.5	13.0	5.5	6.2
55°	4.1	8.2	6.8	4.1	4.8
57.5°	0.7	1.4	3.4	3.4	3.4
60°	0.7	0.7	1.4	2.1	2.7
62.5°	0.7	0.0	0.7	1.4	2.1
65°	0.0	0.0	0.7	0.7	1.4
67.5°	0.0	0.0	0.0	0.7	0.7
70°	0.0	0.0	0.0	0.7	0.7
72.5°	0.0	0.0	0.0	0.0	0.7
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058374  
 CATALOG NUMBER: S122RDR-H485D840-X4F0-XX-UDD-BVL-B

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00