

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058269

Luminaire Tested: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-20)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 734.6 lumens
Efficiency: N/A
Efficacy: 20.1 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.85 / 0.91
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058269

CATALOG NUMBER: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058269

CATALOG NUMBER: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92				
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84				
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64				
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59				
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54				
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50				
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12603	12603	12603
5°	12525	12349	12399
10°	12262	11776	11623
15°	11615	10939	10625
20°	10441	9852	9504
25°	9298	8494	8189
30°	8133	7087	6884
35°	6848	5742	5559
40°	5516	4531	4006
45°	4126	3272	2383
50°	2584	2113	1565
55°	878	1139	1271
60°	502	705	1008
65°	358	476	773
70°	297	367	588
75°	192	292	485
80°	149	287	436
85°	0	0	296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4126 cd/sqm



TEST NUMBER: P1058269

CATALOG NUMBER: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.0	8.6
10°-20°	161.2	21.9
20°-30°	194.0	26.4
30°-40°	165.8	22.6
40°-50°	97.1	13.2
50°-60°	35.2	4.8
60°-70°	12.5	1.7
70°-80°	5.0	0.7
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.2	56.9
0°-40°	583.9	79.5
0°-60°	716.2	97.5
0°-90°	734.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	683	683	683	683	683	
5°	676	678	667	669	669	64
15°	608	598	573	562	556	169
25°	457	438	417	410	402	210
35°	304	281	255	252	247	190
45°	158	142	125	105	91	122
55°	27	38	35	37	40	34
65°	8	10	11	15	18	9
75°	3	4	4	6	7	3
85°	0	0	0	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P1058269

CATALOG NUMBER: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	683.0	683.0	683.0	683.0	683.0
2.5°	681.7	683.0	676.2	683.0	685.7
5°	676.2	677.6	666.7	669.4	669.4
7.5°	668.0	666.7	651.7	648.9	647.6
10°	654.4	650.3	628.5	624.4	620.3
12.5°	633.9	625.8	602.6	595.8	590.3
15°	608.0	598.5	572.6	561.7	556.2
17.5°	572.6	561.7	537.1	526.2	520.8
20°	531.7	520.8	501.7	489.4	484.0
22.5°	497.6	479.9	459.4	451.3	444.4
25°	456.7	437.6	417.2	410.4	402.2
27.5°	418.5	395.4	374.9	369.5	362.6
30°	381.7	357.2	332.6	332.6	323.1
32.5°	342.2	319.0	293.1	291.7	286.3
35°	304.0	280.8	254.9	252.2	246.8
37.5°	268.6	245.4	220.9	212.7	205.9
40°	229.0	208.6	188.1	174.5	166.3
42.5°	197.7	174.5	154.1	137.7	126.8
45°	158.1	141.8	125.4	105.0	91.3
47.5°	122.7	111.8	98.2	75.0	68.2
50°	90.0	84.5	73.6	55.9	54.5
52.5°	57.3	60.0	53.2	43.6	47.7
55°	27.3	38.2	35.4	36.8	39.5
57.5°	17.7	19.1	25.9	30.0	32.7
60°	13.6	13.6	19.1	24.5	27.3
62.5°	10.9	10.9	15.0	20.4	21.8
65°	8.2	9.5	10.9	15.0	17.7
67.5°	6.8	6.8	8.2	12.3	13.6
70°	5.5	5.5	6.8	9.5	10.9
72.5°	4.1	4.1	5.5	8.2	8.2
75°	2.7	4.1	4.1	5.5	6.8
77.5°	2.7	2.7	2.7	4.1	5.5
80°	1.4	1.4	2.7	2.7	4.1
82.5°	1.4	1.4	1.4	1.4	2.7
85°	0.0	0.0	0.0	1.4	1.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058269
 CATALOG NUMBER: S122RDR-H1005D950-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.69	5.85	5.05	6.16	6.48	8.08	9.25	8.45	9.56	9.87
	3H	5.21	6.23	5.59	6.56	6.93	8.81	9.83	9.19	10.16	10.53
	4H	5.34	6.29	5.75	6.64	7.03	9.03	9.98	9.43	10.33	10.72
	6H	5.42	6.28	5.83	6.66	7.05	9.18	10.05	9.60	10.42	10.82
	8H	5.43	6.24	5.86	6.63	7.04	9.21	10.03	9.65	10.42	10.83
	12H	5.39	6.17	5.82	6.55	6.99	9.21	9.99	9.65	10.38	10.81
4H	2H	5.00	5.94	5.40	6.30	6.68	8.05	9.00	8.46	9.35	9.74
	3H	5.66	6.43	6.07	6.83	7.24	8.92	9.69	9.34	10.10	10.50
	4H	5.90	6.58	6.34	7.01	7.45	9.21	9.89	9.65	10.31	10.76
	6H	6.02	6.60	6.49	7.05	7.52	9.43	10.02	9.90	10.47	10.94
	8H	6.04	6.58	6.51	7.03	7.51	9.48	10.03	9.95	10.47	10.95
	12H	6.01	6.48	6.49	6.97	7.45	9.50	9.98	9.99	10.47	10.94
8H	4H	6.01	6.55	6.48	7.00	7.47	9.14	9.68	9.61	10.13	10.61
	6H	6.17	6.61	6.68	7.11	7.60	9.40	9.84	9.91	10.34	10.82
	8H	6.22	6.62	6.75	7.14	7.63	9.46	9.86	9.99	10.38	10.87
	12H	6.20	6.55	6.72	7.05	7.62	9.53	9.87	10.04	10.37	10.95
12H	4H	5.99	6.47	6.48	6.96	7.43	9.09	9.57	9.58	10.05	10.53
	6H	6.17	6.57	6.70	7.09	7.58	9.35	9.75	9.88	10.26	10.76
	8H	6.25	6.60	6.77	7.10	7.67	9.44	9.78	9.95	10.28	10.86