

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1058431

Luminaire Tested: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1058431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2406-143-20)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDR-H485D950-X4F0-XX-UDD-SVL-B
Description: DEFINE 2 BLACK REGRESSED DIRECT RECESSED HOUSING WITH SILVER STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 348.1 lumens
Efficiency: N/A
Efficacy: 20.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.85 / 0.91
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1058431

CATALOG NUMBER: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1058431

CATALOG NUMBER: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5973	5973	5973
5°	5937	5853	5877
10°	5812	5582	5509
15°	5506	5185	5036
20°	4948	4670	4505
25°	4408	4025	3881
30°	3854	3360	3262
35°	3246	2721	2636
40°	2616	2149	1898
45°	1957	1550	1130
50°	1223	1002	741
55°	415	540	602
60°	240	332	476
65°	170	227	367
70°	140	173	281
75°	93	135	228
80°	64	138	202
85°	0	0	127

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1957 cd/sqm



TEST NUMBER: P1058431

CATALOG NUMBER: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.8	8.6
10°-20°	76.4	21.9
20°-30°	92.0	26.4
30°-40°	78.6	22.6
40°-50°	46.0	13.2
50°-60°	16.7	4.8
60°-70°	5.9	1.7
70°-80°	2.4	0.7
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	198.2	56.9
0°-40°	276.8	79.5
0°-60°	339.5	97.5
0°-90°	348.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	348.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	324	324	324	324	324	
5°	320	321	316	317	317	30
15°	288	284	271	266	264	80
25°	216	207	198	194	191	99
35°	144	133	121	120	117	90
45°	75	67	59	50	43	58
55°	13	18	17	17	19	16
65°	4	4	5	7	8	4
75°	1	2	2	3	3	2
85°	0	0	0	1	1	0
90°	0	0	0	0	0	



TEST NUMBER: P1058431

CATALOG NUMBER: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	323.7	323.7	323.7	323.7	323.7
2.5°	323.1	323.7	320.5	323.7	325.0
5°	320.5	321.1	316.0	317.3	317.3
7.5°	316.6	316.0	308.9	307.6	306.9
10°	310.2	308.2	297.9	295.9	294.0
12.5°	300.5	296.6	285.6	282.4	279.8
15°	288.2	283.7	271.4	266.2	263.6
17.5°	271.4	266.2	254.6	249.4	246.8
20°	252.0	246.8	237.8	232.0	229.4
22.5°	235.8	227.4	217.8	213.9	210.6
25°	216.5	207.4	197.7	194.5	190.6
27.5°	198.4	187.4	177.7	175.1	171.9
30°	180.9	169.3	157.7	157.7	153.1
32.5°	162.2	151.2	138.9	138.3	135.7
35°	144.1	133.1	120.8	119.5	117.0
37.5°	127.3	116.3	104.7	100.8	97.6
40°	108.6	98.9	89.2	82.7	78.8
42.5°	93.7	82.7	73.0	65.3	60.1
45°	75.0	67.2	59.4	49.8	43.3
47.5°	58.2	53.0	46.5	35.5	32.3
50°	42.6	40.1	34.9	26.5	25.8
52.5°	27.1	28.4	25.2	20.7	22.6
55°	12.9	18.1	16.8	17.4	18.7
57.5°	8.4	9.0	12.3	14.2	15.5
60°	6.5	6.5	9.0	11.6	12.9
62.5°	5.2	5.2	7.1	9.7	10.3
65°	3.9	4.5	5.2	7.1	8.4
67.5°	3.2	3.2	3.9	5.8	6.5
70°	2.6	2.6	3.2	4.5	5.2
72.5°	1.9	1.9	2.6	3.9	3.9
75°	1.3	1.9	1.9	2.6	3.2
77.5°	1.3	1.3	1.3	1.9	2.6
80°	0.6	0.6	1.3	1.3	1.9
82.5°	0.6	0.6	0.6	0.6	1.3
85°	0.0	0.0	0.0	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1058431
 CATALOG NUMBER: S122RDR-H485D950-X4F0-XX-UDD-SVL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.07	3.23	2.43	3.54	3.86	5.48	6.65	5.85	6.96	7.27
	3H	2.59	3.61	2.97	3.94	4.31	6.22	7.24	6.60	7.57	7.94
	4H	2.72	3.67	3.12	4.02	4.41	6.43	7.38	6.84	7.73	8.12
	6H	2.79	3.66	3.21	4.03	4.43	6.58	7.45	7.00	7.82	8.22
	8H	2.79	3.61	3.22	4.00	4.41	6.61	7.43	7.04	7.82	8.23
	12H	2.75	3.53	3.19	3.92	4.35	6.61	7.39	7.04	7.77	8.20
4H	2H	2.39	3.33	2.79	3.69	4.07	5.45	6.40	5.86	6.75	7.14
	3H	3.04	3.81	3.46	4.22	4.62	6.33	7.10	6.75	7.51	7.91
	4H	3.28	3.96	3.71	4.38	4.83	6.61	7.30	7.05	7.72	8.16
	6H	3.39	3.98	3.86	4.43	4.90	6.83	7.42	7.30	7.87	8.34
	8H	3.40	3.94	3.87	4.39	4.87	6.88	7.42	7.35	7.87	8.34
	12H	3.36	3.84	3.85	4.32	4.80	6.89	7.37	7.38	7.85	8.33
8H	4H	3.38	3.93	3.86	4.38	4.85	6.54	7.09	7.01	7.54	8.01
	6H	3.54	3.98	4.05	4.48	4.97	6.80	7.24	7.30	7.74	8.22
	8H	3.57	3.97	4.10	4.49	4.98	6.85	7.25	7.38	7.77	8.26
	12H	3.55	3.89	4.07	4.39	4.97	6.90	7.25	7.42	7.75	8.32
12H	4H	3.37	3.85	3.86	4.33	4.81	6.49	6.97	6.98	7.46	7.93
	6H	3.54	3.93	4.07	4.45	4.95	6.75	7.14	7.27	7.66	8.16
	8H	3.60	3.94	4.11	4.44	5.02	6.83	7.17	7.34	7.67	8.25