

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056604

Luminaire Tested: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2019
Report Number: P1056604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B
Description: DEFINE 5, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1583.7 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 0.89 / 1.07
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 23.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056604

CATALOG NUMBER: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

Luminous Intensity Polar Plot





TEST NUMBER: P1056604

CATALOG NUMBER: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	74	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49
7	72	61	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6907	6907	6907
5°	6852	6831	6824
10°	6812	6611	6472
15°	6726	6315	6045
20°	6615	5952	5486
25°	6488	5529	4864
30°	6332	5067	4206
35°	6176	4555	3476
40°	6005	4003	2753
45°	5829	3417	1995
50°	5634	2758	1289
55°	5418	2018	573
60°	5162	1246	164
65°	4843	453	97
70°	4384	159	39
75°	3808	52	27
80°	2919	41	0
85°	1338	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5829 cd/sqm



TEST NUMBER: P1056604

CATALOG NUMBER: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	5.7
10°-20°	243.7	15.4
20°-30°	329.7	20.8
30°-40°	338.7	21.4
40°-50°	280.6	17.7
50°-60°	180.1	11.4
60°-70°	87.0	5.5
70°-80°	29.4	1.9
80°-90°	3.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	664.1	41.9
0°-40°	1002.8	63.3
0°-60°	1463.5	92.4
0°-90°	1583.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1583.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	977	977	977	977	977	
5°	966	973	963	957	962	92
15°	919	907	863	833	826	259
25°	832	791	709	645	624	383
35°	716	647	528	436	403	447
45°	583	487	342	236	200	450
55°	440	322	164	72	46	393
65°	290	160	27	8	6	286
75°	139	30	2	1	1	148
85°	16	0	0	0	0	26
90°	0	0	0	0	0	



TEST NUMBER: P1056604

CATALOG NUMBER: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	977.1	977.1	977.1	977.1	977.1
2.5°	971.3	979.0	972.2	971.3	973.2
5°	965.5	973.2	962.6	956.8	961.6
7.5°	958.7	962.6	944.2	934.5	936.4
10°	949.0	948.0	920.9	904.5	901.6
12.5°	934.5	929.6	893.8	870.6	865.7
15°	919.0	907.4	862.8	832.8	826.0
17.5°	900.6	882.2	828.9	790.2	780.5
20°	879.3	854.1	791.2	743.7	729.2
22.5°	856.0	824.1	751.5	695.3	675.9
25°	831.8	791.2	708.8	644.9	623.6
27.5°	804.7	757.3	666.2	593.6	567.5
30°	775.7	721.4	620.7	541.3	515.2
32.5°	745.6	685.6	575.2	489.0	457.1
35°	715.6	646.9	527.8	435.8	402.8
37.5°	683.7	608.1	481.3	385.4	349.6
40°	650.7	568.4	433.8	333.1	298.3
42.5°	616.9	527.8	386.4	283.7	247.9
45°	583.0	487.1	341.8	236.3	199.5
47.5°	548.1	445.5	295.4	189.8	157.8
50°	512.3	404.8	250.8	148.2	117.2
52.5°	476.4	363.1	205.3	107.5	79.4
55°	439.6	322.5	163.7	71.7	46.5
57.5°	402.8	280.8	124.9	39.7	17.4
60°	365.1	241.1	88.1	13.6	11.6
62.5°	328.3	198.5	55.2	10.7	8.7
65°	289.5	159.8	27.1	7.7	5.8
67.5°	251.8	123.0	11.6	4.8	2.9
70°	212.1	89.1	7.7	2.9	1.9
72.5°	175.3	57.1	4.8	1.9	1.0
75°	139.4	30.0	1.9	1.0	1.0
77.5°	104.6	12.6	1.0	1.0	1.0
80°	71.7	5.8	1.0	1.0	0.0
82.5°	42.6	1.9	1.0	1.0	0.0
85°	16.5	0.0	0.0	0.0	0.0
87.5°	1.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056604

CATALOG NUMBER: S125R3DR-H850D835-X4F0-XX-UDD-FLL-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.78	19.17	18.15	19.48	19.79	2.65	4.03	3.01	4.34	4.66
	3H	19.33	20.56	19.71	20.89	21.25	2.57	3.80	2.95	4.12	4.49
	4H	19.86	21.00	20.26	21.35	21.73	2.50	3.65	2.90	4.00	4.38
	6H	20.19	21.25	20.61	21.62	22.01	2.43	3.48	2.85	3.85	4.25
	8H	20.28	21.27	20.71	21.66	22.07	2.39	3.39	2.82	3.78	4.18
	12H	20.29	21.25	20.73	21.63	22.06	2.35	3.30	2.78	3.69	4.12
4H	2H	17.59	18.73	17.99	19.08	19.46	3.51	4.65	3.91	5.00	5.39
	3H	19.20	20.13	19.61	20.54	20.94	3.46	4.39	3.87	4.79	5.20
	4H	19.72	20.56	20.16	20.97	21.42	3.38	4.21	3.82	4.63	5.08
	6H	20.10	20.82	20.56	21.26	21.73	3.32	4.04	3.78	4.48	4.95
	8H	20.20	20.87	20.66	21.31	21.78	3.27	3.94	3.73	4.38	4.85
	12H	20.23	20.83	20.72	21.31	21.78	3.22	3.82	3.71	4.30	4.77
8H	4H	19.59	20.27	20.06	20.71	21.18	4.40	5.07	4.87	5.52	5.99
	6H	19.95	20.50	20.45	20.99	21.47	4.32	4.87	4.82	5.36	5.84
	8H	20.04	20.54	20.57	21.05	21.54	4.27	4.76	4.79	5.27	5.77
	12H	20.09	20.52	20.60	21.02	21.59	4.23	4.66	4.74	5.16	5.73
12H	4H	19.55	20.15	20.04	20.63	21.10	4.48	5.07	4.97	5.56	6.03
	6H	19.89	20.38	20.41	20.90	21.39	4.38	4.88	4.90	5.39	5.88
	8H	20.00	20.44	20.52	20.93	21.50	4.35	4.79	4.87	5.28	5.85