

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056612

Luminaire Tested: S125R3DR-H850D850-X4F0-XX-UDD-F-W

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125R3DR-H850D850-X4F0-XX-UDD-F-W
Description: DEFINE 5, WHITE 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3056.9 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.01 / 1.17
Luminous Opening: Rectangular (W 0.39' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 23.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056612

CATALOG NUMBER: S125R3DR-H850D850-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P1056612

CATALOG NUMBER: S125R3DR-H850D850-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86
2	101	93	87	81	98	91	85	80	88	83	79	84	80	77	81	78	75	73
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63
4	85	74	66	59	83	73	65	59	70	63	58	68	62	57	66	61	57	55
5	79	67	58	52	77	66	58	52	63	56	51	62	55	51	60	54	50	48
6	73	60	52	46	71	59	51	46	58	51	45	56	50	45	55	49	45	43
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38
8	63	51	42	37	62	50	42	37	49	42	37	47	41	36	46	40	36	34
9	59	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10196	10196	10196
5°	10136	10128	10136
10°	10068	9883	9791
15°	9966	9581	9385
20°	9833	9210	8879
25°	9684	8770	8276
30°	9494	8293	7636
35°	9287	7776	6970
40°	9078	7244	6313
45°	8858	6689	5659
50°	8622	6118	5007
55°	8404	5493	4354
60°	8109	4828	3826
65°	7706	4097	3556
70°	7236	3663	3330
75°	6542	3373	3138
80°	5683	3061	2931
85°	4445	2701	2701

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8858 cd/sqm



TEST NUMBER: P1056612

CATALOG NUMBER: S125R3DR-H850D850-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	4.4
10°-20°	370.5	12.1
20°-30°	523.4	17.1
30°-40°	576.2	18.8
40°-50°	537.5	17.6
50°-60°	429.1	14.0
60°-70°	288.7	9.4
70°-80°	153.8	5.0
80°-90°	42.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1028.9	33.7
0°-40°	1605.1	52.5
0°-60°	2571.6	84.1
0°-90°	3056.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3056.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1442	1442	1442	1442	1442	
5°	1428	1440	1427	1423	1428	136
15°	1362	1354	1309	1287	1282	384
25°	1242	1204	1124	1075	1061	571
35°	1076	1013	901	830	808	673
45°	886	802	669	587	566	684
55°	682	579	446	375	353	609
65°	461	360	245	217	213	457
75°	240	159	124	116	115	255
85°	55	38	33	34	33	65
90°	0	0	0	0	0	



TEST NUMBER: P1056612

CATALOG NUMBER: S125R3DR-H850D850-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1442.3	1442.3	1442.3	1442.3	1442.3
2.5°	1434.8	1446.6	1436.9	1439.1	1441.2
5°	1428.3	1440.1	1427.2	1422.9	1428.3
7.5°	1417.6	1427.2	1405.8	1396.1	1400.4
10°	1402.5	1409.0	1376.8	1363.9	1363.9
12.5°	1384.3	1384.3	1345.6	1327.4	1327.4
15°	1361.7	1354.2	1309.1	1286.6	1282.3
17.5°	1336.0	1322.0	1268.3	1239.3	1233.9
20°	1307.0	1284.4	1224.3	1186.7	1180.2
22.5°	1274.7	1245.8	1175.9	1129.8	1122.2
25°	1241.5	1203.9	1124.4	1075.0	1061.0
27.5°	1203.9	1158.8	1071.8	1015.9	998.7
30°	1163.1	1111.5	1015.9	953.6	935.4
32.5°	1121.2	1063.2	959.0	892.4	872.0
35°	1076.1	1012.7	901.0	830.1	807.6
37.5°	1031.0	962.2	844.1	770.0	746.4
40°	983.7	908.5	785.0	708.8	684.1
42.5°	936.5	855.9	727.0	649.7	623.9
45°	886.0	802.2	669.1	587.4	566.0
47.5°	837.7	747.5	612.1	532.7	509.0
50°	784.0	690.5	556.3	476.8	455.3
52.5°	734.6	634.7	500.4	426.3	403.8
55°	681.9	578.8	445.7	374.8	353.3
57.5°	627.2	523.0	393.1	326.5	306.1
60°	573.5	467.2	341.5	280.3	270.6
62.5°	518.7	414.5	293.2	245.9	239.5
65°	460.7	359.8	244.9	216.9	212.6
67.5°	405.9	307.1	206.2	190.1	185.8
70°	350.1	254.5	177.2	163.2	161.1
72.5°	295.3	204.0	149.3	139.6	137.5
75°	239.5	158.9	123.5	116.0	114.9
77.5°	187.9	119.2	97.7	94.5	92.4
80°	139.6	89.1	75.2	73.0	72.0
82.5°	95.6	61.2	53.7	53.7	51.5
85°	54.8	37.6	33.3	34.4	33.3
87.5°	20.4	16.1	15.0	16.1	16.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1056612
 CATALOG NUMBER: S125R3DR-H850D850-X4F0-XX-UDD-F-W

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.36	20.90	19.72	21.21	21.52	15.74	17.28	16.10	17.59	17.91
	3H	21.14	22.52	21.52	22.85	23.21	17.21	18.60	17.59	18.93	19.29
	4H	21.79	23.09	22.19	23.44	23.82	17.80	19.10	18.20	19.45	19.83
	6H	22.27	23.47	22.68	23.84	24.23	18.27	19.47	18.68	19.83	20.23
	8H	22.42	23.57	22.85	23.96	24.36	18.43	19.57	18.85	19.96	20.36
	12H	22.52	23.62	22.95	24.00	24.43	18.54	19.64	18.97	20.02	20.45
4H	2H	19.49	20.79	19.89	21.14	21.52	16.42	17.71	16.81	18.06	18.44
	3H	21.46	22.54	21.87	22.94	23.34	18.09	19.17	18.50	19.57	19.97
	4H	22.21	23.18	22.64	23.59	24.03	18.80	19.77	19.23	20.18	20.62
	6H	22.80	23.65	23.26	24.09	24.55	19.38	20.23	19.84	20.67	21.13
	8H	23.01	23.80	23.47	24.24	24.71	19.59	20.38	20.05	20.83	21.29
	12H	23.15	23.86	23.64	24.34	24.81	19.75	20.46	20.23	20.94	21.41
8H	4H	22.27	23.06	22.73	23.51	23.97	19.16	19.95	19.62	20.40	20.86
	6H	22.93	23.58	23.42	24.07	24.55	19.86	20.52	20.36	21.01	21.49
	8H	23.18	23.77	23.69	24.28	24.77	20.15	20.73	20.66	21.24	21.73
	12H	23.39	23.91	23.90	24.40	24.97	20.39	20.91	20.90	21.40	21.96
12H	4H	22.26	22.97	22.74	23.45	23.92	19.21	19.92	19.69	20.39	20.86
	6H	22.92	23.51	23.44	24.02	24.51	19.93	20.52	20.45	21.03	21.52
	8H	23.22	23.74	23.73	24.23	24.79	20.28	20.80	20.79	21.29	21.85