

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1061912

Luminaire Tested: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1061912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-87)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S
Description: DEFINE 5 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1199.1 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.14 / 0.98
Luminous Opening: Rectangular (W 0.39' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1061912

CATALOG NUMBER: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1061912

CATALOG NUMBER: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	60	52	47	69	59	52	47	58	52	47	57	51	47	55	50	47	45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42
10	63	52	45	41	62	51	45	40	50	44	40	50	44	40	49	44	40	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6419	6419	6419
5°	6206	6301	6404
10°	5716	5988	6358
15°	5132	5573	6253
20°	4492	5098	6082
25°	3795	4553	5870
30°	3058	3962	5632
35°	2248	3339	5366
40°	1404	2694	5087
45°	526	1968	4729
50°	246	1230	4366
55°	179	510	4038
60°	127	269	3494
65°	75	318	2768
70°	68	370	1757
75°	90	367	551
80°	135	456	408
85°	269	727	545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4729 cd/sqm

TEST NUMBER: P1061912

CATALOG NUMBER: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	7.1
10°-20°	221.3	18.5
20°-30°	282.0	23.5
30°-40°	262.4	21.9
40°-50°	179.8	15.0
50°-60°	99.0	8.3
60°-70°	46.9	3.9
70°-80°	14.7	1.2
80°-90°	7.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.8	49.1
0°-40°	851.2	71.0
0°-60°	1130.0	94.2
0°-90°	1199.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	932	932	932	932	932	
5°	898	909	912	918	927	83
15°	720	743	782	840	877	201
25°	500	530	599	696	773	228
35°	268	305	397	528	638	166
45°	54	91	202	358	486	51
55°	15	17	42	200	336	14
65°	5	6	20	74	170	5
75°	3	6	14	15	21	4
85°	3	8	9	8	7	3
90°	0	0	0	0	0	



TEST NUMBER: P1061912

CATALOG NUMBER: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.3	932.3	932.3	932.3	932.3
2.5°	923.1	932.3	925.4	925.4	926.6
5°	897.9	909.4	911.6	918.5	926.6
7.5°	861.1	876.1	887.5	907.1	920.8
10°	817.5	835.9	856.5	888.7	909.4
12.5°	771.6	791.1	822.1	866.9	895.6
15°	719.9	742.9	781.9	840.5	877.2
17.5°	667.1	692.3	740.6	809.5	855.4
20°	613.1	639.5	695.8	772.7	830.1
22.5°	556.9	585.6	647.6	734.8	802.6
25°	499.5	530.5	599.3	695.8	772.7
27.5°	442.0	474.2	550.0	655.6	741.7
30°	384.6	417.9	498.3	614.3	708.4
32.5°	326.1	362.8	447.8	572.9	674.0
35°	267.5	305.4	397.3	528.2	638.4
37.5°	210.1	249.2	347.9	485.7	602.8
40°	156.2	195.2	299.7	443.2	566.0
42.5°	101.0	142.4	249.2	399.6	525.9
45°	54.0	90.7	202.1	358.2	485.7
47.5°	28.7	48.2	157.3	316.9	447.8
50°	23.0	26.4	114.8	275.6	407.6
52.5°	18.4	20.7	73.5	233.1	372.0
55°	14.9	17.2	42.5	199.8	336.4
57.5°	11.5	13.8	24.1	166.5	295.1
60°	9.2	10.3	19.5	133.2	253.7
62.5°	5.7	8.0	19.5	103.3	212.4
65°	4.6	5.7	19.5	73.5	169.9
67.5°	4.6	4.6	19.5	48.2	127.4
70°	3.4	3.4	18.4	31.0	87.3
72.5°	3.4	3.4	16.1	20.7	50.5
75°	3.4	5.7	13.8	14.9	20.7
77.5°	3.4	9.2	12.6	12.6	11.5
80°	3.4	9.2	11.5	10.3	10.3
82.5°	3.4	9.2	9.2	9.2	8.0
85°	3.4	8.0	9.2	8.0	6.9
87.5°	3.4	8.0	8.0	8.0	4.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1061912
 CATALOG NUMBER: S125RDR-H1090D950-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	15.51	16.79	15.87	17.10	17.42
	3H	0.00	0.00	0.00	0.00	0.00	16.29	17.43	16.67	17.76	18.12
	4H	0.00	0.00	0.00	0.00	0.00	16.32	17.38	16.72	17.73	18.11
	6H	0.00	0.15	0.00	0.52	0.91	16.27	17.25	16.69	17.62	18.01
	8H	0.00	0.77	0.28	1.16	1.56	16.25	17.17	16.68	17.56	17.97
	12H	0.59	1.46	1.02	1.85	2.28	16.23	17.11	16.67	17.49	17.92
4H	2H	0.00	0.35	0.00	0.70	1.08	15.29	16.35	15.69	16.70	17.08
	3H	0.15	1.02	0.57	1.42	1.83	16.12	16.98	16.53	17.38	17.79
	4H	0.74	1.51	1.18	1.93	2.38	16.15	16.92	16.59	17.34	17.79
	6H	2.24	2.90	2.70	3.35	3.82	16.14	16.80	16.60	17.25	17.72
	8H	2.98	3.60	3.45	4.05	4.52	16.12	16.74	16.59	17.19	17.66
	12H	3.71	4.26	4.20	4.74	5.22	16.12	16.67	16.61	17.15	17.63
8H	4H	2.79	3.41	3.26	3.86	4.33	16.04	16.66	16.51	17.10	17.58
	6H	4.54	5.04	5.04	5.54	6.02	16.04	16.54	16.54	17.04	17.52
	8H	5.49	5.94	6.01	6.46	6.95	16.04	16.50	16.57	17.01	17.51
	12H	6.42	6.82	6.93	7.31	7.88	16.09	16.49	16.60	16.99	17.56
12H	4H	3.09	3.64	3.58	4.12	4.60	15.99	16.54	16.48	17.02	17.50
	6H	5.00	5.45	5.52	5.97	6.46	15.99	16.45	16.52	16.96	17.46
	8H	6.13	6.53	6.64	7.03	7.60	16.03	16.43	16.55	16.93	17.50