

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998495

Luminaire Tested: S124DR-B350DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P998495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DR-B350DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1468.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998495

CATALOG NUMBER: S124DR-B350DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998495

CATALOG NUMBER: S124DR-B350DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	73	73	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	60
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53	53	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	47	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	41	41	39
7	66	52	44	38	64	52	43	37	50	43	37	49	42	37	47	41	37	37	37	35
8	61	48	39	34	60	47	39	34	46	39	33	45	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4678	4622	4655
10°	4649	4584	4607
15°	4593	4519	4531
20°	4518	4438	4442
25°	4433	4346	4334
30°	4329	4237	4199
35°	4220	4124	4070
40°	4108	3995	3923
45°	3990	3869	3794
50°	3860	3756	3640
55°	3721	3610	3492
60°	3580	3446	3342
65°	3423	3290	3157
70°	3245	3080	2961
75°	2974	2829	2757
80°	2649	2541	2475
85°	2311	2227	2189

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3990 cd/sqm

TEST NUMBER: P998495

CATALOG NUMBER: S124DR-B350DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	3.7
10°-20°	151.9	10.3
20°-30°	223.5	15.2
30°-40°	259.8	17.7
40°-50°	259.8	17.7
50°-60°	227.2	15.5
60°-70°	168.7	11.5
70°-80°	95.7	6.5
80°-90°	27.4	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.3	29.2
0°-40°	689.1	46.9
0°-60°	1176.2	80.1
0°-90°	1468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	28
90°	0	0	0	0	0	

TEST NUMBER: P998495

CATALOG NUMBER: S124DR-B350DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)