

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007187

Luminaire Tested: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2367.0 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007187

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007187

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	64	64	61
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	55	55	53
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	48	48	46
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	43	43	41
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	38	38	36
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	34	34	33
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	31	31	29
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6419	6419	6419
5°	6433	6361	6399
10°	6385	6301	6301
15°	6309	6173	6123
20°	6211	5995	5923
25°	6098	5820	5692
30°	5956	5615	5436
35°	5812	5403	5149
40°	5677	5183	4867
45°	5513	4936	4559
50°	5348	4669	4239
55°	5156	4412	3896
60°	4964	4102	3529
65°	4738	3740	3109
70°	4479	3288	2679
75°	4122	2773	2228
80°	3631	2177	1871
85°	3058	1779	1669

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5513 cd/sqm

TEST NUMBER: P1007187

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	4.0
10°-20°	263.5	11.1
20°-30°	382.1	16.1
30°-40°	435.3	18.4
40°-50°	424.3	17.9
50°-60°	357.1	15.1
60°-70°	250.2	10.6
70°-80°	128.3	5.4
80°-90°	32.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.9	31.3
0°-40°	1175.2	49.6
0°-60°	1956.5	82.7
0°-90°	2367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2367.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1002	1002	1002	1002	1002	
5°	1000	997	989	996	995	95
15°	951	947	931	930	923	268
25°	863	851	823	813	805	397
35°	743	725	691	669	658	465
45°	608	586	545	514	503	469
55°	462	437	395	361	349	413
65°	312	287	247	216	205	309
75°	166	144	112	95	90	176
85°	42	28	24	24	23	48
90°	0	0	0	0	0	

TEST NUMBER: P1007187

CATALOG NUMBER: S125RDR-B610DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1001.8	1001.8	1001.8	1001.8	1001.8
2.5°	1004.1	1001.8	994.3	1001.8	1001.1
5°	1000.3	997.3	989.0	996.5	995.0
7.5°	992.8	989.7	979.9	986.0	984.4
10°	981.4	979.1	968.5	970.8	968.5
12.5°	968.5	965.5	950.4	951.9	948.1
15°	951.1	946.6	930.7	930.0	923.1
17.5°	933.0	926.2	907.3	903.5	898.2
20°	911.0	903.5	879.3	875.5	868.7
22.5°	886.8	879.3	853.5	845.2	839.9
25°	862.6	851.3	823.3	813.4	805.1
27.5°	835.4	821.8	792.2	779.4	771.1
30°	805.1	790.7	758.9	741.5	734.7
32.5°	775.6	758.2	725.7	706.0	696.9
35°	743.1	724.9	690.8	668.9	658.3
37.5°	712.0	690.1	655.3	629.6	619.0
40°	678.7	656.0	619.7	591.0	581.9
42.5°	643.9	620.5	582.6	555.4	541.0
45°	608.4	586.4	544.8	514.5	503.2
47.5°	571.3	548.6	507.0	476.0	463.1
50°	536.5	511.5	468.4	436.6	425.3
52.5°	498.7	472.9	432.8	398.0	386.7
55°	461.6	437.4	395.0	360.9	348.8
57.5°	423.7	398.0	357.2	323.9	313.3
60°	387.4	360.9	320.1	286.8	275.4
62.5°	348.8	323.9	282.2	252.0	240.6
65°	312.5	286.8	246.7	216.4	205.1
67.5°	276.2	250.5	211.9	183.1	174.0
70°	239.1	213.4	175.5	152.1	143.0
72.5°	202.8	177.8	143.0	121.8	116.5
75°	166.5	143.8	112.0	95.3	90.0
77.5°	129.4	111.2	84.7	71.9	67.3
80°	98.4	80.2	59.0	52.2	50.7
82.5°	68.1	52.2	39.3	37.1	36.3
85°	41.6	28.0	24.2	23.5	22.7
87.5°	17.4	12.1	11.4	11.4	10.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)