

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037181

Luminaire Tested: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Regressed Direct Surface with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1625.0 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037181

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1037181

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12507	12507	12507
5°	12554	12351	12418
10°	12459	12148	12045
15°	12315	11788	11448
20°	12117	11274	10708
25°	11915	10691	9990
30°	11632	10090	9070
35°	11359	9438	8263
40°	11082	8761	7329
45°	10756	8003	6483
50°	10424	7238	5652
55°	10084	6414	4854
60°	9688	5547	4030
65°	9240	4659	3671
70°	8706	3837	3374
75°	8049	3498	3150
80°	7101	3127	2871
85°	5576	2470	2470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10756 cd/sqm

TEST NUMBER: P1037181

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	4.6
10°-20°	203.3	12.5
20°-30°	285.4	17.6
30°-40°	311.1	19.1
40°-50°	285.9	17.6
50°-60°	224.6	13.8
60°-70°	146.2	9.0
70°-80°	75.2	4.6
80°-90°	19.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.8	34.6
0°-40°	873.9	53.8
0°-60°	1384.4	85.2
0°-90°	1625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1625.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	787	777	784	782	75
15°	752	744	719	706	699	212
25°	682	659	612	583	572	314
35°	588	551	488	443	428	368
45°	480	433	358	307	290	371
55°	365	310	232	190	176	326
65°	247	189	124	100	98	245
75°	132	82	57	52	52	139
85°	31	16	14	14	14	37
90°	0	0	0	0	0	

TEST NUMBER: P1037181

CATALOG NUMBER: S122RDS-B485DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	790.1	790.1	790.1	790.1	790.1
2.5°	793.7	790.1	782.3	789.4	788.0
5°	790.1	786.6	777.3	783.7	781.5
7.5°	783.7	779.4	769.4	772.3	768.7
10°	775.1	770.1	755.8	753.7	749.4
12.5°	764.4	758.0	738.6	734.4	726.5
15°	751.5	743.6	719.3	705.8	698.6
17.5°	736.5	725.1	695.0	679.3	667.9
20°	719.3	705.0	669.3	651.4	635.7
22.5°	700.7	684.3	642.8	618.5	607.8
25°	682.2	659.3	612.1	582.8	572.0
27.5°	660.0	635.7	583.5	549.9	533.4
30°	636.4	609.2	552.0	515.5	496.2
32.5°	613.5	580.6	522.0	479.1	461.2
35°	587.8	551.3	488.4	443.3	427.6
37.5°	562.7	523.4	456.9	407.6	389.7
40°	536.3	493.4	424.0	373.3	354.7
42.5°	509.1	463.4	391.1	338.2	320.3
45°	480.5	432.6	357.5	306.8	289.6
47.5°	453.3	402.6	325.3	274.6	258.8
50°	423.3	372.5	293.9	244.5	229.5
52.5°	394.0	340.4	263.9	216.7	203.1
55°	365.4	309.6	232.4	189.5	175.9
57.5°	336.1	278.9	204.5	164.5	153.0
60°	306.0	248.8	175.2	138.7	127.3
62.5°	276.7	219.5	150.2	115.8	110.1
65°	246.7	188.8	124.4	100.1	98.0
67.5°	218.1	160.2	100.1	88.0	85.8
70°	188.1	132.3	82.9	75.8	72.9
72.5°	159.5	106.5	69.4	63.6	62.2
75°	131.6	81.5	57.2	52.2	51.5
77.5°	103.7	57.9	45.0	42.2	40.8
80°	77.9	41.5	34.3	31.5	31.5
82.5°	54.3	27.9	23.6	22.2	22.2
85°	30.7	15.7	13.6	13.6	13.6
87.5°	11.4	5.7	5.7	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)