

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037594

Luminaire Tested: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct Surface with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4421.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037594

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1037594

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	52	43	37	50	43	37	49	42	37	47	41	37
8	61	48	39	34	60	47	39	34	46	39	33	45	38	33	43	37	33
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14045	14045	14045
5°	14088	13919	14020
10°	13999	13805	13874
15°	13831	13609	13644
20°	13606	13366	13378
25°	13350	13089	13052
30°	13035	12761	12645
35°	12709	12421	12255
40°	12370	12033	11813
45°	12017	11651	11428
50°	11626	11311	10961
55°	11204	10870	10518
60°	10782	10377	10061
65°	10306	9906	9507
70°	9773	9279	8917
75°	8957	8523	8305
80°	7974	7650	7453
85°	6970	6718	6587

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12017 cd/sqm

TEST NUMBER: P1037594

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	3.7
10°-20°	457.4	10.3
20°-30°	673.1	15.2
30°-40°	782.5	17.7
40°-50°	782.4	17.7
50°-60°	684.3	15.5
60°-70°	508.0	11.5
70°-80°	288.3	6.5
80°-90°	82.6	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1292.9	29.2
0°-40°	2075.4	46.9
0°-60°	3542.1	80.1
0°-90°	4421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4421.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1722	1722	1722	1722	1722	
5°	1721	1716	1700	1716	1713	163
15°	1638	1633	1612	1620	1616	462
25°	1484	1474	1455	1456	1451	683
35°	1277	1267	1248	1238	1231	798
45°	1042	1032	1010	995	991	803
55°	788	784	765	748	740	706
65°	534	527	513	500	493	529
75°	284	277	270	265	264	302
85°	74	74	72	72	70	85
90°	0	0	0	0	0	

TEST NUMBER: P1037594

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1722.4	1722.4	1722.4	1722.4	1722.4
2.5°	1728.0	1723.8	1708.6	1722.4	1721.1
5°	1721.1	1715.5	1700.4	1715.5	1712.8
7.5°	1708.6	1703.1	1686.6	1699.0	1697.6
10°	1690.7	1685.2	1667.2	1678.3	1675.5
12.5°	1667.2	1661.7	1642.4	1654.8	1650.7
15°	1638.3	1632.7	1612.0	1620.3	1616.2
17.5°	1605.1	1598.2	1578.9	1584.4	1581.7
20°	1567.9	1561.0	1540.3	1544.4	1541.6
22.5°	1527.8	1518.2	1497.5	1505.8	1500.2
25°	1483.7	1474.0	1454.7	1456.1	1450.6
27.5°	1434.0	1424.3	1406.4	1403.6	1396.7
30°	1384.3	1373.3	1355.3	1349.8	1342.9
32.5°	1331.9	1322.2	1302.9	1296.0	1289.1
35°	1276.7	1267.0	1247.7	1238.0	1231.1
37.5°	1218.7	1210.4	1189.7	1180.0	1170.4
40°	1162.1	1151.1	1130.4	1116.6	1109.7
42.5°	1101.4	1095.9	1072.4	1055.8	1051.7
45°	1042.0	1032.4	1010.3	995.1	991.0
47.5°	979.9	973.0	952.3	935.8	924.7
50°	916.4	910.9	891.6	872.3	864.0
52.5°	854.3	847.4	826.7	810.2	799.1
55°	788.1	783.9	764.6	748.1	739.8
57.5°	726.0	721.8	702.5	685.9	677.7
60°	661.1	654.2	636.3	623.8	616.9
62.5°	597.6	592.1	572.8	561.7	554.8
65°	534.1	527.2	513.4	499.6	492.7
67.5°	469.3	463.7	449.9	436.1	434.8
70°	409.9	400.2	389.2	378.2	374.0
72.5°	346.4	336.8	328.5	320.2	316.1
75°	284.3	277.4	270.5	265.0	263.6
77.5°	223.6	220.8	213.9	212.5	208.4
80°	169.8	165.6	162.9	160.1	158.7
82.5°	117.3	115.9	115.9	114.6	113.2
85°	74.5	74.5	71.8	71.8	70.4
87.5°	35.9	34.5	33.1	33.1	33.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)