

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1059689

Luminaire Tested: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

Issue Date: 8/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1059689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2406-143-69)
Test Lab: INNOVATION CENTER
Issue Date: 8/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDR-H560D927-X4F0-XX-UDD-BVL-S
Description: DEFINE 3 SILVER REGRESSED DIRECT RECESSED HOUSING WITH BLACK STRAIGHT BLADE
LOUVER WITH DIFFUSER
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 411.5 lumens
Efficiency: N/A
Efficacy: 23.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 1.06 / 0.94
Luminous Opening: Rectangular (W 0.23' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1059689

CATALOG NUMBER: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

Luminous Intensity Polar Plot





TEST NUMBER: P1059689

CATALOG NUMBER: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90				
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81				
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73				
4	92	83	76	71	90	81	75	70	79	74	69	77	72	69	75	71	68	66				
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60				
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55				
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50				
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4023	4023	4023
5°	3884	3951	4014
10°	3585	3748	3947
15°	3215	3465	3833
20°	2808	3123	3653
25°	2362	2748	3427
30°	1897	2344	3211
35°	1389	1929	3003
40°	858	1502	2794
45°	330	1131	2488
50°	163	775	2104
55°	129	430	1652
60°	87	357	1106
65°	72	320	495
70°	72	288	288
75°	95	309	286
80°	142	392	318
85°	216	633	418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 2488 cd/sqm



TEST NUMBER: P1059689

CATALOG NUMBER: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.4	7.6
10°-20°	80.4	19.5
20°-30°	99.8	24.3
30°-40°	89.4	21.7
40°-50°	58.8	14.3
50°-60°	29.5	7.2
60°-70°	11.6	2.8
70°-80°	6.5	1.6
80°-90°	4.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.6	51.4
0°-40°	301.0	73.2
0°-60°	389.3	94.6
0°-90°	411.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	411.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	343	343	343	343	343	
5°	330	335	335	337	340	31
15°	264	273	285	304	315	74
25°	182	194	212	242	264	83
35°	97	110	135	176	210	60
45°	20	33	68	115	150	19
55°	6	7	21	57	81	6
65°	3	7	12	15	18	3
75°	2	7	7	6	6	2
85°	2	5	5	5	3	2
90°	0	0	0	0	0	



TEST NUMBER: P1059689

CATALOG NUMBER: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	342.6	342.6	342.6	342.6	342.6
2.5°	338.4	343.1	340.5	340.5	341.0
5°	329.5	334.7	335.2	337.3	340.5
7.5°	316.4	323.2	326.3	332.6	337.3
10°	300.7	308.0	314.3	325.3	331.0
12.5°	283.4	290.7	300.1	315.3	324.2
15°	264.5	272.9	285.0	304.3	315.3
17.5°	245.1	253.5	268.2	290.2	304.3
20°	224.7	234.1	249.9	275.0	292.3
22.5°	204.3	214.8	231.5	258.8	278.7
25°	182.3	193.8	212.1	242.0	264.5
27.5°	161.3	173.4	192.8	225.2	250.9
30°	139.9	151.9	172.9	208.0	236.8
32.5°	117.9	131.5	153.5	191.7	222.6
35°	96.9	110.0	134.6	176.0	209.5
37.5°	76.5	89.6	115.2	160.8	196.4
40°	56.0	69.7	98.0	146.1	182.3
42.5°	36.7	50.8	82.8	131.5	166.6
45°	19.9	33.0	68.1	114.7	149.8
47.5°	11.0	17.8	55.0	99.0	133.6
50°	8.9	10.0	42.4	84.3	115.2
52.5°	7.3	8.4	30.4	70.2	98.5
55°	6.3	7.3	21.0	56.6	80.7
57.5°	5.2	6.3	16.8	43.5	63.4
60°	3.7	6.3	15.2	32.0	47.1
62.5°	3.1	6.3	13.1	22.0	31.4
65°	2.6	7.3	11.5	14.7	17.8
67.5°	2.1	7.3	10.0	9.4	9.4
70°	2.1	7.3	8.4	7.9	8.4
72.5°	2.1	7.9	7.9	7.3	7.3
75°	2.1	6.8	6.8	6.3	6.3
77.5°	2.1	6.3	6.3	5.8	5.8
80°	2.1	5.8	5.8	5.2	4.7
82.5°	2.1	5.2	5.2	4.7	4.2
85°	1.6	4.7	4.7	4.7	3.1
87.5°	1.6	4.2	4.7	4.2	2.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1059689
 CATALOG NUMBER: S123RDR-H560D927-X4F0-XX-UDD-BVL-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	11.39	12.64	11.75	12.96	13.27
	3H	0.00	0.92	0.19	1.25	1.62	11.46	12.58	11.84	12.91	13.27
	4H	0.98	2.02	1.39	2.37	2.75	11.53	12.56	11.93	12.91	13.30
	6H	2.04	2.99	2.46	3.36	3.76	11.63	12.58	12.04	12.95	13.34
	8H	2.58	3.48	3.01	3.87	4.28	11.69	12.59	12.12	12.98	13.38
	12H	3.07	3.93	3.50	4.31	4.74	11.75	12.61	12.19	13.00	13.43
4H	2H	0.55	1.58	0.95	1.94	2.32	11.25	12.28	11.65	12.63	13.02
	3H	3.01	3.86	3.43	4.26	4.67	11.42	12.27	11.83	12.67	13.07
	4H	4.36	5.12	4.80	5.54	5.98	11.55	12.30	11.98	12.72	13.17
	6H	5.50	6.15	5.96	6.60	7.07	11.76	12.42	12.23	12.86	13.33
	8H	6.01	6.62	6.48	7.07	7.54	11.89	12.50	12.36	12.95	13.42
	12H	6.47	7.01	6.95	7.49	7.97	12.05	12.58	12.53	13.07	13.54
8H	4H	5.28	5.89	5.75	6.34	6.81	11.55	12.16	12.02	12.61	13.08
	6H	6.89	7.39	7.39	7.89	8.37	11.88	12.38	12.38	12.88	13.36
	8H	7.71	8.16	8.23	8.68	9.17	12.11	12.56	12.63	13.08	13.57
	12H	8.49	8.89	9.00	9.38	9.95	12.43	12.83	12.95	13.32	13.90
12H	4H	5.45	5.99	5.94	6.47	6.95	11.54	12.08	12.03	12.56	13.04
	6H	7.20	7.65	7.73	8.17	8.66	11.91	12.36	12.43	12.88	13.37
	8H	8.20	8.60	8.72	9.10	9.67	12.22	12.62	12.73	13.11	13.69