

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037595

Luminaire Tested: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037595
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct Surface with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4377.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037595

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1037595

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79	76	73	70
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70	66	62	60
4	83	71	63	56	81	70	62	56	67	60	55		65	59	54		63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52	46	41	39
7	66	52	44	38	64	52	43	37	50	43	37		49	42	37		47	41	37	35
8	61	48	39	34	60	47	39	34	46	39	33		45	38	33		43	37	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13947	13780	13880
10°	13860	13667	13735
15°	13693	13474	13508
20°	13471	13233	13245
25°	13216	12958	12921
30°	12905	12634	12519
35°	12582	12297	12134
40°	12247	11913	11695
45°	11898	11534	11314
50°	11510	11198	10852
55°	11092	10762	10412
60°	10674	10273	9962
65°	10203	9808	9412
70°	9675	9186	8829
75°	8869	8437	8223
80°	7894	7570	7377
85°	6905	6652	6521

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11898 cd/sqm

TEST NUMBER: P1037595

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	3.7
10°-20°	452.8	10.3
20°-30°	666.4	15.2
30°-40°	774.7	17.7
40°-50°	774.6	17.7
50°-60°	677.5	15.5
60°-70°	503.0	11.5
70°-80°	285.4	6.5
80°-90°	81.7	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1280.0	29.2
0°-40°	2054.7	46.9
0°-60°	3506.8	80.1
0°-90°	4377.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4377.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	84
90°	0	0	0	0	0	

TEST NUMBER: P1037595

CATALOG NUMBER: S124DS-B1020DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)