

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1056127

Luminaire Tested: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

Issue Date: 7/25/2025

Test Information

Test Method: LM-79-2024
Report Number: P1056127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2503-402-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/25/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124R3DR-H1195D927-X4F0-XX-UDD-F-B
Description: DEFINE 4, BLACK 3-INCH REGRESSED DIRECT RECESSED HOUSING WITH FROSTED LENS
HIGH PERFORMANCE LIGHT ENGINE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1647.6 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 0.81 / 0.97
Luminous Opening: Rectangular (W 0.31' x L: 3.9' x H: 0')
CIE Type: Direct

Input Watts (W): 36.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1056127

CATALOG NUMBER: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

Luminous Intensity Polar Plot





TEST NUMBER: P1056127

CATALOG NUMBER: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	84	74	66	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52
7	74	63	55	50	73	62	55	50	60	54	50	59	53	49	58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	39	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10422	10422	10422
5°	10329	10237	10226
10°	10241	9836	9577
15°	10113	9246	8675
20°	9950	8525	7579
25°	9730	7677	6324
30°	9486	6737	5026
35°	9219	5713	3742
40°	8937	4655	2494
45°	8627	3555	1373
50°	8330	2432	381
55°	7999	1318	250
60°	7602	408	143
65°	7109	266	73
70°	6424	119	31
75°	5527	41	0
80°	4180	0	0
85°	1755	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8627 cd/sqm



TEST NUMBER: P1056127

CATALOG NUMBER: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	6.6
10°-20°	285.5	17.3
20°-30°	368.9	22.4
30°-40°	352.6	21.4
40°-50°	263.7	16.0
50°-60°	156.9	9.5
60°-70°	79.7	4.8
70°-80°	27.7	1.7
80°-90°	3.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.2	46.3
0°-40°	1115.8	67.7
0°-60°	1536.4	93.3
0°-90°	1647.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1647.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1164	1173	1153	1148	1152	110
15°	1105	1082	1010	963	948	311
25°	997	928	787	683	648	459
35°	854	736	529	394	347	534
45°	690	529	284	151	110	533
55°	519	322	86	20	16	463
65°	340	131	13	5	4	336
75°	162	17	1	1	0	172
85°	17	0	0	0	0	29
90°	0	0	0	0	0	



TEST NUMBER: P1056127

CATALOG NUMBER: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	<i>1178.8</i>	1178.8	1178.8	1178.8
2.5°	<i>1167.3</i>	<i>1181.1</i>	<i>1169.6</i>	<i>1170.7</i>	<i>1171.9</i>
5°	1163.8	<i>1173.0</i>	1153.4	1147.6	1152.2
7.5°	1154.5	<i>1158.0</i>	1129.1	1114.1	1115.2
10°	1140.7	<i>1137.2</i>	1095.6	1070.2	1066.7
12.5°	1124.5	<i>1112.9</i>	1055.2	1018.2	1010.1
15°	1104.8	<i>1081.7</i>	1010.1	962.7	947.7
17.5°	1081.7	<i>1048.2</i>	960.4	898.0	879.5
20°	1057.5	<i>1011.2</i>	906.1	828.6	805.5
22.5°	1028.6	<i>969.6</i>	847.1	755.8	726.9
25°	997.4	<i>928.0</i>	787.0	683.0	648.3
27.5°	965.0	<i>883.0</i>	723.5	609.1	568.6
30°	929.2	<i>835.6</i>	659.9	533.9	492.3
32.5°	892.2	<i>787.0</i>	594.0	464.6	418.4
35°	854.1	<i>736.2</i>	529.3	394.1	346.7
37.5°	814.8	<i>685.3</i>	466.9	327.1	278.5
40°	774.3	<i>633.3</i>	403.3	263.5	216.1
42.5°	735.0	<i>581.3</i>	343.2	203.4	159.5
45°	690.0	<i>529.3</i>	284.3	151.4	109.8
47.5°	649.5	<i>478.5</i>	227.7	102.9	64.7
50°	605.6	<i>424.1</i>	176.8	60.1	27.7
52.5°	561.7	<i>373.3</i>	129.4	26.6	20.8
55°	518.9	<i>322.4</i>	85.5	19.6	16.2
57.5°	473.8	<i>271.6</i>	46.2	15.0	11.6
60°	429.9	<i>221.9</i>	23.1	11.6	8.1
62.5°	384.8	<i>174.5</i>	18.5	6.9	4.6
65°	339.8	<i>130.6</i>	12.7	4.6	3.5
67.5°	294.7	<i>89.0</i>	8.1	2.3	1.2
70°	248.5	<i>54.3</i>	4.6	1.2	1.2
72.5°	204.6	<i>27.7</i>	2.3	1.2	1.2
75°	161.8	<i>17.3</i>	1.2	1.2	0.0
77.5°	120.2	<i>9.2</i>	1.2	1.2	0.0
80°	82.1	<i>3.5</i>	0.0	0.0	0.0
82.5°	47.4	<i>1.2</i>	0.0	0.0	0.0
85°	17.3	<i>0.0</i>	0.0	0.0	0.0
87.5°	0.0	<i>0.0</i>	0.0	0.0	0.0
90°	0.0	<i>0.0</i>	0.0	0.0	0.0



TEST NUMBER: P1056127
 CATALOG NUMBER: S124R3DR-H1195D927-X4F0-XX-UDD-F-B

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.60	19.93	18.96	20.24	20.56	0.00	0.00	0.00	0.00	0.00
	3H	20.14	21.32	20.52	21.65	22.01	0.00	0.00	0.00	0.00	0.00
	4H	20.73	21.83	21.14	22.18	22.56	0.00	0.00	0.00	0.00	0.00
	6H	21.15	22.16	21.57	22.53	22.92	0.00	0.00	0.00	0.00	0.00
	8H	21.25	22.20	21.68	22.59	23.00	0.00	0.00	0.00	0.00	0.00
	12H	21.27	22.18	21.70	22.56	22.99	0.00	0.00	0.00	0.00	0.00
4H	2H	18.38	19.47	18.78	19.82	20.21	0.00	0.00	0.00	0.00	0.07
	3H	19.94	20.83	20.35	21.24	21.64	0.00	0.00	0.00	0.00	0.00
	4H	20.52	21.32	20.96	21.74	22.18	0.00	0.00	0.00	0.00	0.00
	6H	20.98	21.67	21.45	22.12	22.58	0.00	0.00	0.00	0.00	0.00
	8H	21.10	21.74	21.57	22.19	22.66	0.00	0.00	0.00	0.00	0.00
	12H	21.14	21.71	21.63	22.19	22.67	0.00	0.00	0.00	0.00	0.00
8H	4H	20.39	21.03	20.86	21.48	21.95	0.00	0.53	0.36	0.98	1.45
	6H	20.83	21.35	21.33	21.85	22.33	0.00	0.33	0.31	0.82	1.30
	8H	20.95	21.41	21.47	21.93	22.42	0.00	0.21	0.26	0.73	1.22
	12H	20.99	21.41	21.51	21.90	22.47	0.00	0.11	0.21	0.61	1.18
12H	4H	20.34	20.91	20.83	21.39	21.86	0.31	0.87	0.79	1.35	1.83
	6H	20.77	21.23	21.29	21.75	22.24	0.20	0.67	0.72	1.18	1.68
	8H	20.90	21.31	21.42	21.81	22.38	0.16	0.57	0.67	1.06	1.63